

6 ft DVI-D Dual Link Cable - M/M

Product ID: DVIDDMM6



The DVIDDMM6 6ft DVI-D Dual Link cable features 2 male DVI (25-pin) connectors and provides a reliable, purely digital connection between your desktop or laptop computer and a DVI-D monitor or projector.

The 6 ft DVI-D digital monitor cable supports resolutions of up to 2560x1600 and transmission rates of up to 9.9 Gbits/sec and is fully compliant with DVI DDWG standards.

Designed and constructed for maximum durability, this high quality digital video cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Connect your desktop or laptop computer to a DVI-D Dual Link display or projector

Features

- Supports a maximum resolution of 2560x1600
- High-speed digital transmission rate of up to 9.9 Gbits/sec
- Ferrite core eliminates EMI interference
- Aluminum-Mylar Foil with Braided Shielding
- Supports hot-plugging of DVI display devices

- Compliant with DVI DDWG Standards

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Shield Material	Aluminum-Mylar Foil with Braid
Industry Standards	DVI DDWG Standard

Performance

General Specifications	Insertion Rating: 3000
------------------------	------------------------

Connector(s)

Connector A	DVI-D (25 pin)
Connector B	DVI-D (25 pin)

Environmental


Operating Temperature	0 to 50 C
Storage Temperature	-20 to 70 C
Humidity	0 to 95%

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	1.6 in [40.0 mm]
Product Height	0.6 in [16.0 mm]
Weight of Product	9.7 oz [274.0 g]

Packaging Information

Package Length	0.9 in [22.5 mm]
Package Width	0.8 in [20.0 mm]



Package Height	0.0 in [0.1 mm]
Shipping (Package) Weight	10.0 oz [284.0 g]

What's in the Box

Included in Package	6 ft DVI-D Dual Link Cable - M/M
---------------------	----------------------------------

****Product appearance and specifications are subject to change without notice.***

