



0.138"±0.02" Y4



1.58"±0.2" Y2

BLACK BOX CORP.
DVI-I-DL-***M



Only one CABLE LABEL on cable unless
the cable is over 20 feet then each
side of cable get a CABLE LABEL

1.58"±0.2" Y3

(0.4")

MM/YY

BLACK BOX CORP.
DVI-I-DL-***M



MATERIALS LIST:

- UL20276 1354(S)28AWG*3C+(28AWG*1PR+EAM)*7+28AWG*1PR+28AWG*5C
+DAB 85% OD:0.39" COLOR:BLACK
- CONNECTOR: DVI-I (24+5) MALE, PIN G/F, GOLD FLASH SHELL
- MOLDING PVC:COLOR:BLACK V398 45P
- SCREW: #4-40 0.158"*1.12" COLOR:BLACK
- COVER: V027 45P
- LABEL: YEAR MONTH LABEL

ELECTRONIC TEST:

- OPEN/SHORT/INTERMITTENCE: 100%.
- HI-POT: 300V DC/sec
- INSULATION RESISTANCE: 20M ohm (MIN)
- CONDUCTIVE RESISTANCE: 1~3M 2 ohm (MAX)
5M 3 ohm (MAX)
10M 6 ohm (MAX)

COMPUTER TEST:

A:under 15ft....UXGA(1600*1200),
15.1~25ft.....SXGA(1280*1024)

NOTES:

- CHECK IMPORTANT SIZE Y1-Y5
- ALL MATERIALS TO MEET RoHS

PIN OUT

CN1	CN2	CN1	CN2
1 WHITE	1 WHITE	17 WHITE	17 WHITE
2 BROWN	2 BROWN	18 BLUE	18 BLUE
3 DRAIN	3 DRAIN	19 DRAIN	19 DRAIN
4 GRAY	4 GRAY	20 BULE	20 BULE
5 BLACK	5 BLACK	21 PURPLE	21 PURPLE
6 ORANGE	6 ORANGE	22 DRAIN	22 DRAIN
7 YELLOW	7 YELLOW	23 PINK	23 PINK
8 GREEN	8 GREEN	24 ORANGE	24 ORANGE
9 WHITE	9 WHITE	C1 RED(CEN)	C1 RED(CEN)
10 RED	10 RED	C2 GREEN(CEN)	C2 GREEN(CEN)
11 DRAIN	11 DRAIN	C3 BULE(CEN)	C3 BULE(CEN)
12 WHITE	12 WHITE	C4 WHITE	C4 WHITE
13 GREEN	13 GREEN	C5 GREEN(S)+BULE(S)+RED(S)	C5 GREEN(S)+BULE(S)+RED(S)
14 RED	14 RED	SHELL BRAID	SHELL BRAID
15 BLACK	15 BLACK		
16 BROWN	16 BROWN		

Customer P/N	SSTL P/N	LENGHT
DVI-I-DL-001M	J00581477	39"+3"/-0
DVI-I-DL-001.5M	J00581478	59"+3"/-0
DVI-I-DL-002M	J00581479	79"+3"/-0
DVI-I-DL-003M	J00581480	118"+3"/-0
DVI-I-DL-005M	J00581481	197"+6"/-0
DVI-I-DL-010M	J00581482	394"+6"/-0

 BLACK BOX			
Tolerance:	Approved by:		
X. ±	<i>wayne</i>		
.X ±	Checked by:	BLACK BOX P/N:	
.XX ±	<i>lucency</i>	DVI-I-DL-xxxM	
.XXX ±	Drawn by:	Description:	
Angle:	<i>xiong</i>	DVI I TO DVI I CABLE	
X' ±	Date:	DWG. NO:	
.X' ±	11.12.24	T101105004	
	Scale:	Unit: mm	SHEET: 1 OF 1
			REV: 01

REV	ECN NO	DESCRIPTION	Drawn	DATE
01	R111212001	CHANGE YEAR MONTH LABEL PRESS	xiong	11.12.24