

1 Port USB Wireless N Network Print Server with 10/100 Mbps Ethernet Port - 802.11 b/g/n

**Product ID:** PM1115UW



The PM1115UW Wireless-N Print Server lets you share a standard USB printer with multiple users simultaneously over a WiFi network, or a wired LAN connection.

This compact wireless print server supports 802.11b/g/n wireless standards for functionality with almost any wireless network, plus, serving as a primary or backup interface the print server also offers an RJ45 port for 10/100 Mbps wired connections. Providing wireless network printing access enables you to place your printer in any location with network access and avoids the added cost of purchasing individual printers for each workstation or area.

This wireless USB print server can have you up and running in minutes, using either a web-based interface or a Windows based installation wizard, and also features a WiFi Protected Setup (WPS) button for quick and easy connection to your wireless network. Compatibility with USB 2.0 standards and a wide variety of USB printers and operating systems makes this network print server perfect for installation into mixed environments, with Simple Network Management Protocol (SNMP) support for remote monitoring.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Convert a standard USB printer into a standalone, wireless printer and share between multiple networked computers
- A convenient network printing solution for education and government institutions
- Eliminate the performance issues of an always-on, dedicated PC acting as the printer server

## Features

- Compliant with 802.11b/g/n wireless networks, with data rates up to 150 Mbps
- USB 2.0 support
- Optional 10/100 Mbps RJ-45 LAN Port
- Compact, lightweight design with an internal antenna
- Supports SNMP for remote printer management - works with most SNMP based applications
- Easy-to-use web interface or Windows-based configuration and setup
- Built-in multi-function button for resetting the device, loading factory defaults or printing a self-test page
- Built-in WPS (WiFi Protected Setup) button for simple connection to a wireless network
- Supports DHCP Server/Client protocols, and UPnP

---

### Hardware

Warranty	2 Years
Ports	1
Interface	USB 2.0
	RJ45 (10/100 Ethernet)
	Wireless Ethernet
Industry Standards	IEEE 802.3 10BASE-T, IEEE 802.3u 100BASE-T, IEEE 802.11b/g/n Wireless

---

### Performance

Compatible Networks	10/100 Mbps
Frequency	2.4 GHz
Security Features	WEP Data Encryption
	WPA and WPA2-PSK Data Encryption
Supported Protocols	TCP/IP (LDP / LPR Printer Port)
	IPX
	NetBEUI
	AppleTalk



SNMP

SMB over IP

---

**Connector(s)**

Connector Type(s)	USB Type-A (4 pin) USB 2.0
	RJ-45
	Wireless N (IEEE 802.11n)

---

**Software**

OS Compatibility	Windows XP, Vista, 7, 8, 8.1, 10
	Windows Server 2003, 2008 R2, 2012, 2016, 2019
	Mac OS 10.x, 9.x
	Linux (<i>LTS Versions only</i>)

---

**Special Notes / Requirements**

System and Cable Requirements	USB printer cable not included
Note	The device is compatible with any operating system that supports network printing. Please note that the included software is compatible with Windows only.

---

**Indicators**

LED Indicators	Status
	USB
	WLAN

---

**Power**

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.2 A
Output Voltage	5 DC
Output Current	1 A
Center Tip Polarity	Positive



Plug Type H

Power Consumption (In Watts) 10

#### Environmental

Operating Temperature 0C to 50C (32F to 122F)

Storage Temperature -5C to 65C (23F to 149F)

Humidity 0~70% RH (Non-Condensing)

#### Physical Characteristics

Color White

Material Plastic

Product Length 2.8 in [72 mm]

Product Width 2.3 in [58 mm]

Product Height 1.0 in [25 mm]

Weight of Product 1.8 oz [52 g]

#### Packaging Information

Package Length 6.0 in [15.3 cm]

Package Width 9.1 in [23.2 cm]

Package Height 2.7 in [68 mm]

Shipping (Package) Weight 10.8 oz [306 g]

#### What's in the Box

Included in Package Wireless Print Server

Power Adapter

Software CD

Quick Install Guide

***\*Product appearance and specifications are subject to change without notice.***

