

1 Port 10/100 Mbps Ethernet Parallel Network Print Server

Product ID: PM1115P2



The PM1115P2 Ethernet to Parallel Network Print Server lets you convert a standard parallel printer into a shared network printer over a 10/100Mbps network. Providing network printing access allows you to share a single printer among multiple network connected computers, while also avoiding the added costs and inconveniences of purchasing printers for each workstation or area.

This compact, lightweight Ethernet print server connects directly to the Centronics port on your printer, for a discreet solution that doesn't require a cable between your printer and the device - simply connect the device to the network using an RJ45 cable. The ability to position your printer anywhere on the network does away with the need for a dedicated print server PC, saving resources and avoiding performance bottlenecks.

The parallel print server can have you up and running in minutes, using either a remote web-based or Windows based installation wizard. The print server offers broad operating system compatibility and works with a wide variety of parallel printing devices for easy installation into mixed environments, and also supports Simple Network Management Protocol (SNMP) for remote monitoring.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Convert a standard parallel printer into a standalone network printer and share a single printer among multiple network connected computers
- A convenient network printing solution for education and government institutions
- Eliminate performance issues of an always-on dedicated PC acting as the printer server

Features

- Connects directly to the Centronics port of a printer
- Compliant with IEEE 802.3, and IEEE 802.3u standards
- Compact and lightweight
- Supports SNMP for remote printer management - works with most SNMP based applications
- Easy-to-use web interface or Windows-based configuration and setup
- Support for Internet Printing Protocol(IPP), Print Job Control/Status, Email Alert, Rendezvous, DHCP Client, SNMP (v1 and 2) & HP Web JetAdmin, Windows Print Monitor Technology
- Supports 10/100Mbps Ethernet network

Hardware

Warranty	2 Years
Ports	1
Interface	Parallel RJ45 (10/100 Ethernet)
Industry Standards	IEEE 802.3 10BASE-T, IEEE 802.3u 100BASE-TX

Performance

Maximum Data Transfer Rate	100Mbps
Remote Management Ability	Yes
Supported Protocols	IPX >TCP/IP (LPR, IPP, RAW 9100) NetBEUI >AppleTalk SNMP v1 and 2 SMB

Connector(s)

Connector Type(s)	RJ-45 Centronics (36 pin)
-------------------	------------------------------

Software



OS Compatibility	Windows 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server 2003, 2008 R2, 2012, 2012 R2, 2016, 2019 Mac OS 10.6 to 10.9 Unix/Linux
------------------	--

Special Notes / Requirements

System and Cable Requirements	Ethernet network cable not included
Note	OS Compatibility refers to the included software only – the Print Server itself can be used without software on any platform that supports network printing

Indicators

LED Indicators	Power/Status: Yellow Solid 100Mbps Link/Activity: Green Solid/Flashing 10Mbps Link/Activity: Yellow Solid/Flashing
----------------	--

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.2 A
Output Voltage	5 DC
Output Current	1 A
Center Tip Polarity	Positive
Plug Type	H

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	0C to 50C (32F to 122F)
Humidity	10~70% RH

Physical Characteristics

Color	Beige
-------	-------



Material	Plastic
Product Length	2.4 in [60 mm]
Product Width	2.4 in [62 mm]
Product Height	0.9 in [24 mm]
Weight of Product	1.8 oz [52 g]

Packaging Information

Package Length	9.0 in [22.8 cm]
Package Width	6.0 in [15.2 cm]
Package Height	2.6 in [67 mm]
Shipping (Package) Weight	2.7 oz [76 g]

What's in the Box

Included in Package	Parallel Print Server
	Power Adapter
	Software CD
	Quick Start Guide

****Product appearance and specifications are subject to change without notice.***

