

4 Port Gigabit Power over Ethernet PCIe Network Card - PSE / PoE PCI Express NIC

Product ID: ST4000PEXPSE



The ST4000PEXPSE 4-Port PoE NIC lets you add four Gigabit Power over Ethernet ports through a single PCI Express slot. Each port can provide up to 25.5W of power, combining network data and power over a single Ethernet cable for reduced cable clutter and added convenience for remote PoE devices.

The PCI express PoE card supports the IEEE 802.3at (Type 1 and 2) standard for Power Sourcing Equipment (PSE), and can deliver up to 48V DC power to compliant Powered Devices (PD). This eliminates the need for a separate power source and data connection for PoE devices such as IP cameras, IP phones or wireless access points.

Suitable for any standard profile PCIe-enabled client, server or workstation, the PoE network card supports features such as Jumbo Frames (up to 9KB), VLAN tagging and Wake on LAN (WoL).

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Create a host computer for networked security cameras situated in remote areas, where standard power connection is not possible
- Install PoE-powered Wireless Access Points (WAP) or repeaters in industrial, warehousing or business environments
- Enable remote installation of touchscreens or information kiosks

Features

- Four 10/100/1000 Mbps compatible PoE RJ45 ports
- Fully compliant with IEEE 802.3at (Type 1 & 2) Power over Ethernet standards
- Power Sourcing Equipment (PSE) supports up to 48V, 25.5 Watts max. output per port
- Built-in SATA and LP4 Molex power connector
- Up to 9K Jumbo Frame support
- Wake-on-LAN (Remote Wake-up) support
- Supports Pair Swap, Polarity and Skew Correction

Hardware

Warranty	2 Years
Ports	4
Interface	RJ45 (Gigabit Ethernet)
Bus Type	PCI Express
Card Type	Standard Profile
Port Style	Integrated on Card
Industry Standards	IEEE 802.3at, 802.3af, 802.3, 802.3u, 802.3ab, 802.3az Draft 2.2 Energy-Efficient Ethernet (EEE), 802.1q VLAN tagging, 802.1p Layer 2 Priority Encoding and 802.3x Full Duplex Flow Control
Chipset ID	Realtek - RTL8111E

Performance

Maximum Data Transfer Rate	2000 Mbps (Full-duplex)
Buffer Size	48 KB
Compatible Networks	10/100/1000 Mbps
Auto MDIX	Yes
Full Duplex Support	Yes
Jumbo Frame Support	9K max.
Promiscuous Mode	Yes

Connector(s)



Connector Type(s)	PCI Express x4
Internal Ports	LP4 (4 pin; Large Drive Power) SATA Power (15 pin)
External Ports	RJ-45

Software

OS Compatibility	Windows 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server 2003, 2008 R2, 2012, 2012 R2, 2016, 2019 Linux 2.4.x to 4.11.x <i>LTS Versions Only</i>
------------------	---

Special Notes / Requirements


Patents and Licenses	The following patents are licensed for this product. This list might not be all inclusive. <ul style="list-style-type: none"> • United States Patent No. 5,406,260 (expired) • United States Patent No. 6,650,622 • United States Patent No. 7,457,250 • United States Patent No. 8,155,012 • United States Patent No. 8,902,760 • United States Patent No. 8,942,107 • United States Patent No. 9,019,838 • United States Patent No. 9,049,019 • United States Patent Application No. 14/695,456 • United States Patent Application No. 14/726,940
System and Cable Requirements	Available full height (standard profile) PCI Express expansion slot Available LP4 Molex or SATA power connector

Indicators

LED Indicators	Link/ Activity (green) PoE Active (yellow)
----------------	---

Power

Output Voltage	48 DC
----------------	-------



Environmental

Operating Temperature	0C to 55C (32F to 131F)
Storage Temperature	-40C to 75C (-40F to 158F)
Humidity	10~90% RH (Non-condensing)

Physical Characteristics

Material	Steel
Product Length	9.6 in [24.3 cm]
Product Width	0.7 in [18.0 mm]
Product Height	4.7 in [12.0 cm]
Weight of Product	3.6 oz [102.0 g]

Packaging Information

Package Length	11.7 in [29.6 cm]
Package Width	7.4 in [18.8 cm]
Package Height	2.6 in [66.0 mm]
Shipping (Package) Weight	15.1 oz [428.0 g]

What's in the Box

Included in Package	PCI Express Network Card
	Driver CD
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

