



LOUROE ELECTRONICS

6955 VALJEAN AVE, VAN NUYS, CA 91406
PH: (818)994-6498 / FAX: (818)994-6458
techsupport@louroe.com / www.louroe.com

VERIFACT[®] D-V


MICROPHONE TECHNICAL DATA SHEET

DESCRIPTION


Verifact[®] D-V is a low impedance electret condenser microphone mounted to a 16 gauge stainless steel faceplate. It fits into a single gang electrical box for flush or surface mounting and is designed for areas of high vandalism.

APPLICATION

- Correctional Facilities
- Public Access Areas
- Parking Structures
- Juvenile Detention Centers
- Or anywhere vandalism is a concern




Microphone element is mounted in a recessed housing to prevent damage from foreign objects



SIDE VIEW

MODEL D-V MICROPHONE



FRONT VIEW

FEATURES

- High sensitivity to low sound pressure
- Microphone can pick up normal sounds 15' away
- 16 gauge stainless steel faceplate
- Hooded Audio port for microphone protection
- Recessed housing for microphone protection
- Tamper proof mounting screws
- May be located up to 1000' from base station
- Powered from Louroe Base Station
- Microphone preamp contains sensitivity switch for lowering gain
- Fits into single gang electrical box (not included)

IMPORTANT NOTICE

When this equipment is used as part of an audio monitoring system, the law requires that the public be given notice of AUDIO MONITORING ON THE PREMISES. A decal notice is included with each microphone shipped.



Federal Law References:
Federal Regulations, US Code, Title 18.
Crime and Criminal Procedure, Sec 2510.

WIRING REQUIREMENTS

2 Conductor **shielded** cable, 22 gauge with a 24 gauge drain wire

NOTE: Unshielded cable is not satisfactory for audio systems

West Penn 452 or equivalent



SPECIFICATIONS

■ Sensitivity	-45 dBV/Pa 1 Pa = 94 dB SPL
■ Frequency Response	50 Hz to 15 kHz
■ Output	Line Level (0 dBV, 600Ω @ 1kHz)
■ Current Drain	10mA
■ Supply Voltage	12 Vdc
■ Microphone Housing	Stainless faceplate
■ Dimensions (Faceplate)	2 3/4" W x 4 1/2" H
■ Weight	4 oz
Shipping Weight	1 lb