HP LaserJet 3x550-sheet Paper Feeder with Cabinet (J8J93A)



Overview

Help improve productivity when you increase input capacity

Automatically print on up to four different types of paper without manually loading paper for each print job.

Free up space on a desk or table when you add the HP LaserJet 3x550-sheet paper feeder with cabinet. Use the cabinet for convenient storage of extra paper or print supplies.

Help individuals and workteams save time and be more productive with additional paper capacity of 1,650 sheets.

Specifications

Dimensions (W x D x H)	661 x 667 x 479 mm
Dimensions (W x D x H)	26 x 26.2 x 18.8 in *(Without trays and covers; not extended)*
Weight	22.7 kg
Weight	50 lb
Package dimensions (W x D x H)	794 x 745 x 615 mm
Package weight	27.9 kg
UPC number	889894213617
Manufacturer Warranty	90 Day HP Dealer Exchange. Warranty and support options vary by product, country and local legal requirements. Go to hp.com/support to learn about HP award winning service and support options in your region. (wty code 3Y)
What's in the box	HP LaserJet 3x550-sheet paper feeder with cabinet; Documentation (Hardware Install Guide)

Additional specifications

Accessory type	Input
Additive metric depth	109
Additive metric height	479
Additive metric width	149
Business filter	cMPS
Cartons per layer	1
Compatibility	HP LaserJet Enterprise MFP M631dn J8J63A, HP LaserJet Enterprise Flow MFP M631h J8J64A, HP LaserJet Enterprise MFP M631z J8J65A, HP LaserJet Enterprise MFP M632h J8J70A, HP LaserJet Enterprise MFP M633fh J8J76A, HP LaserJet Managed MFP E62555dn J8J66A, HP LaserJet Managed MFP E62565hs J8J73A, HP LaserJet Managed Flow MFP E62565h J8J74A, HP LaserJet Managed Flow MFP E62565z J8J79A, HP LaserJet Managed Flow MFP E62575z J8J80A
Component type	Printer accessories
Count of layers in pallet	3
Electromagnetic compatibility	CISPR 22:2008 (International) - Class A, CISPR 32:2012 (International) - Class A, EN 55032: 2012 (EU) - Class A, EN 61000-3-2: 2014 (EU), EN 61000-3-3: 2013 (EU), EN 55024: 2010 (EU), EMC Directive 2014/30/EU, FCC CFR 47 Part 15 Class A / ICES-003, Issue 6 Class A (US/Canada), Other EMC approvals as required by individual countries
Maximum input capacity (sheets)	Up to 550 sheets for each tray
Media sizes, custom	99 x 148 to 216 x 356 mm
Media sizes, custom	3.90 x 5.83 to 8.5 x 14 in
Media types	Paper (plain, light, bond, recycled, heavy, pre-printed, pre-punched, colored, roug), mono transparency, labels, letterhead
Metric depth	667
Metric height	479
Metric width	661
Non-Operating Humidity Range	10 to 90% RH
Operating humidity range	10 to 80% RH
Operating temperature range	15 to 32.5ºC
Operating temperature range	59 to 90.5ºF
Orderable product number	J8J93A
Package dimensions (W x D x H)	31.3 x 29.3 x 24.2 in
Package weight	61.5 lb
Pallet dimensions	32.5 x 31.5 x 77.6 in
Pallet dimensions (W x D x H)	825 x 800 x 1972 mm
Pallet weight	104.2 kg

Pallet weight	229.6 lb
Quantity per pallet	3
Safety	IEC 60950-1:2005 +A1:2009 +A2:2013 (International); EN60950-1:2006 +A11:2009 +A1:2010 +A12:2011 +A2:2013 (EU); Low Voltage Directive 2014/35/EU with CE Mark (Europe). Other safety approvals as required by individual countries
Storage temperature range	-30 to 60ºC
Storage temperature range	-22 to 140ºF
Tariff numbers	8443995015 (AM-Base-HTS); 8443999000 (EU-Base-HTS); 84439990 (AP-Base-HTS)
Tray capacity	1650
UNSPSC code	44101705
Warranty	90 Day HP dealer Exchange. Warranty and support options vary by product, country and local legal requirements. Go to hp.com/support to learn about HP award winning service and support options in your region. (wty code 3Y)

Disclaimer — Copyright

© Copyright 2026 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Jan 15, 2026 11:45 AM UTC+0000