

NetWay8E

8-Port Managed PoE Switch



Altronix NetWay8E is an 8-port networked switch in a 1U rack enclosure. It provides PoE/PoE+ (up to 30W) power per port and passes data at 10/100/1000 Mbps at distances up to 100m. Features also include an integral battery charger for applications requiring backup and embedded LINQ™ Technology to monitor, control, and report power and diagnostics from anywhere.




NetWay8E

Key Features

- IEEE 802.3af (15W) and IEEE 802.3at (30W) compliant
- Eight (8) ports for cameras/edge devices over ethernet
- Speed: 10/100/1000 Mbps
- 30W maximum power per port
- Two (2) 1Gb uplink (10/100/1000Mbps)
- Port status LEDs
- Auto detection and protection of legacy non-PoE cameras/devices
- Local and/or remote access to critical information via LAN/WAN
- Real-time power diagnostics with e-mail and Windows Dashboard Alert notifications
- Event Log tracks history
- Built-in IP networked management allows for remote camera reset and monitoring
- Built-in battery charger
- UL Listed in the U.S. and Canada
- CE European Conformity
- Lifetime Warranty

Typical Application



Lifetime Warranty

NetWay8E

8-Port Managed PoE Switch



Specifications

Input

115VAC, 60Hz, 3A or 230VAC, 50Hz, 1.8A

Power

Unit provides PoE / PoE+
30W full power per port
Total power: 240W

Ethernet

Two (2) 1Gb uplink (10/100/1000Mbps)
Connectivity: RJ45, auto-crossover
Wire type: 4-pair CAT5e or better structured cable
Distance: up to 100m
Speed: 10/100/1000 BaseT, half/full duplex, auto negotiation

Indicators (LED)

Yellow and Green LED (by RJ45 jack):
IP Link status, 10/100/1000 Base-T/active
Power LED Power ON

LINQ Technology:

Remote network management allows for camera/device reset and monitoring
Provides local and/or remote access to critical information via LAN/WAN
Email and Windows Dashboard Alert notifications report real-time diagnostics
Event log tracks history

Battery Charging

Type Sealed lead acid or gel type
Failover Upon AC loss, instantaneous
Batteries are sold separately. Separate enclosure is required

Agency Listings

UL/cUL UL60950-1
 (Information Technology Equipment)
CE European Conformity

Physical and Environmental

Dimensions (H x W x D)

Enclosure:
Modular 1U standard EIA 19" rack mount chassis
1.625" x 19.125" x 8.5" (41.3mm x 486mm x 216mm)
Shipping:
20.25" x 12.5" x 5.5" (514.4mm x 317.5mm x 139.7mm)

Weight (approx.)

Product: 6.17 lb. (2.8 kg)
Shipping: 7.5 lb. (3.4 kg)

Temperature

Operating: – 20°C to 40°C (– 4°F to 104°F)
Storage: – 20°C to 70°C (– 4°F to 158°F)

Relative Humidity 85% +/- 5%

Operating Altitude: – 304.8 to 3,048m

BTU/Hr (approx.) 123 BTU/Hr.

Accessories (order separately)

Repeaters:



NetWayXT

**NetWayXT
PoE Repeater Module**
Extends data (video) for 100m



NetWayXTX

**NetWayXTX
PoE+ Repeater Module**
Extends data (video) for 100m

Battery Backup:



RE2


RE2 – Rack Mount Battery Enclosure
Accommodates up to four (4) 12VDC/7AH batteries

Lifetime Warranty

Dimensions and Drawing

Enclosure Dimensions (H x W x D approximate)

1.625" x 19.125" x 8.5" (41.3mm x 486mm x 216mm)



Lifetime Warranty

Altronix Corporation | 140 58th St | Brooklyn, NY 11220 USA

phone: +1 718.567.8181 | fax: +1 718.567.9056 | email: info@altronix.com | www.altronix.com