

DVI to DisplayPort Adapter with USB Power - 1920 x 1200

**Product ID:** DVI2DP2



This DVI to DisplayPort adapter lets you connect a DVI video source, such as your desktop computer, to your DisplayPort (DP) monitor or projector.

The DVI to DisplayPort converter is USB powered, giving you the freedom to power it using a USB port on your computer, unlike some converters that require bulky external power adapters. USB powered devices don't require an AC outlet, so you can connect a DVI computer to a DP projector or display where power outlets are limited or inaccessible, such as your boardroom or workstation.

The DVI to DP adapter also supports plug-and-play installation, so you won't need to load any drivers or software on your computer.

Using the DVI to DisplayPort adapter, you can connect a secondary monitor through a vacant DVI port on your computer. The added screen space makes it easier to multitask, so you can work more efficiently and accomplish more in less time. It's perfect for office use, or wherever you view documents, spreadsheets, or web pages across multiple screens.

With support for display resolutions up to 1920x1200 or 1080p, the DVI to DisplayPort adapter lets you take full advantage of the single-link DVI-D capabilities that are built into your computer's graphics card.

The DVI2DP2 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Connect your DVI-enabled laptop or desktop computer to a DisplayPort monitor
- Use in your office or at a hot desk to connect a secondary display

- Share your DVI computer with a DisplayPort projector in a boardroom or conference setting

## Features

- Bridge compatibility between your DVI computer and your DisplayPort monitor
- Easy setup with USB power and plug-and-play installation
- Increase productivity by using your DVI output to connect another display for multitasking
- Get high-definition video with support for resolutions up to 1920x1200

---

### Hardware

Warranty	2 Years
AV Input	DVI-D
AV Output	DisplayPort
Audio	Yes
Chipset ID	Mega Chip - STDP2600

---

### Performance

Video Revision	DisplayPort 1.2
Maximum Digital Resolutions	1920 x 1200 at 60Hz
Supported Resolutions	1920x1200
	1920x1080 (1080p)
	1680x1050 (WSXGA+)
	1600x1200
	1600x900
	1440x900
	1400x1050 (SXGA+)
	1366x768
	1360x768
	1280x1024
	1280x960



1280x800  
1280x768 (WXGA)  
1280x720p (720p)  
1280x600  
1152x864  
1024x768  
800x600 (SVGA)  
640x480 (480p)

Wide Screen Supported Yes  
MTBF 1,040,762 hours

---

**Connector(s)**

Connector A DVI-D (25 pin)  
DisplayPort (20 pin)

---

**Power**

Power Source USB-Powered

---

**Environmental**

Operating Temperature 0C to 55C (32F to 131F)  
Storage Temperature -10C to 70C (14F to 158F)  
Humidity 40%-50%RH


---

**Physical Characteristics**

Color Black  
Cable Length 10.0 in [25.4 cm]  
Product Length 6.8 in [17.2 cm]  
Product Width 5.6 in [14.3 cm]  
Product Height 1.3 in [32.0 mm]  
Weight of Product 5.3 oz [150.0 g]

---

**Packaging Information**



Package Length	10.0 in [25.4 cm]
Package Width	1.3 in [34.0 mm]
Package Height	0.7 in [17.0 mm]
Shipping (Package) Weight	2.3 oz [64.0 g]

---

**What's in the Box**

Included in Package	DVI to DisplayPort adapter
	24 in. [610 mm] USB extension cable

---

***\*Product appearance and specifications are subject to change without notice.***

