

# Product data sheet

Specifications



## Power Cord Kit (6 ea), Locking, C13 to C14, 0.6m (2ft), North America, Blue

AP8702S-NAX590

### Overview

Lead time Usually in Stock

### Main

Product or Component Type Power cord  
Input Connection Type IEC 60320 C14  
Cable length 2 ft (0.6 m)  
Number of cables 6

### Physical

Color Blue  
Height 9.4 in (24 cm)  
Width 2.8 in (7 cm)  
Depth 1.6 in (4 cm)  
Net Weight 1.5 lb(US) (0.7 kg)  
Mounting preference No preference  
Mounting Mode Not rack-mountable

### Input

Max line current 10 A  
Input current limits 10 A

### Output

Maximum Total Current Draw per Phase 10 A  
Number of power socket outlets 1 IEC 60320 C13  
Cord Length 2 ft (0.6 m)

### Conformance

Product Certifications CSA  
UL Listed

### Environmental

Ambient Air Temperature for Operation 32.0000000000...221.0000000000 °F (0...105 °C)  
Relative Humidity 20...80 %

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

<b>Operating altitude</b>	0...10000 ft
<b>Ambient Air Temperature for Storage</b>	-13.0000000000...221.0000000000 °F (-25...105 °C)
<b>Storage Relative Humidity</b>	20...80 %
<b>Storage altitude</b>	0...50000 ft (0.0000000000...15240.0000000000 m)

## Ordering and shipping details

<b>GTIN</b>	731304324560
<b>Country of origin</b>	CN

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	9.4 in (24 cm)
<b>Package 1 Width</b>	1.6 in (4 cm)
<b>Package 1 Length</b>	2.8 in (7 cm)
<b>Package 1 Weight</b>	1.5 lb(US) (0.7 kg)

## Contractual warranty

<b>Warranty</b>	2 years repair or replace
-----------------	---------------------------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)




Take-back Transparency RoHS/REACH

## Resource performance

 Take-Back Program Available

## Well-being performance

 Lead Free

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)