



Pan-Lug™ PCSB4-2-12Y Multi-Tap Mech Con, Double Sided, 4, Tin Plt Al, PK12

PCSB4-2-12Y

The PCSB4-2-12Y Multi-Tap Mechanical Lug has a flexible design that can be used as a tap, splice, or dead-end Lug. Made from high strength, extruded aluminum alloy to provide premium electrical and mechanical performance. Insulated with clear PVC to eliminate the need for taping and allow for visual inspection of the complete conductor insertion. UL Listed and CSA Certified.

Specifications

Application	Aluminum or Copper Code Conductors
Product Type	Multi-Tap Mechanical Connectors, Double Sided
Base Material	Aluminum
Minimum Aluminum Conductor Size (AWG)	14
Minimum Copper Conductor Size (AWG SOL)	14
Minimum Copper Conductor Size (AWG STR)	14
Maximum Aluminum Conductor Size (AWG)	4
Maximum Copper Conductor Size (AWG SOL)	10
Maximum Copper Conductor Size (AWG STR)	4
Number of Ports	2
Overall Height (In.)	1.25
Overall Height (mm)	31.7
Overall Length (In.)	1.23
Overall Length (mm)	31.2
Overall Width (In.)	1.5
Overall Width (mm)	38.1
Insulation Material	Clear PVC
Finish/Coating	Tin-Plated
Standards Met	UL listed and CSA certified for use up to 600V & Temperature Rated to 90°C
UL Temperature Rating (°C)	90
Maximum Voltage (V)	600

Specifications (continued)

Hex Size (In.)	1/8
Hex Size (mm)	3.17
Sub Brand	Pan-Lug™
Wire Strip Length (In.)	0.56
Wire Strip Length (mm)	14.2
Part Features	Each port pre-filled with oxide inhibiting joint compound seals out air and moisture to deter surface oxidation.

Packaging Detail

UPC	07498359754
Std. Pkg. Qty.	12
Std. Pkg. Volume (cf)	0.0365
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000