

Features

- Designed for 10Gig Ethernet applications, OM4 Rated
- MPO/8xLC connectors
- Backward compatible with legacy optical LAN
- Maximum 10Gb distance of 300 meters at 850NM
- TPU Jacket
- Ideal for Fibre Channel (SAN) application
- IEEE 802.3ae and TIA LOMM compliant
- Use with VCSEL and LED laser light sources



Product Description

This is an MPO (female) to 8xLC (male) 8-strand aqua riser-rated fiber fanout cable. An OM4 cable has a core size of 50µm microns that supports 10 Gigabit Ethernet at lengths measuring up to 550 meters, and 100 Gigabit Ethernet measuring up to 150 meters and is reverse compatible with OM3. This optical fiber, nonconductive, riser (OFNR) cable is best suited for use in interior fiber-optic applications. Our patch cables are 100% compliant for all of your networking needs. Our products are guaranteed by federal law to not affect or void OEM warranties.

Order Information

Part Number	Description
ADD-MPO-4LC1M5OM4	1m MPO (Female) to 8xLC (Male) 8-strand Aqua OM4 Fiber Fanout Cable
ADD-MPO-4LC2M5OM4	2m MPO (Female) to 8xLC (Male) 8-strand Aqua OM4 Fiber Fanout Cable
ADD-MPO-4LC5M5OM4	5m MPO (Female) to 8xLC (Male) 8-strand Aqua OM4 Fiber Fanout Cable
ADD-MPO-4LC7M5OM4	7m MPO (Female) to 8xLC (Male) 8-strand Aqua OM4 Fiber Fanout Cable
ADD-MPO-4LC10M5OM4	10m MPO (Female) to 8xLC (Male) 8-strand Aqua OM4 Fiber Fanout Cable
ADD-MPO-4LC15M5OM4	15m MPO (Female) to 8xLC (Male) 8-strand Aqua OM4 Fiber Fanout Cable
ADD-MPO-4LC20M5OM4	20m MPO (Female) to 8xLC (Male) 8-strand Aqua OM4 Fiber Fanout Cable
ADD-MPO-4LC25M5OM4	25m MPO (Female) to 8xLC (Male) 8-strand Aqua OM4 Fiber Fanout Cable
ADD-MPO-4LC30M5OM4	30m MPO (Female) to 8xLC (Male) 8-strand Aqua OM4 Fiber Fanout Cable

Applications	OM1 (MMF)		OM3 (MMF)		OM4 (MMF)		OS2 (SMF)	
	850nm	1300nm	850nm	1300nm	850nm	1310nm	1310nm	1550nm
ATM 622Mbps	300m	500m	300m	500m			2000m	
Fiber Channel 1062Mbps	300m		500m				2000m	
FDDI		2000m		2000m		2000m		
100Base-FX Ethernet		2000m		2000m		2000m		
1000Base-SX Ethernet	275m		550m		1000m			
1000Base-LX Ethernet	550m			>500m		>500m	5000m	
10GBase-LX4 Ethernet		300m					1000m	
10GBase-SR/SW Ethernet	33m		300m		550m		1000m	40000m
40GBase-SR/LR Ethernet			300m		400m			
100GBase-SR Ethernet			100m		150m			
100GBase-LR Ethernet							1000m	40000m

Type	Single-mode			Multimode
Polishing	PC		APC	PC
Insertion Loss	≤ 0.2dB (Typical ≤0.1dB)			≤ 0.3dB/0.5dB (MTRJ)
Return Loss (each channel)	≥ 45dB	≥55dB	≥60dB	≥ 35dB
Durability (500 matings)	≤ 0.2dB increase (Max)			
Operating Temperature	-40°C~+75°C			
Storage Temperature	-40°C~+75°C			

Contact Information

Founded in 1999, AddOn Networks is North America's leading provider of transceivers and high-speed cabling. With a reputation for high quality products as well as an extensive custom design portfolio, AddOn has the connectivity solution regardless of the requirement.

At AddOn, 100% of the products we ship every day are tested in the specific application for which they are intended—never batch or spec tested only. We run bandwidth, distance and IOS network tests. We have documented an impressive 0.03% failure rate over the last 10 years. To continue this rate of success we invest millions annually in our own on-site testing lab.

Corporate office:
AddOn Networks
15775 Gateway Circle
Tustin, CA 92780

Tel: 877-292-1701
Fax: 949-266-9273
Email: sales@addonnetworks.com
Email: support@addonnetworks.com
Web: <http://www.addonnetworks.com>