

Specifications

Eaton PR40

TAA-Compliant 40-Amp DC Power Supply,
13.8VDC, Precision Regulated AC-to-DC
Conversion

General specifications

PRODUCT NAME	Eaton Tripp Lite series DC power supply
CATALOG NUMBER	PR40
UPC	037332060075
PRODUCT LENGTH/DEPTH	15.9 in
PRODUCT HEIGHT	7.2 in
PRODUCT WIDTH	11.2 in
PRODUCT WEIGHT	23.48 lb

Product specifications

FEATURES	Flex Center
INPUT FREQUENCY	60 Hz
INPUT CURRENT	7.5A
OUTPUT NOMINAL VOLTAGE	13.8V (+/- 0.5VDC)
OUTPUT VOLTAGE REGULATION	0.15V Max Ripple Voltage
OVERLOAD PROTECTION	Yes
OUTPUT CONNECTOR TYPE	1/4" DC Terminal Posts support Ring and U Style connectors or bare wire.
OUTPUT VOLTAGE (VDC)	13.8VDC (+/- 0.5VDC)
RECOMMENDED ELECTRICAL SERVICE	120V 15A
SWITCHES	Lighted (Red) ON/OFF Rocker Switch - Illuminates Red when in ON position indicating DC output is available
INPUT PLUG TYPE	NEMA 5-15P
INPUT CORD LENGTH	6 ft
UNIT WEIGHT	26.455 lb
INPUT CIRCUIT BREAKERS	1x 10A inline fuse
OUTPUT CAPACITY DETAILS	40A Peak Intermittent Communication Service (ICS) 32A Continuous Duty Amps
OPERATING TEMPERATURE RANGE	32° to 104°F (0° to 40°C)
STORAGE TEMPERATURE RANGE	5° to 122°F (-15° to 50°C)
OPERATING HUMIDITY RANGE	0 to 95% humidity, non-condensing
INPUT NOMINAL VOLTAGE	120 VAC
INTERMITTENT AMPS	40

Resources

MANUALS AND USER GUIDES

[Owner's Manual for PR/TL Power](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

