




Polarity and Continuity Test	
Dielectric Voltage Withstand Test :1500V /1 Sec	
Electrical Performance (20°C)	
Item	Parameter
Conductor resistance	≤ 14.38Ω/1000m
Voltage Rating	AC 300V

WIRE MARKING WX(NO.577):
(ETL)US 3176559 SJT 3×16AWG 105℃ 300V VW-1 C(ETL) SJT 3×1.31 mm² (16AWG) FT2

WIRE MARKING PH(NO.834):
(ETL) US 5019033 SJT 3×16AWG 105℃ 300V VW-1 C(ETL) SJT 3×1.31 mm² (16AWG) FT2

		C (ETL) US General Use Cordset Indoor label 13A 125V	1	PC
		PVC 40P Black	AR	G
5		Bracket 5-15P Three Plug ABS Black UL94-V0	1	PC
4		C13Terminal Brass Natural color and Bracket, With 18-14AWG. White	1	PC
3		5-15P Non-Polar, Current Carrying End, With Riveting 18-16AWG Nickel Plating	2	PCS
2		5-15P Terminal Nickel Plated 18-16AWG	1	PC
1		SJT 16AWG 3C 105℃ Black	1	PC
NO.	PART NAME	SPECIFICATION DESCRIPTION	QTY	UNIT

PID	Cable Color	Molding Color	Length (FT)
27292	Black	Black	8ft.(96")

Pinout		
NEMA5-15P SF-31	Wire	IEC 60320 C13 (SF-82S)
E	GREEN	E
N	WHITE	N
L	BLACK	L



DESCRIPTION : Monoprice™ Power Cord - NEMA 5-15P to IEC 60320 C13, 16AWG, 13A/1625W, 3-Prong, Black, 8ft		
PID # : 27292		
DATE :	UNIT : FT / IN / MM	FILE NAME: