

# Product data sheet

Specifications



## Galaxy VS Maintenance Bypass Cabinet with Input Transformer 30-50kW 480V or 600V In, 208V Out

GVSBPIT50

### Overview

**Presentation** Maintenance bypass cabinet with transformer. The maintenance bypass isolates the UPS completely during service operations. The input transformer can be configured onsite for either 480V or 600V input and delivers 208V output. Compatible with 208V UPS.

**Lead time** Usually Ships within 2 Weeks

### Physical

<b>Color</b>	White
<b>Height</b>	58.46 in (148.5 cm)
<b>Width</b>	23.62 in (60 cm)
<b>Depth</b>	32.91 in (83.6 cm)
<b>Net Weight</b>	1168.45 lb(US) (530 kg)

### Environmental

<b>Ambient air temperature for operation</b>	32...104 °F (0...40 °C)
<b>Relative Humidity</b>	0...95 % non-condensing
<b>Ambient Air Temperature for Storage</b>	-13...131 °F (-25...55 °C)
<b>Storage Relative Humidity</b>	0...95 % non-condensing

### Ordering and shipping details

**GTIN** 731304342908

### Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	65.75 in (167 cm)
<b>Package 1 Width</b>	38.98 in (99 cm)
<b>Package 1 Length</b>	31.50 in (80 cm)
<b>Package 1 Weight</b>	1234.59 lb(US) (560 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

### Recommended replacement(s)