

USB C Multiport Adapter - USB-C to DVI-D (Digital) Video Adapter with 60W Power Delivery Passthrough Charging, GbE, USB-A - Portable USB Type-C/Thunderbolt 3 Mini Laptop Dock

Product ID: DKT30CDVPD



This USB-C multiport adapter equips your USB-C Windows or MacBook laptop with essential connections, including a DVI output, a Gigabit Ethernet port and a USB 3.0 (Type-A) port. Plus, you can power both the adapter and your laptop simultaneously, with 60 W USB Power Delivery 2.0 and a USB-C power adapter.

The versatile adapter combines the performance of three single-function adapters into one powerful solution.

- USB-C to DVI adapter
- USB-C Ethernet adapter
- USB-C to USB -A adapter

Add a second display through the DVI port. Get fast, reliable network access through the Gigabit Ethernet RJ45 port and connect a USB 3.0 peripheral device, such as a mouse or USB flash drive, all with one, simple-to-use device.

The multiport adapter's USB-C port supports 60 W USB Power Delivery 2.0, so you can power and charge your laptop while you work.

The USB Type-C multiport adapter is highly portable and features an integrated USB-C cable and USB-powered performance, so there's no need to carry a separate power adapter with you.

- Maximum compatibility - StarTech.com has a docking station to fit every operating system, laptop brand, and connectivity need

Get more done faster - More ports and more displays maximize end user connectivity and productivity

Quick installation - eliminate deployment headaches that waste time and frustrate end users

IT Grade quality - trusted by IT pros around the world for our rigorous in-house product testing, robust compliance, and lifetime multilingual technical support

The DKT30CDVPD is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Note: To ensure full adapter functionality, your laptop's USB-C port must support USB Power Delivery and DP Alt Mode.

Certifications, Reports and Compatibility

Applications

- Connect your MacBook, Ultrabook, or Chromebook to wired Gigabit internet, in locations where Wi-Fi isn't available
- Integrate the compact adapter into small work spaces in offices and home offices

Features

- **4-IN-1 USB-C MULTIPORT ADAPTER:** This USB C mini dock has DVI-D video output, Gigabit Ethernet port, 1x 5Gbps USB-A 3.0 port & 60W Power Delivery pass through charging, to work from home or in office
- **DVI DIGITAL VIDEO OUTPUT:** The DVI Digital video output on this USB Type-C multiport adapter provides a sharper digital display image and supports resolutions up to 1920x1200 / 1080p (Single Link)
- **POWERED BY LAPTOP OR EXTERNAL ADAPTER:** The dock can be USB bus powered or with a USB-C power adapter; Charge the laptop via PD Passthrough w/ your USB-C power adapter (7W for dock, 53W for charging)
- **DEVICE COMPATIBILITY:** Portable USB-C docking station w/ white housing is compatible w/ laptops and Ultrabooks incl. MacBook Pro/Air, HP EliteBook, Dell XPS, Lenovo ThinkPad X1 Carbon & Chromebooks
- **WIDE OPERATING SYSTEM COMPATIBILITY:** With automatic driver setup, this all-in-one USB-C travel dock supports major operating systems incl. Windows, macOS, Chrome OS Thunderbolt 3 Compatible

Hardware

Warranty	3 Years
4K Support	Yes
Fast-Charge Port(s)	No
Displays Supported	1
Audio	Yes
Bus Type	USB-C
Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab USB 3.0 - Backward compatible with USB 2.0 and 1.1

Chipset ID	VIA/VLI - VL813
	VIA/VLI - VL100
	Parade - PS171
	Realtek - RTL8153

Performance

Maximum Data Transfer Rate	5 Gbps (USB 3.0) <br / >2 Gbps (Ethernet; Full-Duplex)
Maximum Digital Resolutions	1920 1200 - 60 Hz (DVI)
Type and Rate	USB 3.0 - 5 Gbit/s
UASP Support	Yes
Compatible Networks	10/100/1000 Mbps
Auto MDIX	Yes
Full Duplex Support	Yes

Connector(s)

Connector Type(s)	USB Type-C (24 pin) USB 3.0 (5Gbps)
	DVI-I (29 pin)
	RJ-45
	USB Type-A (9 pin) USB 3.0 (5 Gbps)
	USB-C (24 pin) USB Power Delivery only

Software

OS Compatibility	Windows 7, 8.1, 10<br / >macOS 10.11 to 10.15, 11.0<br / >Chrome OS
------------------	---

Special Notes / Requirements

System and Cable Requirements	A host laptop with an available USB-C port (to ensure full adapter functionality, the host USB-C port must support USB Power Delivery 2.0 and DP alt mode)
	Optional: USB-C power adapter (for example, your laptop's USB-C based power adapter)



Note Not all USB-C ports support the full functionality of the USB Type-C standard. Ensure that your host USB-C port supports USB Power Delivery 2.0 and DP alt mode.

The adapter can connect to a host laptop's USB-C port that doesn't support USB Power Delivery 2.0. However, in this configuration if a power adapter is connected to the multifunction adapter, it will not pass power through to your host laptop.

USB 3.0 is also known as USB 3.1 Gen 1; this connectivity standard offers speeds up to 5Gbps.

Power

Power Source	USB-Powered
Power Delivery	60W

Environmental

Operating Temperature	0C to 45C (32F to 113F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	10%-85%RH

Physical Characteristics

Color	White
Cable Length	5.5 in [14 cm]
Product Length	3.7 in [94.0 mm]
Product Width	6.3 in [16.0 cm]
Product Height	0.7 in [17.0 mm]
Weight of Product	4.5 oz [127.0 g]

Packaging Information

Package Length	5.6 in [14.2 cm]
Package Width	6.7 in [17.0 cm]
Package Height	1.2 in [30.0 mm]
Shipping (Package) Weight	4.8 oz [135.0 g]



**What's in the
Box**

Included in Package	multiport adapter
	instruction manual

****Product appearance and specifications are subject to change without notice.***

