

6U Vertical Server Cabinet - 30 in. Deep

Product ID: RK630WALVS



This 6U vertical server cabinet offers a space-saving way to keep your network and server equipment secure. With its 30 in. depth and a weight capacity of up to 200 lb. (90.7 kg), the server rack/cabinet is designed to fit your needs. It also features an additional 2U mounting bracket positioned toward the top of the enclosure, that you can use to mount patch cables or other shallow rack-mount equipment.

Free up space

Wall-mount your equipment, even if you don't have enough space for a full-sized rack or cabinet. This low-profile server cabinet is perfect for areas where space is at a premium, such as an office. The cabinet saves space by extending only minimally from the wall and housing the length of your equipment vertically. This reduces the horizontal footprint of your equipment while still providing plenty of room for your servers, patch panels, and switches.

Keep your equipment cool and secure

To help keep your equipment secure, the vertical server cabinet/network rack features a sturdy metal design and a lock on both the door and access panel. It is also vented, providing passive cooling to help keep your equipment running at suitable temperatures.

Easy, hassle-free installation

The server rack comes fully assembled and includes all of the necessary hardware to install equipment, making installation fast and easy. The mounting holes are spaced 16 in. apart, making it suitable for mounting on almost any wall, based on common North American wall-frame stud spacing.

The RK630WALVS is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Securely mount servers and telecommunication equipment flush against the wall
- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or retail supercenter
- Install a large server anywhere in an office without a full server room, while protecting against unauthorized access
- Ideal for small and medium businesses requiring small, secure rack solutions dispersed throughout the organization

Features

- Total load capacity of 200 lb. (90.7 kg)
- Save space by mounting your server vertically to the wall
- Extra 2U of space for switches and patch cables
- Keep equipment secure with lockable door and access panel
- Comes fully assembled with all necessary hardware to install equipment for easy installation
- Provides 6U of storage space

Hardware

Warranty	5 Years
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Enclosed Cabinet
U Height	6U
Special Features	Adjustable Mounting Rails
	Lockable Top Hatch
	Ships Fully Assembled
	Wall-Mountable
Mounting Rail Profile	C-Shape
Fan Options	Two Optional Fans: 120 mm
Mounting Hole Types	Threaded Hole

Industry Standards EIA/ECA-310-E

Performance

Weight Capacity 198.9 lb [90 kg]

Physical Characteristics

Color Black

Front Door Construction Steel

Front Door Features Secure Key Lock with Reversible and Removable Front Door

Side Panel Construction Steel

Product Measurements

Internal Width 25.2 in [64.1 cm]

Internal Depth 11.3 in [28.8 cm]

Product Length 11.6 in [29.4 cm]

Product Width 25.4 in [64.5 cm]

Product Height 37.0 in [94.1 cm]

Weight of Product 72.9 lb [33.0 kg]

Maximum Mounting Depth 29.9 in [76 cm]

Packaging Information

Flat Pack (Assembly Required) No

Package Length 14.6 in [37.0 cm]

Package Width 28.3 in [72.0 cm]

Package Height 3.3 ft [1.0 m]

Shipping (Package) Weight 77.4 lb [35.0 kg]

What's in the Box



Included in Package	wall-mount rack
	door keys
	front-panel keys
	12-24 screws
	plastic washers
	instruction manual

****Product appearance and specifications are subject to change without notice.***

