

DURAFRAME SUN Letter Size 2 pk- Magnetic frame for shop window, self adhesive

Article number	400023	Sales unit quantity	1 Bag
Colour	Silver	Sales unit EAN	616528901806
Base EAN	616528901806	Packing weight (gross)	G
		Country of origin	PL



Logos and awards



Product description

- The info-frame for A4 format documents
- Ideal for glass surfaces with direct exposure to sunlight
- Present information in a high-quality and professional way.
- Quick insertion and replacement of documents via a hinged magnetic frame
- Static-cling adhesion, reposition time and time again without leaving residue
- Fields of application: For displaying A4 format documents such as opening hours and special offers in the window
- Simple, bubble-free fastening
- Residue-free removal for repeated use
- Heat resistant up to approx. 70°C
- UV-stabilised for up to 2 years
- Readability from both sides of glass thanks to 2 inserts
- Identical frame look from both sides
- For portrait and landscape formats
- A wide range of labelling style sheets is available at www.duraprint.de

400023_PDS_DURABLE_en.pdf | 2025-12-08 04:12

1/2

DURABLE Hunke & Jochheim GmbH & Co. KG
 Westfalenstraße 77 – 79 · 58636 Iserlohn · Germany
 Phone +49 (0) 2371 662 0 · Fax +49 (0) 2371 662 221
 Mail durable@ durable.de | durable.de

The statements contained herein are for informational purposes only and are true and accurate to the best of our scientific and technical knowledge. This information does not constitute a guarantee or warranty, express or implied, nor does it establish a legally valid contractual relationship. It is the customer's responsibility to determine the suitability of this product for the customer's intended use. DURABLE does not assume any liability for the customer's use of this product or the information contained herein.



DURAFRAME SUN Letter Size 2 pk- Magnetic frame for shop window, self adhesive

- External dimensions: 236 x 323 mm

Product features

Filling quantity / Filling quantity for	2 Sheet (80 g/sqm)
Format / Format for	Letter Size
Orientation Format	Portrait / landscape
Brand	DURABLE
Width of Visible Area (mm)	210
Height of Visible Area (mm)	272
Frame width (mm)	17
Attachment type	Static Cling
Surface product can be used on	Glass surfaces
Can be removed	Without residue
Frame can be opened	Yes
Read from both front and back	Yes
Frame looks identical on both sides	Yes
UV Resistance	Up to 2 years
Heat Stability	Up to approx. 70°
Anti-glare / minimises reflections	Yes
Reusable	Yes
Application area	Indoor
Label type	Download