


ULTIMATE SU650 SOLID STATE DRIVE

# FIRST SSD? GREAT TIMING!



## Ultimate SU650 3D NAND SSD

The Ultimate SU650 solid state drive implements 3D NAND Flash and a high speed controller, offering capacities up to 1TB. It delivers read/write performance up to 520/450MB/s and greater reliability than 2D NAND SSDs. The SU650 features SLC caching and advanced error correction technologies to ensure optimized data performance and integrity. For those who want to experience a clear PC upgrade, the SU650 is an excellent choice with a great cost-performance ratio.

### Features

- 3D NAND Flash for higher durability and capacity
- Wide capacity range: 120GB to 1TB
- SLC caching: enhances transmission speed
- Advanced error correction
- Tougher, quieter, and more reliable than HDDs
- Supports ADATA proprietary software – “SSD Toolbox” and “Migration Utility”

### Ordering Information

Capacity	Model Number	EAN Code
<b>120GB</b>	ASU650SS-120GT-R	4713218461155
<b>240GB</b>	ASU650SS-240GT-R	4713218461162
<b>256GB</b>	ASU650SS-256GT-R	4711085931511
<b>480GB</b>	ASU650SS-480GT-R	4713218461179
<b>512GB</b>	ASU650SS-512GT-R	4711085931528
<b>960GB</b>	ASU650SS-960GT-R	4713218461186
<b>1TB</b>	ASU650SS-1TT-R	4711085940049



# Specification

- Capacity: 120GB / 240GB / 256GB / 480GB / 512GB / 960GB / 1TB
- NAND Flash: 3D NAND
- Interface: SATA 6Gb/s (SATA III)
- Form factor: 2.5"
- MTBF: 2,000,000 hours
- Sequential read/write (Max.): R/W 520/450MB/s
- Error correction: ECC
- Terabytes Written (TBW)(Max. capacity): 600TB
- Dimensions (L x W x H): 100.45 x 69.85 x 7mm
- Weight: 47.5g / 1.67oz
- Operating temperature: 0°C-70°C
- Storage temperature: -40°C-85°C
- Shock resistance: 1500G/0.5ms
- Warranty: 3-year limited warranty
- Certifications: CE, FCC, BSMI, KC, EAC, RCM, morocco, UKCA, VCCI


# Performance

Capacity	Sequential Performance (Up to) <sup>1</sup>		TBW <sup>2</sup>
	Read (MB/s)	Write (MB/s)	
120GB	520	320	70TB
240GB	520	450	140TB
256GB	520	450	140TB
480GB	520	450	280TB
512GB	520	450	280TB
960GB	520	450	560TB
1TB	520	450	600TB

<sup>1</sup>Performance may vary based on SSD capacity, hardware test platform, test software, operating system, and other system variables

<sup>2</sup>The value is the minimum amount of terabyte written that could be reached.

# Schematics



ADATA Technology Co., Ltd  
 2F, No.258 Liancheng Rd.,  
 Zhonghe Dist., New Taipei City 235, Taiwan  
 T: +886-2-8228-0886  
 F: +886-2-8228-0887  
 E: [adata@adata.com](mailto:adata@adata.com)

CAN ICES-3 (B)/NMB-3(B)

UK	REP	APEX CE SPECIALISTS LIMITED Address: 89 Phoenix Street, Manchester, M1 4PE, UK E-mail: <a href="mailto:adata_europe@adata.com">adata_europe@adata.com</a>
EU	REP	ADATA Technology B.V. Address: Transpolderweg, Sint-Anthonis 17-27, 3112 WC, Hoofddorp, The Netherlands E-mail: <a href="mailto:adata_europe@adata.com">adata_europe@adata.com</a>

WARNING: Cancer and Reproductive Harm  
[www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

