

USB 3.0 Multiport Adapter + USB-C to USB-A Cable - HDMI & VGA - 1xA

Product ID: BNDDKT30CAHV



This USB 3.0 multiport adapter comes with a USB-C to A adapter cable, so you can use it with either a USB-A or USB-C laptop. Use it as a portable docking station to expand the connectivity of your laptop, adding HDMI and VGA ports, one USB-A port and a Gigabit Ethernet port.

This USB-A and USB-C multiport adapter combo provides a cost-effective solution for wide-scale use in organizations currently using a mix of USB-A and USB-C laptops through a combination of two products:

A USB 3.0 multiport adapter (USB3SMDOCKHV) with hideaway cable that connects to your laptop's USB-A port

A 6" (152 mm) USB-C to USB-A adapter cable (USB31CAADP) that connects to newer USB-C port equipped laptops

Enjoy flexible video output with this USB multiport adapter. You can extend your laptop's display by connecting to an HDMI (2048x1152p) or VGA (2048x1152p) monitor or projector, to give presentations or set up a workstation.

Transform your USB-A or USB-C laptop into a full-scale workstation. Connect a flash drive, mouse or other peripheral to your laptop. The multiport adapter also adds wired network connectivity with the GbE port, making it ideal in areas without Wi-Fi.

Each item in the BNDDKT30CAHV bundle is backed by its own StarTech.com warranty, ranging from 2 years to 3 years, with the added benefit of free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Transform your USB-A or USB-C laptop into a portable workstation
- Connect your laptop to an external HDMI or VGA monitor to give presentations

- Use an HDMI TV in a hotel room as a second display when traveling
- Add wired Gigabit network access to your laptop

Features

- Connect your USB-A or USB-C laptop to an HDMI or VGA monitor
- USB 3.0 multiport adapter includes a USB-C to A adapter cable
- Built-in hideaway cable for enhanced cable management and portability
- Connect a flash drive, mouse or other device with the USB 3.0 Type-A port
- Add wired network connectivity with the Gigabit Ethernet RJ45 port

Hardware

Warranty	3 Years
4K Support	No
Fast-Charge Port(s)	No
Displays Supported	1
Bus Type	USB 3.0
Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab USB 3.0 - Hub port supports USB 2.0/1.1 backward-compatibility
Chipset ID	DisplayLink - DL-3700

Performance

Maximum Data Transfer Rate	5 Gbps (USB 3.0) <br / >2 Gbps (Ethernet; Full-Duplex)
Maximum Analog Resolutions	2048x1152 (VGA)
Maximum Digital Resolutions	2048x1152 (HDMI)
Type and Rate	USB 3.0 - 5 Gbit/s
UASP Support	Yes
Compatible Networks	10/100/1000 Mbps

Auto MDIX Yes

Full Duplex Support Yes

Connector(s)

Connector Type(s) USB Type-A (9 pin) USB 3.0 (5 Gbps)
HDMI (19 pin)
VGA (15 pin, High Density D-Sub)
RJ-45
USB Type-A (9 pin) USB 3.0 (5 Gbps)

Software

OS Compatibility Windows 7, 8, 8.1, 10
macOS 10.11 - 10.12, 10.14 - 10.15, 11.0
Chrome OS v55+

Special Notes / Requirements

System and Cable Requirements USB enabled computer system with available USB 3.0 port or USB-C port (using adapter).
Note Only a single video output can be used at one time, HDMI or VGA. If a display is connected to each video output port at the same time, then the HDMI port will take priority

Indicators

LED Indicators Link (Green)
Activity (Yellow)

Power

Power Source USB-Powered

Environmental

Operating Temperature 0C to 40C (32F to 104F)
Storage Temperature -20C to 70C (-4F to 158F)
Humidity 90% RH

Physical

Characteristics

Color	Black
Material	Plastic
Cable Length	3.7 in [93 mm]
Product Length	4.9 in [12.5 cm]
Product Width	2.2 in [55.0 mm]
Product Height	0.7 in [17.0 mm]
Weight of Product	3.4 oz [97.0 g]

Packaging Information

Package Length	5.6 in [14.3 cm]
Package Width	6.6 in [16.7 cm]
Package Height	1.7 in [43.0 mm]
Shipping (Package) Weight	7.5 oz [212.0 g]

What's in the Box

Included in Package	USB 3.0 Multiport Adapter
	USB 3.1 USB-C to USB-A Adapter [6 in. / 152.4 mm]
	Driver CD
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

