

## **4X20M26252-AA**

Lenovo® 4X20M26252 Compatible USB 3.1 (C) Male to NEMA 5-15P Male 45W 20V at 2.25A Black USB-C Laptop Power Adapter and Cable.

### **Features**

- Laptop Power Adapter and Cable
- Color: Black
- 45W 15V at 3A
- Connector 1: USB 3.1 (C) Male
- Connector 2: NEMA 5-15P Male
- Tip Size: USB-C
- Compatible with intended systems

### **Product Description**

This is a Lenovo® 4X20M26252 compatible 45W 20V at 2.25A USB-C laptop power adapter specifically designed for Lenovo® notebooks. Our power adapters are 100% tested and compatible with the intended systems.

## Specifications

Parameter	Specification
<b>Input Characteristics</b>	
AC input voltage rating	100VAC to 240VAC.
AC Variation Range	95VAC to 265VAC.
AC input frequency	50/60Hz
Variation Frequency	47/63Hz
Input current	0.9A max
Efficiency	More than 86.5% (at 100V/240VAC/50Hz input with full load)
Standby power	<1W
Start-up time	≤150ms
<b>Output Characteristics</b>	
Output Power	45W
Output Voltage	15V
Output Current	2.25A
Tip Size	Type C
Turn On Delay Time	10 second Max. At 115Vac input and output Max. Load
Rise time	100ms Max. At 100Vac input and output Max. Load.
Hold Up Time	5mS Min. At 100Vac input and output Max. Load
<b>Protection Features</b>	
Short Circuit Protection	The power supply will be auto recovered when short circuit faults remove.
Over Current Protection	The Power supply will be auto recovered when faults remove.
Over Voltage Protection	The power supply will not be auto recovered until faults remove
<b>Environmental Conditions</b>	
Operating Temperature	0°C to 40°C, Full load Normal Operation
Storage Temperature	-20°C to +55°C
Relative Humidity	5% (0°C) ~90% (40°C) RH, 70Hrs, Full load Normal Operating
<b>Test Procedures</b>	
No-load output voltage test -Input power load test- No-load output ripple test- Full load open test – Full load output voltage test- Full load outour ripple test- Full load input power test- Half load output voltage test- Half load output ripple test- Over load test- Over current pretection tes -Short circuit protection test- High voltage test- Burn in test- Turn on delay time test- Rise time test- Hold time test	

## **About AddOn Networks**

In 1999, AddOn Networks entered the market with a single product. Our founders fulfilled a severe shortage for compatible, cost-effective optical transceivers that compete at the same performance levels as leading OEM manufacturers. Adhering to the idea of redefining service and product quality not previously had in the fiber optic networking industry, AddOn invested resources in solution design, production, fulfillment, and global support.

Combining one of the most extensive and stringent testing processes in the industry, an exceptional free tech support center, and a consistent roll-out of innovative technologies, AddOn has continually set industry standards of quality and reliability throughout its history.

Reliability is the cornerstone of any optical fiber network and is engrained in AddOn's DNA. It has played a key role in nurturing the long-term relationships developed over the years with customers. AddOn remains committed to exceeding industry standards with certifications from ranging from NEBS Level 3 to ISO 9001:2005 with every new development while maintaining the signature reliability of its products.

## **U.S. Headquarters**

Email: [sales@addonnetworks.com](mailto:sales@addonnetworks.com)

Telephone: +1 877.292.1701

Fax: 949.266.9273

## **Europe Headquarters**

Email: [salesupportemea@addonnetworks.com](mailto:salesupportemea@addonnetworks.com)

Telephone: +44 1285 842070