



# N3

1U Active Cooler

**PRODUCT SPECIFICATIONS**

## Table of Contents

|                                   |    |
|-----------------------------------|----|
| 1. PRODUCT DESCRIPTION .....      | 2  |
| 2. THERMAL PERFORMANCE CURVE..... | 3  |
| 3. DM DRAWING .....               | 5  |
| 4. EP DRAWING .....               | 6  |
| 5. BLOWER/FAN SPECIFICATION ..... | 7  |
| 6. ROHS CERTIFICATE .....         | 21 |

## Model Number: N3


- Intel® Ice Lake and Cooper Lake Server Processors, Socket FCLGA4189-4 / -5 (Socket P4 / P5 or P+)
- Active Cooler for 1U Server and up

## Overall Specification


|                 |   |
|-----------------|---|
| Dimension       | 113 x 80 x 27 mm                                      |
| Weight          | 410 g   |
| Fan             | 8013 Steel PWM Dual-Outlet Blower for Heat Exhausting |
| Material        | Copper1100 Heatsink with Vapor Chamber Base           |
| Mounting        | Convenient Heat Sink Screw Captive Mounting           |
| Package Carrier | PHM Package Carrier is included                       |
| Thermal Grease  | Shin-Etsu 7762 or Equivalent                          |
| TDP             | Support CPU Power up to 205 Watts Heat Dissipation    |

## Fan Specification


|                       |   |
|-----------------------|---|
| Model Number          | DB128013BU-PWM ( Dual-Outlet Type )   |
| Dimension             | Ø80 x 13 mm   |
| Bearing               | Double Ball   |
| Rated Voltage         | 12V   |
| Rated Speed           | At Duty Cycle 0~20%: 2000 ± 200 RPM<br>At Duty Cycle 50%: 4900 ±10% RPM<br>At Duty Cycle 100%: 8600 ± 10% RPM                     |
| Input Power           | At Duty Cycle 0~20%: 1.08 W<br>At Duty Cycle 50%: 4.7 W<br>At Duty Cycle 100%: 23.45 W  |
| Maximum Airflow       | At Duty Cycle 0~20%: 5.59 CFM<br>At Duty Cycle 50%: 14.76 CFM<br>At Duty Cycle 100%: 26.25 CFM                                    |
| Rated Static Pressure | At Duty Cycle 0~20%: 3.69 mm-H2O<br>At Duty Cycle 50%: 25.28 mm-H2O<br>At Duty Cycle 100%: 89.90 mm-H2O                           |
| Acoustical Noise      | At Duty Cycle 0~20%: 23.3 dBA<br>At Duty Cycle 50%: 43.5 dBA<br>At Duty Cycle 100%: 62.2 dBA                                      |
| Lead Wire Pin Out     | Pin#1- Black(-)<br>Pin#2- Black(+)<br>Pin#3- Black(Tachometer/ Signal Output)<br>Pin#4- Black(PWM)<br>Lead Wire Pin Out Diagram : |

**N3 | Socket LGA 4189**


## Performance Chart: Active Cooler N3 Thermal Resistance Cooling Performance vs. Airflow



## Cooling Performance vs. Fan Speed





**CONFIDENTIAL DOCUMENT**

THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO DYNATRON CORPORATION AND DYNAEON INDUSTRIAL CO., LTD. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DRAWING IS EXPRESSLY PROHIBITED EXCEPT AS DYNATRON CORPORATION AND DYNAEON INDUSTRIAL CO., LTD. MAY OTHERWISE AGREE TO IN WRITING.

| REV# | DESCRIPTION                       | CHECKER | DATE       |
|------|-----------------------------------|---------|------------|
| 0.0  | INITIAL RELEASE                   | LANG    | 11/12/2019 |
| 1.0  | CHANGE BLOWER TO DUAL-OUTLET TYPE | LANG    | 05/21/2020 |

**ASSEMBLY PARTS**


**WHOLE SET OF HEATSINK**








**NOTES:**

1. THE FIGURE IS FOR REFERENCE ONLY, AND NOT FOR SCALE
2. OVERALL DIMENSION : 113 x 80 x 27 mm
3. OVERALL WEIGHT : 410 g

| ITEM# | DESCRIPTION   | MATERIAL   | QTY. |
|-------|---|--|------|
| 8     | THERMAL GREASE, PRE-PRINT                               | SHIN-ETSU 7762   | 1    |
| 7     | PHM PACKAGE CARRIER, FOR SOCKET <b>P4</b>               | PLASTIC  | 1    |
| 6     | HEATSINK, STACKED FIN                                   | COPPER 1100, VC BASE<br>SK7 STIFFENER<br>COPPER 1100 FIN | 1    |
| 5     | ANTI-TILT ROTATING WIRE ASSEMBLY SET                    | PLASTIC NUT AND CAPTIVATION<br>STEEL ROTATING WIRE       | 4    |
| 4     | SCREW, BLOWER MOUNTING                                  | STEEL  | 4    |
| 3     | BLOWER COVER  | SPCC   | 1    |
| 2     | SCREW, BLOWER COVER MOUNTING                            | STEEL  | 4    |
| 1     | BLOWER, DB128013BM - PWM<br>( DUAL - OUTLET, 8500 RPM ) | STEEL FRAME  | 1    |

| DATE       | NAME | DYNATRON CORPORATION   |            |
|------------|------|--|------------|
| 05/21/2020 | Engr | <br><b>1U Active Cooler N3</b><br>BOM & Exploded Assembly Drawing |            |
| 05/21/2020 | LANG |  |            |
|            |      |  |            |
|            |      |  |            |
| COMMENTS:  |      | DWG. No:   | REV        |
|            |      | <b>DYN-EP-N3</b>   | <b>1.0</b> |

| REV# | DESCRIPTION                       | CHECKER | DATE       |
|------|-----------------------------------|---------|------------|
| 0.0  | Initial Release                   | LANG    | 07/03/2019 |
| 1.0  | Change Blower to Dual-Outlet Type | LANG    | 05/21/2020 |



|               | NAME | DATE       |
|---------------|------|------------|
| DRAWN BY      | engr | 05/21/2020 |
| CHECKED BY    | LANG | 05/21/2020 |
| ENG. APPROVED |      |            |
| MFG. APPROVED | -    | -          |



**DYNATRON CORPORATION**

TOP MOTOR

TITLE: **1U Active Cooler N3**  
Overall Dimension Drawing

|       |    |
|-------|----|
| VIEW  |    |
| UNITS | MM |

DWG. No:

**DYN-DM-N3**

REV.  
**1.0**

**CONFIDENTIAL DOCUMENT**

THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO DYNATRON CORPORATION AND DYNAEON INDUSTRIAL CO., LTD. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DRAWING IS EXPRESSLY PROHIBITED EXCEPT AS DYNATRON CORPORATION AND DYNAEON INDUSTRIAL CO., LTD. MAY OTHERWISE AGREE TO IN WRITING.



# DYNATRON CORPORATION

TOP MOTOR TECHNOLOGY (HUIZHOU) CO, LTD

## Specification for Approval

|   |   |   |
|---|---|---|
| Customer:   |   |   |
| Model Number:   | DF128013BU (dual-outlet, 80*80*13mm)  |   |
| Part Number:  |   |   |
| Issued Date:  | Thursday, May 20, 2020  |   |
| Version:  | A   |   |
| Customer Approval   |   |   |
| Approval:   | Check:  |   |
|   |   |   |
| Corporate Headquarters<br><b>Dynatron Corporation</b><br>33200 Western Avenue<br>Union City, CA 94587<br>U.S.A.<br>Tel: 510-498-8888<br>Fax: 510-498-8488 | <i>Taipei Office</i><br><i>(Taiwan, R.O.C.)</i><br>8F, No. 35, Lane:221<br>Gang Cian. Road, Taipei,<br>Taiwan, R.O.C.<br>Tel: 886-2-27995799 (Rep.)<br>Fax: 886-2-2799-9577 | Manufactory:<br><b>TOP MOTOR</b><br><b>TECHNOLOGY(HUI</b><br><b>ZHOU)CO,LTD</b><br>Baishi Village, QiuchangTown,<br>Huiyang<br>Dist, HuizhouCity, Guangdong<br>Province, P.R.China<br>Tel: 86-752-822-8000 (Rep.)<br>Fax: 86-752-822-8999 |
| Approval:   | Tester:   | Handler:  |
| Glen Gao  | Conrad Yu   | Simon Wang  |



# DYNATRON CORPORATION

*TOP MOTOR TECHNOLOGY (HUIZHOU) CO, LTD*

|    | CONTENTS  | Page  |
|----|---|-------|
| 1. | SCOPE   | 3     |
| 2. | ELECTRICAL CHARACTERISTICS                        | 3     |
| 3. | MECHANICAL CHARACTERISTICS                        | 4     |
| 4. | ENVIRONMENTAL                                     | 4     |
| 5. | PROTECTION  | 5     |
| 6. | ATTACHMENTS                                       |       |
|    | 6.1. Product Dimension                            | 6     |
|    | 6.2. Frequency Generator Output.                  | 7     |
|    | 6.3. TUV Certificate                              | 8     |
|    | 6.4. UL Certificate                               | 9-12  |
|    | 6.5. Electrical specifications for PWM production | 13-14 |



# DYNATRON CORPORATION

TOP MOTOR

TOP MOTOR TECHNOLOGY (HUIZHOU) CO, LTD

## 1. SCOPE

This specification defines the electrical and mechanical characteristics of the  AC /  DC Brush less ( Liquid State Ball /  2-Balls Bearing )axial flow fan, which is carefully designed and manufactured for your special needs by Dynatron Corporation.

## 2. ELECTRICAL CHARACTERISTICS

| Items |   | Description  |  |   |
|-------|---|--|--|---|
| 1.    | Rated Voltage   | DC 12 V  |  |   |
| 2.    | Operating Voltage   | 10.8V~13.2V  |  |   |
| 3.    | PWM Frequency 25KHz   | Duty Cycle<br>D=0~20%  | Duty Cycle<br>D=50%                                      | Duty Cycle<br>D=100%                                    |
| 4.    | Start Voltage   | 7V   |  |   |
| 5.    | Air Flow – At rated voltage zero static pressure (minimal value)      | 0.158m <sup>3</sup> / min<br>(5.59CFM)   | 0.418m <sup>3</sup> / min<br>(14.76CFM)                  | 0.743m <sup>3</sup> / min<br>(26.25CFM)                 |
| 6.    | Static Pressure – At rated voltage At zero air flow                   | 3.69mm-H <sub>2</sub> O<br>(0.145inch-H <sub>2</sub> O)                          | 25.28mm-H <sub>2</sub> O<br>(0.995inch-H <sub>2</sub> O) | 89.8mm-H <sub>2</sub> O<br>(3.535inch-H <sub>2</sub> O) |
| 7.    | Input Current (Max.)  | 0.09A  | 0.39A  | 1.95A   |
| 8.    | Speed   | 2000RPM±200  | 4900RPM±10%  | 8600RPM±10%   |
| 9.    | Acoustical Noise  | 23.3dBA  | 43.5dBA  | 62.2dBA   |
| 10.   | Input Power   | 1.08W  | 4.68W  | 23.45W  |
| 11.   | Insulation Resistance – Between Frame and Terminal                    | 10 M ohm at DC 500 V   |  |   |
| 12.   | Dielectric Strength – Between Frame and Terminal                      | 5 mA (Max.)<br>@ AC 500 V 60 Hz 1 min.   |  |   |
| 13.   | Life – Continuous operating under normal temperature (40°C or 104 °F) | 70,000 hours   |  |   |
| 14.   | Rotation  | Anticlockwise Air Discharged   |  |   |
| 15.   | Lead Wires  | UL 1061, awg 26 or Equivalent<br>“-”: Black; “+”: Yellow; “S”: Green. “PWM”:Blue |  |   |



# DYNATRON CORPORATION

TOP MOTOR TECHNOLOGY (HUIZHOU) CO, LTD

## 3. MECHANICAL CHARACTERISTICS

| Items |                | Description            |
|-------|----------------|------------------------|
| 1.    | Dimension      | Display as Drawing     |
| 2.    | Frame          | Aluminum               |
| 3.    | Impeller       | PBT UL94V-0 (Black GP) |
| 4.    | Bearing System | Two ball Bearing       |
| 5.    | Weight         | 57±10grams             |

## 4. ENVIRONMENTAL

| Items |                       | Description   |
|-------|-----------------------|---|
| 1.    | Operating Temperature | - 10 °C ~ + 65 °C (65 %RH)  |
| 2.    | Storage Temperature   | - 30 °C ~ + 70 °C (65 %RH)  |
| 3.    | Vibration Test        | Displacement Amplitude:<br>0.75mm(Equivalent 10G)<br>Frequency Range: 10Hz<->55Hz/30SEC.<br>Linear Scanning 120 Cycle<br>Endurance Timer Per Axis: 30Min.<br>Orientation:X,Y,Z. |
| 4.    | Drop Test             | Motor withstands one free body drop from 30 cm in high onto 10 mm thickness of wooden board for each of the three faces in minimum packing condition.                           |
| 5.    | Acoustic Noise        | 0.9/8.5/23.5dBA – Curve (Max1.4/9.0/24.0)<br>Measuring Condition – Under rated voltage in semi-anechoic chamber equipment sound level meter. (Figure A.)                        |




Figure A – Noise Level is measure at rated voltage in anechoic chamber in free air as above.

## 5. PROTECTION



# DYNATRON CORPORATION

*TOP MOTOR TECHNOLOGY (HUIZHOU) CO, LTD*

| Items |                     | Description   |
|-------|---------------------|---|
| 1.    | Polarity Protection | For polarity error connection to power, the circuit withstands reversed connection between positive and negative leads. |

## 6. ATTACHMENTS


- 6.1. Product Dimension
- 6.2. Frequency Generator Output
- 6.3. TUV Certificate
- 6.4. UL Certificate
- 6.5. Electrical Specifications for pwm production



# DYNATRON CORPORATION

TOP MOTOR TECHNOLOGY (HUIZHOU) CO, LTD

## 6.1. Product Dimension






# DYNATRON CORPORATION

## TOP MOTOR TECHNOLOGY (HUIZHOU) CO, LTD

### 6.2. Frequency Generator Output

#### FREQUENCY GENERATOR O/P:

Frequency generator function is activated by an internal IC for customer's application.  
Electrical schematic:




#### CUSTOMER'S CIRCUIT

$V_{cc}$  = From +5 To +28 VDC (Generally using +12 or +24 VDC)

$I_c$  = 5 mA max.

$R = V/I$  (Output "R" value calculation)

#### ● SUPPLY A WAVEFORM:



$N = R.P.M.$  (Rotation speed will be different for various models  
L/M/H/HH/VH/SH)

$TS = 60/N$  (Sec)

\* Voltage level after blade locked


#### ● OUTPUT LEVEL:

High =  $V_{cc}$  10%

Low = 0~0.5V

$I_c$  = 5 mA max.

#### ● APPLICATION:



#### ● FUNCTIONS:

- By means of waveform & customer's design, schematic can reach alarm function, either in the form of buzzing or LED flashing. Adjust rotation speed.
- When power supply output voltage level decreases, it will result in the lowering of fan rotation speed. The irregular situation will be controlled by using FG. O/P through P/S circuit to increase the output voltage and result in a stable rotation speed.



# DYNATRON CORPORATION

## TOP MOTOR TECHNOLOGY (HUIZHOU) CO, LTD

### 6.3. TUV Certificate

Zertifikat

Certificate



Zertifikat Nr. Certificate No. R 50064443  
Blatt Page 0002

Ihr Zeichen Client Reference PC/DTI  
Unser Zeichen Our Reference ZTW1-TCC- 10013649 002  
Ausstellungsdatum Date of Issue 11.11.2005 (day/mo/yr)

Genehmigungsinhaber License Holder Dynaeon Industrial Co., Ltd.  
1st Fl., No. 362, Tanan Rd.  
Taipei 111  
Taiwan, R.O.C.  
Fertigungsstätte Manufacturing Plant Dynaeon Ind. Co., Ltd.  
Ta-Li Management Zone  
Ching-Hsi, Dongguan  
P.R. China

Prüfzeichen Test Mark Bauart Geprüft nach Tested acc. to  
EN 60950-1:2001+A11



Zertifiziertes Produkt (Geräteidentifikation) Ventilator (DC Fan)  
Certified Product (Product Identification) wie Blatt (as page) 01  
Lizenzentgelte - Einheit License Fee - Unit

Ergänzung (Addition)

Bezeichnung : DF(X1)(X2)(X3)(X4)(X5)ZZZZ-(X6)  
(Type Designation)  
(X1) steht für (stands for) : 05, 12, 24  
(X2) steht für (stands for) : 40, 50, 60, 70, 80  
(X3) steht für (stands for) : 10, 15, 20  
(X4) steht für (stands for) : S, B, P, Q  
(X5) steht für (stands for) : U, H, M, L, E  
Z steht für (stands for) : A-Z, 0-9 oder freibleibend (or blank)  
(X6) steht für (stands for) : A, B  
Nennspannung : DC 5V (X1 = 05); DC 12V (X1 = 12)  
(Rated Voltage) DC 24V (X1 = 24)  
Nennstrom : siehe Aufbau-Übersicht  
(Rated Current) (see constructional dataform)



ANLAGE (Appendix): 1.1

Dem Zertifikat liegt unsere Prüf- und Zertifizierungsordnung zugrunde.  
Das Produkt entspricht den o.g. Anforderungen, die Herstellung wird überwacht.  
This certificate is based on our Testing and Certification Regulation. The product fulfills above-mentioned-requirements, the production is subject to surveillance.

TÜV Rheinland Product Safety GmbH, Am Grauen Stein, D-51105 Köln

Tel.:(+49/221)8 06 - 13 71 Fax:(+49/221)8 06 - 39 35 e-mail: Althoff@de.tuv.com

Zertifizierungsstelle

F. Stöckel  
Dipl.-Ing. F. Stöckel



# DYNATRON CORPORATION

TOP MOTOR TECHNOLOGY (HUIZHOU) CO, LTD

## 6.4. UL Certificate



ONLINE CERTIFICATIONS DIRECTORY

### GPWV2.E157868 Fans, Electric - Component

[Page Bottom](#)

### Fans, Electric - Component

[See General Information for Fans, Electric - Component](#)

**DYNAEON INDUSTRIAL CO LTD**  
8TH FL 35 LANE 221 GANGCIAN RD  
NEIHU DIST  
TAIPEI, 114 TAIWAN

E157868

**DC fans**, Models D(F)1206(Z)(Y1)(X1), D(F)1207(Z)(Y1)(X1), where (F) may be F or C, (Z) may be SH, BH, BA, SM, BM, BB, SL, BL, BC, SD, BE, BF, SG, BI, BJ, SK, BN, BO, SP, BQ, BR, SS, BT, BU, SV, BW, BX, SY, BY or BZ, (Y1) may be "-", 0 through 9 or A through Z, (X1) may be 0 through 9 or A through Z.

Models DF248015(S)(X)(Y)(Z)(W), DF488015(S)(X)(Y)(Z)(W), where (S) may be S, B or P, (X) may be U, H, M or L, (Y) and (Z) may be any alphanumeric character, blank, "-" or any symbol, (W) may be seven any alphanumeric character, blank, "-" or any symbol.

Models DF121225(A)(B)(C), DF121225(A)E(C), DF241225(A)(B)(C), DF128015(A)U(C), DF128015(A)(B)(C), DF128025(A)U(C), DF128025(A)(B)(C), DF128025(A)E(C), DF248025(A)U(C), DF248025(A)(B)(C), DF129225(A)(B)(C), DF129225(A)E(C), DF249225(A)U(C), DF249225(A)(B)(C), DF126010(A)(B)(C), DF246025(A)U(C), DF246025(A)(B)(C), DF126025(A)U(C), DF126025(A)(B)(C), DF126025(A)E(C), DB126015BU(C), DB126015B(B)(C), DF123010(A)(B)(C), DF053010(A)(B)(C), DF127015(A)U(C), DF127015(A)(B)(C), DF245010(A)(B)(C), where (A) may be S, B, P or Q, (B) may be H, M or L, (C) may be xxxxxxxx, where x may be A through Z, 0 through 9, "-" or blank.

Models DF122510(X)(Y2)(Z)-(M), DF124020(X)(Y2)(Z)-(M), DF244020(X)(Y1)(Z)-(M), DF126025(X)(Y3)(Z)-(M), DF246025(X)(Y3)(Z)-(M), DF121225(X)(Y1)(Z)-(M), DF124028(X)(Y3)(Z)-(M), where (X) may be S, B, P, Q, (Y1) may be H, M or L, (Y2) may be U, H, M or L, (Y3) may be U, H, M, L or E, (Z) is alphanumeric combination of five digits and/or alphabets, may be A through Z, 0 through 9 or blank, (M) may be A or B.

Models DF054010(X)(Y2)(Z1)(Z2)-A, DF054010(X)L(Z1)(Z2)-B, DF124010(X)(Y2)(Z1)(Z2)-A, DF124010(X)L(Z1)(Z2)-B, DF244010(X)(Y2)(Z1)(Z2)-A, DF125015(X)(Y1)(Z1)(Z2)-A, DF125020(X)(Y3)(Z1)(Z2)-A, DF126015(X)(Y1)(Z1)(Z2)-A, DF246015(X)M(Z1)(Z2)-A, DF246015(X)L(Z1)(Z2)-A, DF128020(X)(Y1)(Z1)(Z2)-A, DF128020(X)L(Z1)(Z2)-B, DB127015(X)(Y2)(Z)-A series, where (X) may be S, B, P, Q, (Y1) may be H, M or L, (Y2) may be U, H, M or L, (Y3) may be H, M, L or E, (Z1) may be blank or 3, (Z2) is alphanumeric combination of four digits and/or alphabets, may be A through Z, 0 through 9 or blank, (Z) is alphanumeric combination of five digits and/or alphabets, may be A through Z, 0 through 9 or blank.

Models DF125010(X)(Y)(Z)-A, DF126020(X)(Y)(Z)-A, DF246020(X)(Y)(Z)-A, DF121525(X)(Y1)(Z)-A, DF121525(X)(Y2)(Z)-B series, Where (X) may be S, B, P or Q, (Y) may be H, M or L, (Y1) may be U, H or M, (Y2) may be L or E, (Z) is alphanumeric combination of five digits and/or alphabets, may be A through Z, 0 through 9 or blank.

Models DF128025(X)(a)(Y)-A, DF121225(X)(b)(Y)-C, DF121225(X)E(Y)-C, DF127720(X)(a)(Y)-A, DF121425(X)(c)(Y)-A, DF126010(X)E(Y)-A series, where (X) may be S, B, P, Q, (a) may be H, M, L or E, (b) may be M or L, (c) may be U, H, M, L or E, (Y) is alphanumeric combination of five digits and/or alphabets, may be A through Z, 0 through 9 or blank.

Models DF054010(X)(Y1)(Z1)(Z2)-C, DF124010(X)(Y2)(Z1)(Z2)-C, DF244010(X)(Y2)(Z1)(Z2)-C, DF124020BU(Z1)(Z2)-C, DF124020(X)(Y1)(Z1)(Z2)-C, DF124028BU(Z1)(Z2)-C, DF124028(X)(Y1)(Z1)(Z2)-C, DF126025BU(Z1)(Z2)-C, DF126025(X)(Y1)(Z1)(Z2)-C, DF127015BU(Z1)(Z2)-A, DF127015(X)(Y1)(Z1)(Z2)-A, DF128025BU(Z1)(Z2)-B, DF128025(X)(Y1)(Z1)(Z2)-B, DF129225BU(Z1)(Z2)-A, DF129225(X)(Y1)(Z1)(Z2)-A, DF121225BU(Z1)(Z2)-D, DF121225(X)(Y1)(Z1)(Z2)-D, DF121425(X)(Y1)(Z1)(Z2)-B, DB127015BU(Z1)(Z2)-B, DB127015(X)(Y1)(Z1)(Z2)-B, DB058015(X)(Y3)(Z1)(Z2)-A, where (X) may be S, B, P or Q, where (Y1) may be H, M, L or E, where (Y2) may be U, H, M, L or E, where (Y3) may be M or L, where (Z1) may be blank or 3, where (Z2) may be is alphanumeric combination of four digits and/or alphabets, may be A through Z, 0 through 9 or blank.

Models DB128015(X)(Y1)(Z)-(A), DF128038(X)(Y1)(Z)-(A), DB121225(X)(Y2)(Z)-(A), DF054010(X)(Y2)(Z)-(D), DF124010(X)(Y3)(Z)-(D), DF244010(X)(Y4)(Z)-(D), DF125010(X)(Y2)(Z)-(B), DF126010(X)(Y5)(Z)-(B) series, where (X) may be S, B, P, Q, (Y1) may be U, H, M, L or E, (Y2) may be H, M or L, (Y3) may be U, M, L or E, (Y4) may be U, H, M or L, (Y5) may be H, M, L or E, (Z) is alphanumeric combination of five digits and/or alphabets, may be A through Z, 0 through 9 or blank.

**Electric fans**, Models DC0504, -1204, -1205, -1206, DF1204, -1208, -2408, -0504, -0505, -1205, -2406 followed by "S" or



# DYNATRON CORPORATION

## TOP MOTOR TECHNOLOGY (HUIZHOU) CO, LTD

"B", followed by two alphanumeric characters.

**Low voltage fans**, Models DB1206, DF1209, -1212, -2409, DH1204 followed by B or S, followed by two alphanumeric characters.



Marking: Company name or trademark **TOP MOTOR**, model designation and Recognized Component Mark for Canada,



Last Updated on 2008-02-18

---

[Questions?](#)

[Notice of Disclaimer](#)

[Page Top](#)

Copyright © 2009 Underwriters Laboratories Inc.®

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2009 Underwriters Laboratories Inc.®"


An independent organization working for a safer world with integrity, precision and knowledge.





# DYNATRON CORPORATION

## TOP MOTOR TECHNOLOGY (HUIZHOU) CO, LTD



**GPWV8.E157868**

**Fans, Electric Certified for Canada - Component**

[Page Bottom](#)

**Fans, Electric Certified for Canada - Component**

[See General Information for Fans, Electric Certified for Canada - Component](#)

**DYNAEON INDUSTRIAL CO LTD**  
8TH FL 35 LANE 221 GANGCIAN RD  
NEIHU DIST  
TAIPEI, 114 TAIWAN

E157868

**DC fans**, Models D(F)1206(Z)(Y1)(X1), D(F)1207(Z)(Y1)(X1), where (F) may be F or C, (Z) may be SH, BH, BA, SM, BM, BB, SL, BL, BC, SD, BE, BF, SG, BI, BJ, SK, BN, BO, SP, BQ, BR, SS, BT, BU, SV, BW, BX, SY, BY or BZ, (Y1) may be "-", 0 through 9 or A through Z, (X1) may be 0 through 9 or A through Z.

Models DF248015(S)(X)(Y)(Z)(W), DF488015(S)(X)(Y)(Z)(W), where (S) may be S, B or P, (X) may be U, H, M or L, (Y) and (Z) may be any alphanumeric character, blank, "-" or any symbol, (W) may be seven any alphanumeric character, blank, "-" or any symbol.

Models DF121225(A)(B)(C), DF121225(A)E(C), DF241225(A)(B)(C), DF128015(A)U(C), DF128015(A)(B)(C), DF128025(A)U(C), DF128025(A)(B)(C), DF128025(A)E(C), DF248025(A)U(C), DF248025(A)(B)(C), DF129225(A)(B)(C), DF129225(A)E(C), DF249225(A)U(C), DF249225(A)(B)(C), DF126010(A)(B)(C), DF246025(A)U(C), DF246025(A)(B)(C), DF126025(A)U(C), DF126025(A)(B)(C), DF126025(A)E(C), DB126015BU(C), DB126015B(B)(C), DF123010(A)(B)(C), DF053010(A)(B)(C), DF127015(A)U(C), DF127015(A)(B)(C), DF245010(A)(B)(C), where (A) may be S, B, P or Q, (B) may be H, M or L, (C) may be xxxxxxxx, where x may be A through Z, 0 through 9, "-" or blank.

Models DF122510(X)(Y2)(Z)-(M), DF124020(X)(Y2)(Z)-(M), DF244020(X)(Y1)(Z)-(M), DF126025(X)(Y3)(Z)-(M), DF246025(X)(Y3)(Z)-(M), DF121225(X)(Y1)(Z)-(M), DF124028(X)(Y3)(Z)-(M), where (X) may be S, B, P, Q, (Y1) may be H, M or L, (Y2) may be U, H, M or L, (Y3) may be U, H, M, L or E, (Z) is alphanumeric combination of five digits and/or alphabets, may be A through Z, 0 through 9 or blank, (M) may be A or B.

Models DF054010(X)(Y2)(Z1)(Z2)-A, DF054010(X)L(Z1)(Z2)-B, DF124010(X)(Y2)(Z1)(Z2)-A, DF124010(X)L(Z1)(Z2)-B, DF244010(X)(Y2)(Z1)(Z2)-A, DF125015(X)(Y1)(Z1)(Z2)-A, DF125020(X)(Y3)(Z1)(Z2)-A, DF126015(X)(Y1)(Z1)(Z2)-A, DF246015(X)M(Z1)(Z2)-A, DF246015(X)L(Z1)(Z2)-A, DF128020(X)(Y1)(Z1)(Z2)-A, DF128020(X)L(Z1)(Z2)-B, DB127015(X)(Y2)(Z)-A series, where (X) may be S, B, P, Q, (Y1) may be H, M or L, (Y2) may be U, H, M or L, (Y3) may be H, M, L or E, (Z1) may be blank or 3, (Z2) is alphanumeric combination of four digits and/or alphabets, may be A through Z, 0 through 9 or blank, (Z) is alphanumeric combination of five digits and/or alphabets, may be A through Z, 0 through 9 or blank.

Models DF125010(X)(Y)(Z)-A, DF126020(X)(Y)(Z)-A, DF246020(X)(Y)(Z)-A, DF121525(X)(Y1)(Z)-A, DF121525(X)(Y2)(Z)-B series, Where (X) may be S, B, P or Q, (Y) may be H, M or L, (Y1) may be U, H or M, (Y2) may be L or E, (Z) is alphanumeric combination of five digits and/or alphabets, may be A through Z, 0 through 9 or blank.

Models DF128025(X)(a)(Y)-A, DF121225(X)(b)(Y)-C, DF121225(X)E(Y)-C, DF127720(X)(a)(Y)-A, DF121425(X)(c)(Y)-A, DF126010(X)E(Y)-A series, where (X) may be S, B, P, Q, (a) may be H, M, L or E, (b) may be M or L, (c) may be U, H, M, L or E, (Y) is alphanumeric combination of five digits and/or alphabets, may be A through Z, 0 through 9 or blank.

Models DF054010(X)(Y1)(Z1)(Z2)-C, DF124010(X)(Y2)(Z1)(Z2)-C, DF244010(X)(Y2)(Z1)(Z2)-C, DF124020BU(Z1)(Z2)-C, DF124020(X)(Y1)(Z1)(Z2)-C, DF124028BU(Z1)(Z2)-C, DF124028(X)(Y1)(Z1)(Z2)-C, DF126025BU(Z1)(Z2)-C, DF126025(X)(Y1)(Z1)(Z2)-C, DF127015BU(Z1)(Z2)-A, DF127015(X)(Y1)(Z1)(Z2)-A, DF128025BU(Z1)(Z2)-B, DF128025(X)(Y1)(Z1)(Z2)-B, DF129225BU(Z1)(Z2)-A, DF129225(X)(Y1)(Z1)(Z2)-A, DF121225BU(Z1)(Z2)-D, DF121225(X)(Y1)(Z1)(Z2)-D, DF121425(X)(Y1)(Z1)(Z2)-B, DB127015BU(Z1)(Z2)-B, DB127015(X)(Y1)(Z1)(Z2)-B, DB058015(X)(Y3)(Z1)(Z2)-A, where (X) may be S, B, P or Q, where (Y1) may be H, M, L or E, where (Y2) may be U, H, M, L or E, where (Y3) may be M or L, where (Z1) may be blank or 3, where (Z2) may be is alphanumeric combination of four digits and/or alphabets, may be A through Z, 0 through 9 or blank.

Models DB128015(X)(Y1)-(Z)-A, DF128038(X)(Y1)-(Z)-A, DB121225(X)(Y2)-(Z)-A, DF054010(X)(Y2)-(Z)-D, DF124010(X)(Y3)-(Z)-D, DF244010(X)(Y4)-(Z)-D, DF125010(X)(Y2)-(Z)-B, DF126010(X)(Y5)-(Z)-B series, where (X) may be S, B, P, Q, (Y1) may be U, H, M, L or E, (Y2) may be H, M or L, (Y3) may be U, M, L or E, (Y4) may be U, H, M or L, (Y5) may be H, M, L or E, (Z) is alphanumeric combination of five digits and/or alphabets, may be A through Z, 0 through 9 or blank.

**Electric fans**, Models DC0504, -1204, -1205, -1206, DF0504, -0505, -1204, -1205, -1208, -2406, -2408 followed by "S" or



# DYNATRON CORPORATION

## TOP MOTOR TECHNOLOGY (HUIZHOU) CO, LTD

"B", followed by two alphanumeric characters.

**Low voltage fans**, Models DB1206, DF1209, -1212, -2409, DH1204 followed by B or S, followed by two alphanumeric characters.



Marking: Company name or trademark **TOP MOTOR**, model designation and Recognized Component Mark for Canada,



Last Updated on 2008-02-18

[Questions?](#)

[Notice of Disclaimer](#)

[Page Top](#)

[Copyright © 2009 Underwriters Laboratories Inc.®](#)

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Listed and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Designs and/or Listings (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from Underwriters Laboratories Inc." must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "Copyright © 2009 Underwriters Laboratories Inc.®"

*An independent organization working for a safer world with integrity, precision and knowledge.*





# DYNATRON CORPORATION

TOP MOTOR TECHNOLOGY (HUIZHOU) CO, LTD

## 6.5. Electrical Specifications for pwm production

USA Dynatron Corp.

### Electrical Specifications for PWM production

#### Voltage

Fan operating voltage shall be within the range 12V $\pm$ 1.2V.

#### Current

Peak fan current draw during start-up operation(with 13.2V applied,with fan operating in the free stream condition)shall not exceed 2.0 A.

Fan current spike during start-up operation(with 13.2V applied with fan operating in the free stream condition)shall be allowed to exceed 1.0 A for a duration of no greater than 1.0 sec.

#### Tachometer Output Signal

Fan shall provide tachometer output signal with the following characteristics:

- \* Two pulses per revolution
- \* Open-collector or open-drain type output
- \* Motherboard will have a pull up to 12V, maximum 13.2V

#### PWM Control Input Signal

The following requirements are measured at the PWM(control) pin of the fan cable

connector:PWM Frequency:Target frequency 25kHz,

acceptable operational range 21 kHz to 28 Khz

Maximum voltage for logic low:VIL=0.8V

Absolute maximum current sourced:Imax=5mA(short circuit current)

Absolute maximum voltage level:Vmax=5.25V(open circuit voltage)

#### Fan Speed Control

##### 1.1Maximum Fan Speed Requirements

The maximum fan speed shall be specified for the fan model by the vendor and correspond to 100% duty cycle PWM signal input.

##### 1.2 Minimum Fan Speed Requirements

The vendor shall specify the minimum RPM and the corresponding PWM duty cycle. This specified minimum RPM shall be 30% of maximum RPM or less.The fan shall be able to start and run at this RPM. To allow a lower specified minimum RPM,it is acceptable to provide a higher PWM duty cycle to the fan motor for a short period of time for startup conditions.This pulse should not exceed 30% maximum RPM and should last no longer than 2 seconds.



# DYNATRON CORPORATION


## TOP MOTOR TECHNOLOGY (HUIZHOU) CO, LTD

USA Dynatron Corp.

### 1.3 Fan Speed Response PWM Control Input Signal

The PWM input shall be delivered to the fan through the control signal on Pin4. Fan speed response to this signal shall be a continuous and monotonic of the duty cycle of the signal, from 100% to the minimum specified RPM. The fan RPM (as a percentage of maximum RPM) should match the PWM duty cycle within  $\pm 10\%$ . If no control signal is present the fan shall operate at maximum RPM.

Figure 1 Fan speed Response to PWM Control input Signal



### 1.4 Operation Below Minimum RPM

For all duty cycles less than the minimum duty cycle, the RPM shall not be greater than the minimum RPM. The following graphs and definitions show three recommended solutions to handle PWM duty cycles that are less than the minimum operational PRM, as a percentage of maximum.

Reference resource by Intel's 4-wire PWM Fan controlled specification.



# Certificate of Environment Protection

## 環保證明書

Document Number: RH-N3-R0

|                                       |  |
|---------------------------------------|--|
| <b>Customer:</b><br>客戶名稱:             | <b>Company:</b><br><b>Address:</b> _____<br><b>Phone Number:</b> _____ - _____ - _____ |
| <b>Issue Date:</b><br>發行日期:           | 01/04/2022   |
| <b>Product Model Number:</b><br>產品號碼: | N3   |


**Dynatron Corporation / Dynaeon Industrial Co., Ltd** hereby declares and certifies that all components manufactured are RoHS, ROHS2 & ROHS3 compliant according to the definitions and restrictions given by the European Union's Restriction (Directive 2002/95/EC) (Directive 2011/65/EU) & (Directive (EU) 2015/863) as known as RoHS 3, on the restriction of the use of certain Hazardous Substances in the electrical and electronic equipment.

No exemptions are claimed in order for the part to be compliant with the RoHS directive.

**Dynatron Corporation / 政久興業股份有限公司**證明所有產品,零件 (包括附屬品,包裝類) 之環境管理物質完全符合 RoHS, WEEE, 及該環保標準之規定, 並承諾遵循以上之證明.

**Dynatron Corporation / Dynaeon Industrial Co., Ltd.**

Title (職務): \_\_\_\_\_ ASSISTANT-MANAGER / 副理 \_\_\_\_\_

Signature (簽字): \_\_\_\_\_  


Date: 01/04/2022