

QSFPDD-8SFP56-PDACXM-AO

MSA and TAA Compliant 400GBase-CU QSFP-DD 400G to 8xSFP56 Direct Attach Cable (Passive Twinax, Up to 2.5m)

Features

- Compliant with QSFP-DD MSA Specification Rev 3.4
- SFF-8679 electrical interface compliant
- SFF-8636 management interface support
- Compliant with IEEE802.3Bj, By, IEEE802.3CD Standard
- Support 28 Gbps NRZ or 56 Gbps PAM-4 electrical data rates/channel
- I2C for EEPROM communication
- Pull to Release latch design
- Excellent EMI/EMC performance 360-degree cable shield termination
- Advantage dual side pre-solder automated assembly technologies
- Low loss, stronger mechanical features, more flexible
- ROHS-6 Compliant

Applications

- Servers
- Switches
- Routers
- Data Centers
- High Performance Computing

Product Description

This is an MSA compliant 400GBase-CU QSFP-DD to 8xSFP56 direct attach cable that operates over passive copper with a maximum reach up to 2.5m (8.2ft). It has been programmed, uniquely serialized, and data-traffic and application tested to ensure it is 100% compliant and functional. Our direct attach cables are built to comply with MSA (Multi-Source Agreement) standards. We stand behind the quality of our products and proudly offer a limited lifetime warranty.

AddOn's direct attach cables are RoHS compliant and lead-free.

TAA refers to the Trade Agreements Act (19 U.S.C. & 2501-2581), which is intended to foster fair and open international trade. TAA requires that the U.S. Government may acquire only "U.S. – made or designated country end products."





Order Information

| Part Number | Description |
|---------------------------|---|
| QSFPDD-8SFP56-PDAC1M-AO | MSA and TAA Compliant 400GBase-CU QSFP-DD 400G to 8xSFP56 Direct Attach Cable |
| | (Passive Twinax, 1m) |
| QSFPDD-8SFP56-PDAC2M-AO | MSA and TAA Compliant 400GBase-CU QSFP-DD 400G to 8xSFP56 Direct Attach Cable |
| | (Passive Twinax, 2m) |
| QSFPDD-8SFP56-PDAC2-5M-AO | MSA and TAA Compliant 400GBase-CU QSFP-DD 400G to 8xSFP56 Direct Attach Cable |
| | (Passive Twinax, 2.5m) |

Regulatory Compliance

| Certification | Standard |
|------------------|---|
| Laser Eye Safety | IEC: 60825-1, 3 rd Edition FDA: CFR-21 Sections 1040.10 and 1040.11 |
| Product Safety | TUV: EN62368-1 UL/CSA 60950-1 |
| EMC/EMI | FCC: Part 15 sb.B EN: 55032/55024 |

Mechanical Characteristics

| Length | Wire Gauge | Cable OD | Cable Jacket Material | Flammability Rating |
|--------|------------|----------|-----------------------|---------------------|
| 1m | 32 AWG | 3.81mm | PVC | VW-1 |
| 2m | 28AWG | 4.62mm | PVC | VW-1 |
| 2.5m | 28AWG | 4.62mm | PVC | VW-1 |

Electrical Characteristics

| Licetrical Characteristics | |
|-----------------------------------|------------------------|
| Parameter | Specification |
| Impedance | 100 ohm |
| Data Rate | 56Gbps per lane (PAM4) |
| Voltage | 3.3V DC |
| Current (signal application only) | 0.75A |
| Operating Temperature | -10°C to +60°C |
| High Speed Compliant | IEEE 802.3cd |

QSFP-DD to 8xSFP56 Wiring Schematic

| P1 (QSF | P-DD) | | P2 | (SFP56) |
|----------------------------|-------|------|----------|---------------------|
| GND | | | | GND |
| T X 1 + | 36 | <→> | 13 | RXI+ |
| T X 1 - | 37 | ↔ | 12 | RX1- |
| GND | | | | GND |
| RX1+ | 17 | <->> | 18 | TX1+ |
| RX1- | 18 | <> | 19 | TX1- |
| GND | | | | GND |
| | | | | |
| P1 (QSF | P-DD) | | P3 | (SFP56) |
| GND | | | | GND |
| T X 2 + | 3 | <-> | 13 | RX1+ |
| T X 2 - | 2 | ♦→ | 12 | RX1- |
| GND | | | | GND |
| R X 2 + | 22 | < →> | 18 | TX1+ |
| RX2- | 21 | <> | 19 | TX1- |
| GND | | | | GND |
| P1 (QSF | P-DD) | | P4 | (SFP56) |
| GND | | | | GND |
| T X 3+ | 33 | ↔ | 13 | RX1+ |
| TX3- | 34 | ↔ | 12 | RX1- |
| GND | | | | GND |
| RX3+ | 14 | <-> | 18 | TX1+ |
| RX3- | 15 | <-> | 19 | TX1- |
| GND | | | | GND |
| | | | | |
| | P-DD) | | P5 | (SFP56) |
| 1 (QSF | , | | | |
| GND GND | | | | GND |
| | 6 | <->> | 13 | GND RXI+ |
| GND | | → | 13 12 | |
| GND TX4+ | 6 | | - | RX1+ |
| GND TX4+ TX4- | 6 | | - | RXI+ |
| GND TX4+ TX4- GND | 6 5 | <->> | 12 | RXI+ RXI- GND |

| 1 (QSFI | P-DD) | | P6 | (SFP56) |
|-------------|----------|-----------|----|---------|
| GND | | | | GND |
| T X 5 + | 74 | ↔ | 13 | RX1+ |
| T X 5 - | 75 | <-> | 12 | RX1- |
| GND | | | | GND |
| RX5+ | 55 | <→> | 18 | TX1+ |
| RX5- | 56 | <> | 19 | TX1- |
| GND | | | | GND |
| 21 (QSF | P-DD) | | P7 | (SFP56) |
| GND | | | | GND |
| TX6+ | 41 | d→Þ | 13 | RX1+ |
| TX6- | 40 | <-> | 12 | RX1- |
| GND | | | | GND |
| RX6+ | 60 | <-> | 18 | TX1+ |
| RX6- | 59 | <> | 19 | TX1- |
| GND | | | | GND |
| | | | | |
| 1 (QSF | P-DD) | | P8 | (SFP56) |
| GND | | | | GND |
| T X 7+ | 71 | ↔ | 13 | RX1+ |
| T X 7 - | 72 | <-> | 12 | RX1- |
| GND | | | | GND |
| RX7+ | 52 | ♦→> | 18 | TX1+ |
| RX7- | 53 | 4→> | 19 | TX1- |
| GND | | | | GND |
| 1 (QSF | P-DD) | | P9 | (SFP56) |
| GND | | | | GND |
| +8XT | 44 | <->> | 13 | RXI+ |
| | 43 | 4→> | 12 | RX1- |
| TX8- | | | | GND |
| TX8- GND | | | | 0110 |
| | 63 | <-> | 18 | TX1+ |
| GND | 63 62 | ◇→ | 18 | |

QSFP-DD Pin Descriptions

| PIN | Logic | Symbol | Description | Notes |
|-----|------------|----------|---|-------|
| 1 | | GND | Ground | 1 |
| 2 | CML-I | Tx2n | Transmitter Inverted Data Input | |
| 3 | CML-I | Tx2p | Transmitter Non-Inverted Data Input | |
| 4 | | GND | Ground | 1 |
| 5 | CML-I | Tx4n | Transmitter Inverted Data Input | |
| 6 | CML-I | Tx4p | Transmitter Non-Inverted Data Input | |
| 7 | | GND | Ground | 1 |
| 8 | LVTTL-I | ModSelL | Module Select | |
| 9 | LVTTL-I | ResetL | Module Reset | |
| 10 | | VccRx | +3.3V Power Supply Receiver | 2 |
| 11 | LVCMOS-I/O | SCL | 2-wire serial interface clock | |
| 12 | LVCMOS-I/O | SDA | 2-wire serial interface data | |
| 13 | | GND | Ground | 1 |
| 14 | CML-O | Rx3p | Receiver Non-Inverted Data Output | |
| 15 | CML-O | Rx3n | Receiver Inverted Data Output | |
| 16 | | GND | Ground | 1 |
| 17 | CML-O | Rx1p | Receiver Non-Inverted Data Output | |
| 18 | CML-O | Rx1n | Receiver Inverted Data Output | |
| 19 | | GND | Ground | 1 |
| 20 | | GND | Ground | 1 |
| 21 | CML-O | Rx2n | Receiver Inverted Data Output | |
| 22 | CML-O | Rx2p | Receiver Non-Inverted Data Output | |
| 23 | | GND | Ground | 1 |
| 24 | CML-O | Rx4n | Receiver Inverted Data Output | |
| 25 | CML-O | Rx4p | Receiver Non-Inverted Data Output | |
| 26 | | GND | Ground | 1 |
| 27 | LVTTL-O | ModPrsL | Module Present | |
| 28 | LVTTL-O | IntL | Interrupt | |
| 29 | | VccTx | +3.3V Power Supply Transmitter | 2 |
| 30 | | Vccl | +3.3V Power Supply | 2 |
| 31 | LVTTL-I | InitMode | Initialization mode; In legacy QSFP applications, the InitMode pad is called LPMODE | |
| 32 | | GND | Ground | 1 |
| 33 | CML-I | Тх3р | Transmitter Non-Inverted Data Input | |
| 34 | CML-I | Tx3n | Transmitter Inverted Data Input | |
| 35 | | GND | Ground | 1 |
| 36 | CML-I | Tx1p | Transmitter Non-Inverted Data Input | |
| 37 | CML-I | Tx1n | Transmitter Inverted Data Input | |
| 38 | | GND | Ground | 1 |

| PIN | | Symbol | Description | Notes |
|-----|-------|----------|-------------------------------------|-------|
| 39 | | GND | Ground | 1 |
| 40 | CML-I | Tx6n | Transmitter Inverted Data Input | |
| 41 | CML-I | Тх6р | Transmitter Non-Inverted Data Input | |
| 42 | | GND | Ground | 1 |
| 43 | CML-I | Tx8n | Transmitter Inverted Data Input | |
| 44 | CML-I | Tx8p | Transmitter Non-Inverted Data Input | |
| 45 | | GND | Ground | 1 |
| 46 | | Reserved | For future use | 3 |
| 47 | | VSI | Module Vendor Specific 1 | 3 |
| 48 | | VccRx1 | 3.3V Power Supply | 2 |
| 49 | | VS2 | Module Vendor Specific 2 | 3 |
| 50 | | VS3 | Module Vendor Specific 3 | 3 |
| 51 | | GND | Ground | 1 |
| 52 | CML-O | Rx7p | Receiver Non-Inverted Data Output | |
| 53 | CML-O | Rx7n | Receiver Inverted Data Output | |
| 54 | | GND | Ground | 1 |
| 55 | CML-O | Rx5p | Receiver Non-Inverted Data Output | |
| 56 | CML-O | Rx5n | Receiver Inverted Data Output | |
| 57 | | GND | Ground | 1 |
| 58 | | GND | Ground | 1 |
| 59 | CML-O | Rx6n | Receiver Inverted Data Output | |
| 60 | CML-O | Rx6p | Receiver Non-Inverted Data Output | |
| 61 | | GND | Ground | 1 |
| 62 | CML-O | Rx8n | Receiver Inverted Data Output | |
| 63 | CML-O | Rx8p | Receiver Non-Inverted Data Output | |
| 64 | | GND | Ground | 1 |
| 65 | | NC | No Connect | 3 |
| 66 | | Reserved | For future use | 3 |
| 67 | | VccTx1 | 3.3V Power Supply | 2 |
| 68 | | Vcc2 | 3.3V Power Supply | 2 |
| 69 | | Reserved | For future use | 3 |
| 70 | | GND | Ground | 1 |
| 71 | CML-I | Тх7р | Transmitter Non-Inverted Data Input | |
| 72 | CML-I | Tx7n | Transmitter Inverted Data Input | |
| 73 | | GND | Ground | 1 |
| 74 | CML-I | Тх5р | Transmitter Non-Inverted Data Input | |
| 75 | CML-I | Tx5n | Transmitter Inverted Data Input | |
| 76 | | GND | Ground | 1 |

Notes:


- 1. QSFP-DD uses common ground (GND)for all signals and supply (power). All are common within the QSFP-DD module and all module voltages are referenced to this potential unless otherwise noted. Connect these directly to the host board signal-common ground plane.
- 2. VccRx, VccRx1, Vcc1, Vcc2, VccTx and VccTx1 shall be applied concurrently. Requirements defined for the host side of the Host Card Edge Connector are listed in Table 6. VccRx, VccRx1, Vcc1, Vcc2, VccTx and VccTx1 may be internally connected within the module in any combination. The connector Vcc pins are each rated for a maximum current of 1000 mA.
- **3.** All Vendor Specific, Reserved and No Connect pins may be terminated with 50 ohms to ground on the host. Pad 65 (No Connect) shall be left unconnected within the module. Vendor specific and Reserved pads shall have an impedance to GND that is greater than 10 kOhms and less than 100 pF.
- **4.** Plug Sequence specifies the mating sequence of the host connector and module. The sequence is 1A, 2A, 3A, 1B, 2B, 3B. (see Figure 2 for pad locations) Contact sequence A will make, then break contact with additional QSFP-DD pads. Sequence 1A, 1B will then occur simultaneously, followed by 2A, 2B, followed by 3A,3B.

QSFP-DD Electrical Pin-out Details

Top side viewed from top Module Card Edge (Host Side) 38 GND 76 GND 37 TX1n 75 TX5n 36 TX1p 74 TX5p 35 GND 73 GND 34 TX3n 72 TX7n 33 TX3p 71 TX7p 32 GND 70 GND 31 InitMode 69 Reserved 30 Vcc1 68 Vcc2 29 VccTx 67 VccTx1 28 IntL 66 Reserved 27 ModPrsL 65 NC 26 GND 64 GND 25 RX4p 63 RX8p 24 RX4n 62 RX8n 23 GND 61 GND 22 RX2p 60 RX6p 21 RX2n 59 RX6n 20 GND **58 GND**

www.addonnetworks.com Phone: 877.292.1701 Rev: 0321 | 6

Bottom side viewed from bottom




SFP56 Pin Definitions

| Pin | Symbol | Name/Descriptions | Notes |
|-----|------------|---|-------|
| 1 | VeeT | Transmitter Ground | 1 |
| 2 | TX_Fault | Transmitter Fault (LVTTL-O) - High indicates a fault condition | 2 |
| 3 | TX_Disable | Transmitter Disable (LVTTL-I) – High or open disables the transmitter | 3 |
| 4 | SDA | Two wire serial interface Data Line (LVCMOS-I/O) (MOD-DEF2) | 4 |
| 5 | SCL | Two wire serial interface Clock Line (LVCMOS-I/O) (MOD-DEF1) | 4 |
| 6 | MOD_ABS | Module Absent (Output), connected to VeeT or VeeR in the module | 5 |
| 7 | RS0 | NA | 6 |
| 8 | RX_LOS | Receiver Loss of Signal (LVTTL-O) | 2 |
| 9 | RS1 | NA | 6 |
| 10 | VeeR | Receiver Ground | 1 |
| 11 | VeeR | Receiver Ground | 1 |
| 12 | RD- | Inverse Received Data out (CML-O) | |
| 13 | RD+ | Received Data out (CML-O) | |
| 14 | VeeR | Receiver Ground | |
| 15 | VccR | Receiver Power - +3.3V | |
| 16 | VccT | Transmitter Power - +3.3 V | |
| 17 | VeeT | Transmitter Ground | 1 |
| 18 | TD+ | Transmitter Data In (CML-I) | |
| 19 | TD- | Inverse Transmitter Data In (CML-I) | |
| 20 | VeeT | Transmitter Ground | 1 |


Notes:

- 1. The module signal grounds are isolated from the module case.
- 2. This is an open collector/drain output that on the host board requires a $4.7K\Omega$ to $10K\Omega$ pull-up resistor to Vcc-Host.
- 3. This input is internally biased high with a $4.7K\Omega$ to $10K\Omega$ pull-up resistor to VccT.
- 4. Two-Wire Serial interface clock and data lines require an external pull-up resistor.
- 5. This is a ground return that on the host board requires a $4.7K\Omega$ to $10K\Omega$ pull-up resistor to Vcc-Host.
- 6. Rate select not available




Host PCB SFP56 Pad Assignment Top View

SI Test Reports 1m 30 AWG




1m 30AWG




Mechanical Specifications

QSFP-DD to 8xSFP 1m



QSFP-DD to 8xSFP 2m, 2.5m



About AddOn Networks

In 1999, AddOn Networks entered the market with a single product. Our founders fulfilled a severe shortage for compatible, cost-effective optical transceivers that compete at the same performance levels as leading OEM manufacturers. Adhering to the idea of redefining service and product quality not previously had in the fiber optic networking industry, AddOn invested resources in solution design, production, fulfillment, and global support.

Combining one of the most extensive and stringent testing processes in the industry, an exceptional free tech support center, and a consistent roll-out of innovative technologies, AddOn has continually set industry standards of quality and reliability throughout its history.

Reliability is the cornerstone of any optical fiber network and is in engrained in AddOn's DNA. It has played a key role in nurturing the long-term relationships developed over the years with customers. AddOn remains committed to exceeding industry standards with certifications from ranging from NEBS Level 3 to ISO 9001:2005 with every new development while maintaining the signature reliability of its products.

U.S. Headquarters

Email: sales@addonnetworks.com

Telephone: +1 877.292.1701

Fax: 949.266.9273

Europe Headquarters

Email: salessupportemea@addonnetworks.com

Telephone: +44 1285 842070

www.addonnetworks.com Phone: 877.292.1701 Rev: 0321 |12