

Sharp NEC Display Solutions dvLED solutions:

Direct View LED Kitted SKUs

NEC has created LED installation kits that include all of the key components needed for a video wall built with dvLED. These kits feature a standard 16:9 aspect ratio and include the LED controller, installation frame and even spare parts for service.

110", 137", 165" and 220"

0.9mm - 3.8mm









Sharp/NEC FA Series: High-End Indoor

- LED-FA012i2-110 LED-FA019i2-110 LED-FA015i2-137 LED-FA019i2-165
- LED-FA009i2-165 LED-FA012i2-220 LED-FA025i2-220
- 3 year warranty (extended warranty available)
 170° viewing angle
- 100k hour lifetime
- Redundant power supplies and controller Premium LED and performance

Sharp/NEC FE Series: Mainstream Indoor

- LED-FE012i2-110 LED-FE019i2-110 LED-FE015i2-135 LED-FE019i2-165
- LED-FE009i2-165 LED-FE012i2-220 LED-FE025i2-220
- 3 year warranty (extended warranty available) 160° viewing angle
- Single power supply and scan card Performance without redundancy

Sharp/NEC E Series: Essential Indoor

- LED-E012i-108 LED-E015i-135 LED-E018i-162
- LED-E012i-217 LED-E025i-217
- 2 year Warranty (extended warranty available)
- Affordable / Essential LED performance





