


Samsung 43" UHD Projected Capacitive Touch Screen Solution



Samsung Authorized Solution
SAMSUNG



Projected Capacitive Touch Solution

TSItouch's line of projected capacitive touch displays are engineered specifically for consumer and commercial customers who are looking for a rugged and durable touch screen without having to sacrifice on image quality. Featuring a seamless flat front bezel design, the monitor can easily be wiped clean, thereby eliminating having to worry about dust and dirt collection, which helps extend the use of your display and enhances your touch experience.



Multi-Touch Screen
 True multi-touch support with up to 100 simultaneous touch points for all major operating systems



Easy Integration
 Unrivaled simplicity makes installation easier and faster



Ultra-Fast Response Time
 Allows for split second reactions between touch point and screen



HID Compliant
 Maximum compatibility with numerous operating systems, plug-and-play



Superior Design
 Zero bezel flat front, clear tempered touch screen with excellent optical performance



Easy to Clean
 Water and dust resistant

Specifications

Display Models	QB43R, QH43R, QM43R
Touch Screen (Display Not Included)	TSI43NS15DHJCZZ
QB43R Integrated Touch Screen (Display Included)	TSI43PSTFDHJCZZ
QH43R Integrated Touch Screen (Display Included)	TSI43PSHPDHJCZZ
QM43R Integrated Touch Screen (Display Included)	TSI43PSTEDHJCZZ
Protective Glass	1/4" Clear Tempered Cover Glass
Structure Material	Black Powder Coated Cold Rolled Steel
Touch Technology	PCAP
Touch Points	40
Response Time	6 - 16ms
Touch Accuracy	+/- 2mm (Over 99% Area)
Interface	Type A USB/M
Communication	USB 2.0
Receiver Extender	N/A
Touch Power Source	USB
Width/Height/Depth Including Monitor	39.65" x 23.66" x 2.36"
Touch Screen Weight	29.54 lbs
Display Integrated Weight	52.03 lbs
Boxed Dimensions	42.00" x 27.00" x 7.50"
OS Support	Windows, Google Chrome, Android, Mac, Linux