

Product data sheet

Specifications

APC Smart-UPS SRT 192V 8kVA and 10kVA RM Battery Pack TAA



SRT192RMBP2US

Overview

Lead time Usually in Stock

Main

Product or Component Type Battery

number of rack unit 3U

Battery Type Lead-Acid battery

Provided Equipment Installation guide
Warranty card

Batteries & Runtime

Battery Slots Empty 0

Included Battery Modules 0

Device mounting Stand alone battery stack

Battery Voltage +/- 192 V

RBC Quantity 2

Replacement battery [APCRBC140](#)

Physical

Color Black

Height 5.1 in (13 cm)

Width 17.008 in (43.2 cm)

Depth 26.9 in (68.3 cm)

Net Weight 200.20 lb(US) (90.81 kg)

Mounting Mode Not rack-mountable

Environmental

Ambient Air Temperature for Operation 32...104 °F (0...40 °C)

Operating altitude 0...10000 ft

Relative Humidity 0...95 % non-condensing

Ambient Air Temperature for Storage 5...113 °F (-15...45 °C)

Storage altitude 0...50000 ft (0.0000000000...15240.0000000000 m)

Storage Relative Humidity 0...95 % non-condensing

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

GTIN 731304379881

Country of origin PH

Packing Units

Unit Type of Package 1 PCE

Number of Units in Package 1 1

Package 1 Height 16.5 in (42 cm)

Package 1 Width 39.4 in (100 cm)

Package 1 Length 23.6 in (60 cm)

Package 1 Weight 232.10 lb(US) (105.28 kg)

Contractual warranty

Warranty 2 years repair or replace

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back

Resource performance

✓ Energy Efficient Product

✓ Take-Back Program Available

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information Yes

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information.
