



Rocket 1108
PCIe 3.0 x16 8-Port M.2 NVMe HBA



High-Performance 8-Channel PCIe Gen3 M.2 NVMe Connectivity Solution

R1000 Series NVMe HBAs are fully independent, stand-alone NVMe storage solutions for PCIe Gen3 platforms; they are not tied to a specific motherboard, chipset or operating system, can be easily integrated into any motherboard or server/workstation platform with a free PCIe 3.0/4.0 x16 and are capable of supporting off-the-shelf M.2 NVMe SSDs of any capacity.

The Rocket 1108 is the industry's fastest PCIe Gen3 NVMe connectivity HBA. The eight independent device ports can support off-the-shelf M.2 SSDs of any capacity.

Built-in High-speed, Intelligent Switch Chipset

The Rocket 1108 NVMe HBA's performance-focused hardware architecture leverages intelligent PCIe switch technology to ensure maximum transfer bandwidth is available for each device port, at all times. Up to x4 lanes of host bandwidth are allocated to each M.2 NVMe SSD, as needed.

Native, In-Box NVMe Device Driver Support

HighPoint NVMe HBAs were designed with simplicity in mind. All you need is a little patience and a screwdriver; just install the M.2 SSD's and plug in the card!

Rocket 1000 Series HBAs are natively supported by all major Windows and macOS operating system platforms, VMware ESXi and current distributions of Linux.

You won't need to juggle a series of device drivers, install a complex software suite, or master a specialized management interface. Your NVMe SSDs will be automatically recognized, and can be prepped and mounted using the operating system's standard tool set.

Ultra-High-Performance NVMe Storage Solution

Rocket 1000 Series NVMe HBA's can host RAID arrays created using the operating systems built-in storage management tools.

macOS Disk Utility and Windows Disk Management can configure RAID 0 arrays using 2 or more NVMe SSDs.

Supports any Off-the-Shelf M.2 NVMe SSD

Any Capacity, Any Generation & Any Form-Factor...

Rocket 1000 series M.2 ports are capable of supporting any industry standard off-the-shelf M.2 NVMe SSD

NAND Form Factor: Single & Double-Sided

M.2 Form Factor: 2280, 2260, 2242

Low-Noise Hyper Cooling Solution


The Rocket 1108 employs our new ultra-efficient, Hyper-Cooling solution designed specifically for large M.2 configurations. The Hyper-Cooling system combines a high-conductivity thermal pad with an anodized aluminum heatsink equipped with dual built-in, low noise fans. This design ensures the M.2 SSDs, NVMe chipset and RAID componentry remain cool, even under heavy load, while minimizing the risk of distraction in the work environment.

Key Benefits

- Up to 8 NVMe SSDs
- PCIe 3.0 x16 Host Interface
- Fully compliant with Industry standard PCIe 3.0 Slots; no-Bifurcation dependency or need for a specific brand/model of motherboard
- Integrated, High-Performance, Intelligent PCIe Switch technology allocates up to x4 lanes to each M.2 Slot
- Native, in-box NVMe driver support for all major OS platforms
- Broad Compatibility with current computing platforms: HP, Dell, Alienware, Legacy Mac Pro, 2019 Mac Pro, Apple M1 Platforms
- Low-Noise, Hyper Cooling Solution



The Rocket 1100 series can be used with Legacy Mac Pro 5.1 systems and macOS 10.x or earlier.



R1000 HBA's support OS-based RAID, which can be configured using the operating system's default storage management interface.

Product	Rocket 1108 (R1108)
Bus Interface	PCI-Express 3.0 x16
No. of Channels/Ports	8x M.2 NVMe port (up to PCIe 3.0 x4 per port)
Data Transfer Rate	8 GT/s
Number of devices	8x M.2 NVMe SSDs
SSD Form Factor*	2242/2260/2280
Form Factor	Full-Height
Card Dimensions	11.22"(L)*4.37"(H)*0.83"(D)
Package Weight	1.70 lbs.
Cooling	Full-length anodized aluminum heat sink with built-in Low-Noise fans
Supported Operating Systems & Platforms	
Windows	Windows 11, 10 / Windows Server 2022, 2019 / Microsoft Hyper-V
Linux	Linux Kernel v3.10 or later
macOS	MacOS 10.13 and later
FreeBSD	FreeBSD 12.1 and later
VMware	ESXi 6.7 and later
System Requirements	Mac Platforms: <ul style="list-style-type: none"> • Apple Mac Pro Systems: 2012 and later; 5.1, 7.1 (2019) • Apple M1 Platform compatible
	PC Platforms: <ul style="list-style-type: none"> • Any PC or Motherboard with an industry standard PCIe x16 physical Slot (Bifurcation is not required)
Operating Environment	
Work Temp	+5°C ~ + 35°C
Storage Temp	-20°C ~ +80°C
Operating Voltage	PCI-e: 12V, 3.3V
Power	Typical: 7.16W
MTBF	920,585 Hours
Certification	CE, FCC, RoHS, REACH, WEEE
Kit Contents	R1108
	QIG

* Supports single and double-sided M.2 NVMe SSDs



Compact, Self-Contained M.2 Solution:
M.2 SSDs are directly hosted by HBA (no drive bays or enclosure is required)



Ultra-High Performance:
Dedicated PCIe 3.0 x8 or x16 Bus-Bandwidth