



Large Format

LCD Displays

- ► 4K Resolution
- ▶ 43" to 100" Sizes
- Models with Interactive Touch
- ► TAA Compliant



Built for the most demanding environments, Planar's large format LCD displays deliver high durability and performance for professional applications like digital signage, control rooms, study spaces and retail. Unlike consumer televisions, our displays feature higher brightness, robust design for up to 24x7 use in most models, and options like multi-source viewing and portrait or landscape orientation. Our displays are all 4K resolution and fit every need with various sizes, brightness levels, functionality and prices.

Achieve Clarity & View it All

Planar 4K LCD displays produce amazing, life-like picture quality with smooth motion video and mouse tracking. Thanks to sharp clarity and crisp image quality, every detail shows even at close viewing distances.

Multiple large-format LCD display lines enable people to view more than one—and up to four—sources on the screen simultaneously. Configurable and storable content layout options include picture-in-picture, dual, triple or quad view.



Planar UltraRes X Series

Superior Image Color and Clarity

Planar® UltraRes™ X Series displays offer superior visual performance and advanced processing, ideal for applications ranging from collaborative meeting spaces to high-impact digital signage.

- 75", 85" & 100" sizes
- · Bright 700 nits
- High Dynamic Range (HDR) compatible
- Multi-source viewing with Planar[®] MediaPlex[™] Plus processing
- Optional Planar[®] Profile[™] Mounting System
- Expansion slot for OPS
- Optional Planar[®] ERO-LCD[™] protective glass



Planar QE Series

Only the 24x7 Essentials

Planar® QE Series displays excel in applications from dynamic digital signage to collaborative meeting spaces.

- 98" size
- Exceptional image quality & color accuracy
- 4K at 60Hz support with DisplayPort
 1.2 & HDMI 2.0
- 4K compatibility with HDCP 2.2
- Optional multi-point touch with Planar ERO-LCD
- Planar Touchmark license included with touch model
- Designed for 24x7 operation



Planar UltraRes P Series

Only the 24x7 Essentials

Planar® UltraRes™ P Series displays excel in applications from dynamic digital signage to collaborative meeting spaces.

- 75" & 85" sizes
- Exceptional color accuracy
- 4K at 60Hz support with DisplayPort 1.2 & HDMI 2.0
- 4K with HDCP 2.2
- Optional multi-point touch with Planar ERO-LCD
- Planar[®] Touchmark[™]
 Software license included with touch model
- Designed for 24x7 operation



Series Planar EP Series

High Performance 4K

The Planar® EP Series delivers superior performance and reliability for demanding public venue, corporate and control room applications.

- 50", 58" & 65" sizes
- Exceptional image quality
- 4K at 60Hz support with DisplayPort 1.2 & HDMI 2.0
- 4K compatibility with HDCP 2.2
- Expansion slot for OPS
- Optional multi-point touch
- Planar Touchmark license included with touch models
- Designed for 24x7 operation



Planar PS Series 4K

Essentials for 24x7 Digital Signage

The Planar® PS Series offers a rich feature-set with embedded Android® for cloud-based signage, Wi-Fi (select models), and vibrant brightness specifically designed for digital signage.

- 50", 55" & 65" sizes
- Built-in Android® operating system
- Wi-Fi models available
- Landscape or portrait mounting
- 20-point touch models available
- 450 to 550-nit brightness
- Designed for 24x7 operation



Planar Simplicity M Series

Cost Effective Digital Signage

The Planar® Simplicity™ M Series is designed with simplicity and affordability in mind, in a wide variety of sizes designed to meet the needs of everything from retail to museums.

- 43", 50", 55", 65", 75" & 86" 4K LCD displays
- 500-nit brightness
- 4K at 60Hz support with HDMI 2.0
- 4K compatibility with HDCP 2.2
- Integrated signage tools, including USB playback and LAN distribution



Planar HB Series Huddle Board

4K Touch Screen Collaboration Displays

Planar® HB Series Huddle Board touch screens have embedded tools ideal for in-room and remote unified communication (UC). It enables one-stop collaboration for conference rooms, study group spaces and design centers; or the executive home office.

- Available in 75" & 86" sizes
- 20-point Projected Capacitive touch
- Embedded digital whiteboard app
- Built-in Android® OS pre-loaded with UC apps
- Active & passive stylus pens included





Made for America

Organizations that prefer to use products that have been manufactured in the United States or countries designated in the U.S. Trade Agreements Act (TAA) need look no further. Planar large format LCD displays are TAA Compliant.



Add Toughness

Some displays are available with Planar® ERO-LCD™ (Extended Ruggedness and Optics™), a protective glass bonded to the front of the display using a proprietary process that creates a highly durable surface that withstands rigors of high-traffic and interactive environments.



Get Interactive

For collaborative and interactive environments, select large format LCD displays are available with multi-point touch that enables multiple people to use the display simultaneously, with pinpoint accuracy and false touch prevention.

Specifications

Planar HB Series Huddle Board				
Model	HB75 HB86			
Screen Diagonal	75" 86"			
Brightness (typ)	350 cd/m2			
Backlight Type	Direct-lit LED			
Bezel Width	0.1" (3mm)			
Recommended Usage	18 x 7			
Orientation	Landscape			
OS Compatibility	Internal: Android; External: Windows 8, 10, Mac OSX, Linux			
External Connections	DisplayPort 1.2 x 1, HDMI 2.0 x 3 (HDCP 2.2), VGA x 1, USB-B (for touch controller), microSD slot, USB 2.0 for external USB camera, OPS Slot			
Display Control	LAN, WiFi (802.11 b/g/n, 2.4 GHz, 5 GHz), Bluetooth, RS232 In, IR, Keypad			
Touch Technology	In-Cell Projected Capacitive 20-point touch			
Mounting	VESA: 600 x 400 VESA: 800 x 600			
Operating System	Android 8.0			
Video Processing	CPU: ARM A73 (x2) + ARM A53 (x2) Frequency: 1.5 GHz GPU: Mali-G51 RAM: 3GB DDR4 2400MHz			

Specifications

Planar UltraRes X Series				
Model	URX75 URX75-ERO	URX85 URX85-ERO	URX100 URX100-ERO	
Screen Diagonal	75"	85"	100"	
Brightness (typ)	700 cd/m²/630 cd/m²/630 cd/m²			
Bezel Width	0.7" (17mm) / 0.1" (3mm) /	0.9" (23mm) / 0.1" (3mm) /	1.1" (27.9mm) / 0.1" (3mm) /	
Color Gamut	90% NTSC 88% NTSC		98% NTSC	
HDR (High Dynamic Range)	Yes			
Recommended Usage	24 x 7			
Orientation	Landscape, Portrait			
Display Depth	3.7" (94.2mm) / 3.7" (94.2mm) /	3.7" (94.3mm) / 3.7" (94.3mm) /	3.7" (94.3mm) / 3.7" (94.3mm) /	
Inputs	DisplayPort 1.2 x 1, HDMI 2.0 x 2 (HDCP 2.2), HDMI 1.4 x 2, OPS x 1			
Display Control	IR, RS-232, LAN, HDMI-CEC, Keypad, Mobile app			
Touch Technology	-			
Mounting	Planar® Profile™ Mounting System, VESA			
Planar TouchMark		-		

Planar UltraRes P Series & Planar QE Series				
Model	URP75 URP75-ERO-T	URP85 URP85-ERO-T	QE9850 QE9850-Touch	
Screen Diagonal	75"	85"	98"	
Brightness (typ)	500 cc 450 c	400 cd/m² 380 cd/m²		
Backlight Type	D-LED			
Bezel Width	0.6" (14.9mm) / 0.6" (15.1mm)	0.5" (13mm) / 0.6" (15.1mm)	0.6" (16mm) / 1.2" (31mm)	
Recommended Usage	24 x 7			
Orientation	Landscape, Portrait		Landscape, Portrait (Landscape ERO-LCD Touch model)	
Display Depth	3.6" (91.2mm) / 4.1" (103.7mm)	3.5" (89.4mm) / 4.1" (104.5mm)	3.8" (97mm) / 4.4" (111mm)	
Inputs	HDMI 2.0 x 2 (HDPC 2.2), HDMI 1.4 x 2; DisplayPort 1.2 x 1			
Display Control	HDMI-CEC, IR, LAN, RS-232, Keypad, Mobile App IR, RS-232, LAN, Keypa			
Touch Technology	IR touch: 20-point (Touch models only)			
Mounting	VESA			
Planar TouchMark	Yes (Touch models only)			

Planar EP Series				
Model	EP5024K EP5024K-Touch	EP5824K EP5824K-Touch	EP6524K EP6524K-Touch	
Screen Diagonal	50"	58"	65"	
Brightness (typ)		500 cd/m ²		
Backlight Type	E-LED	E-LED	D-LED	
Bezel Width	0.8" (21mm)/ 0.7" (18mm)	0.6" (14mm)/ 0.9" (22mm)	0.7" (17mm)/ 0.9" (22mm) (top/bottom); 0.8" (21mm) (left/right)	
Recommended Usage	24 x 7			
Orientation	Landscape, Portrait			
Display Depth	2.6" (67mm)/ 3.3" (84mm)	3.1" (80mm)/ 3.8" (98mm)	3.4" (86mm)/ 3.9" (99mm)	
Inputs	HDMI 2.0 x 2 (HDCP 2.2), HDMI 1.4 x 2, DisplayPort 1.2 x 2, VGA x 1, OPS, IR			
Display Control	IR, RS-232, LAN, Keypad, HDMI-CEC (select models)			
Touch Technology	20 pt IR (HID compliant Microsoft* Windows 7, 8 and 10) Touch models only			
Mounting	VESA: 200x200mm	VESA: 200x400mm	VESA: 400x400mm	
Planar TouchMark	Yes (Touch models only)			

Planar PS Series 4K				
Model	PS5074K PS5074K-N PS5074K-Touch PS5074KT-N	PS5574K PS5574K-N PS5574K-Touch PS5574KT-N	PS6574K PS6574K-N	
Screen Diagonal	50"	55"	65"	
Brightness (typ)	550 cd/m² / 450 cd/m²			
Backlight Type	LED			
Bezel Width	0.7" (17mm) top, 0.8 0.9" (2	0.6" (16mm)		
Recommended Usage	24 x 7			
Orientation	Landscape, Portrait			
Display Depth	2.8" (70mm) / 3.4" (88mm)	2.7" (69mm) / 3.4" (87mm)	2.8" (70mm)	
Inputs	DisplayPort 1.2 x 1, HDMI 2.0 x 2 (HDCP 2.2), VGA x 1 USB-B (for touch controller)			
Display Control	IR, RS-232, LAN, HDMI-CEC, Keypad, WLAN/WiFi (Excluding N models)			
Touch Technology	IR touch: 20-point (Touch models only)			
Mounting	VESA: 400mm x 400mm			

Planar Simplicity M Series						
Model	SLM43	SLM50	SLM55	SLM65	SLM75	SLM86
Screen Diagonal	43"	50"	55"	65"	75"	86"
Brightness (typ)	500 nits					
Backlight Type	D-LED					
Bezel Width	0.5" (13.9mm)	0.6" (14.9mm)	0.5" (13.9mm)	0.6" (14.9mm) 0.6" (15.5mm		
Recommended Usage	Up to 16 hours per day					
Orientation	Landscape only					
Inputs	HDMI 2.0 x 2 (HDCP 2.2), DVI-D x 1, VGA x 1, Media Player					
Display Control	IR, RS-232, LAN, HDMI-CEC, Keypad					
Mounting	VESA: 200x200mm	VESA: 400x400mm			<400mm	