Panasonic CONNECT

WX-SE200DN Dante[®] Expansion Receiver

Dante



Designed to be used with Panasonic's WX-SR204 or WX-SR204DN 4-channel wireless mic receivers, the WX-SE200DN Dante expansion receiver allows you to add up to 4 additional wireless microphone channels an existing Panasonic 4-channel system without the need to add an additional antenna to the system*. Choose between Panasonic's WX-ST200 handheld mics and/or WX-ST400 lavalier mic + wireless bodypacks) for microphone options. Perfect for classrooms, conference rooms, auditoriums, museums, retail, and bars / restaurants, the WX-SE200DN features a RJ45 (CAT5 / CAT5e / CAT6) connection to the Panasonic WX-SR204 or WX-SR204DN 4-channel wireless receivers, and Dante primary and secondary connections for independent channel outputs, external audio input and a mix output. LEDs on the front panel show the system status during startup & microphone pairing, antenna status during operation, and an LED indicator of when the receiver is being controlled remotely. Ships with rack ears for easy rack mount installation.

*Depends on room size and desired coverage.



Key Features:

- Provides Expansion to up to 4 additional wireless mic channels to an existing 4-channel system (WX-SR204 or WX-SR204DN required) without the need to install additional antennas. *
- Dante® digital audio connections (2 x RJ45, 1 primary & 1 secondary)
- Easy to setup no need for planning / allocation of channels; Secure pairing with Panasonic microphones
- Supports external audio input and mixing with mic channels
- Rack mountable (1u high, rack ears included)

Panasonic CONNECT

WX-SE200DN Specifications

Channel Output Circuits:	4
Channel Output Connectors:	Dante (RJ45), Euroblock (for mix output only)
Channel Output Characteristics:	Dante Primary & Secondary: CH1/Ch2/MIX Euroblock connector: MIX only @ -10dBV balanced 600 Ohms
Channel Output Signal to Noise Ratio:	70 dB or greater
Channel Output Frequency Response:	50 Hz to 15 kHz
Channel Output Distortion:	<3%
Audio Input Characteristics:	-10 dBV balanced 600 Ohms
Audio Input Frequency Response:	50 Hz to 15 kHz
Audio Input Distortion:	<3%
Mix Output Connectors:	Dante Primary & Secondary or Euroblock
Mix Output Characteristics:	Dante Primary & Secondary or Euroblock -10 dBV Balanced 600 Ohms
Mix Output Signal to Noise Ratio:	64 dB or greater
Mix Output Frequency Response:	50 Hz to 15 kHz
Mix Output Distortion:	<3%
Extension Connector	1 x RJ45, for WX-SR202 4-ch Receiver (required; sold separately)
Display Indicators:	Power, Sync, Main, Remote, RF Level (5-level display), Audio level / mute, Mic battery, Register
Power Source / Power Consumption:	AC 120 V 60 Hz / 39 Watts
Operating Ambient Temperature:	32° F to 113°F (0°C to 45°C)
Accessories Included:	Rack Ears
Warranty (Parts & Labor): Dimensions (W x H x D): Weight (including battery):	3 years 16-17/32 x 1-47/64 x 9-27/32 inches (420mm x 44mm x 250mm) 6.17 lbs. (2.8 kg)