



The 25/70V 50W Audio Amplifier is the ideal solution for supporting a distributed audio system in a classroom, conference room or other environment that requires installation in a plenum space. This amplifier supplies 50 Watts of power, 25 Watts per channel, and is built to an industry standard 25/70 Volt design. This amplifier supports many advanced features which make it a perfect fit for most applications

Noise Reduction

Audio systems installed in commercial environments are susceptible to noise caused by an electrical ground loop. This will often manifest as a hum or buzz through the system. This amplifier features noise reduction technology on both the 3.5mm and RCA Stereo Audio inputs. This noise reduction eliminates the interference and allows the audio signal to pass through.

Standby Mode

After five minutes without a signal, the amplifier will enter standby mode providing energy savings. The amplifier will wake from standby mode automatically when a signal is received.

Accessory Power Output

The accessory power output provides 12 Volts DC and 500 mAmps. This makes the amplifier the perfect match for a controller such as the

Features & Benefits

Reduces noise in commercial environments

Industry standard 25/70 volt design for distributed audio systems

Standby mode saves power

Designed for installation in Plenum air spaces

Specifications

General Info

Product Line	C2G	Color	Black
UPC Number	757120408819	Country Of Origin	Taiwan, Province Of China
Application Sector	Residential, Commercial	Warranty Type	Lifetime
Type	Amplifier		

Listing Agencies / 3rd Party Agencies

FCC Compliant Yes

Buy American Act Compliance

TAA Compliant	Yes
---------------	-----

Additional Information

Prop 65 Warning Required	Yes	Prop 65 Warning Language	Cancer and Reproductive Harm
--------------------------	-----	--------------------------	------------------------------

Technical Information

Adapter Rear	RCA Stereo Audio Female, 3.5mm Microphone Female	Adapter Front	3.5mm Stereo Female
--------------	--	---------------	---------------------
