


OVERVIEW



1. Card reader	6. HDMI 1.4b
2. USB 3.2 Gen 1	7. USB 3.2 Gen 1 (Always On)
3. Ethernet (RJ-45)	8. Headphone / microphone combo jack (3.5mm)
4. Kensington Nano Security Slot	9. NOVO button hole
5. 2x USB-C 3.2 Gen 2	

PERFORMANCE

Processor

Processor Family

AMD Ryzen™ 3 / 5 / 7 Processor

Processor\*\*

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Memory Support	Processor Graphics
AMD Ryzen 3 5300U	4	8	2.6GHz	3.8GHz	2MB L2 / 4MB L3	DDR4-3200	AMD Radeon™ Graphics
AMD Ryzen 5 5500U	6	12	2.1GHz	4.0GHz	3MB L2 / 8MB L3	DDR4-3200	AMD Radeon Graphics
AMD Ryzen 5 5600U	6	12	2.3GHz	4.2GHz	3MB L2 / 16MB L3	DDR4-3200	AMD Radeon Graphics
AMD Ryzen 5 PRO 5650U	6	12	2.3GHz	4.2GHz	3MB L2 / 16MB L3	DDR4-3200	AMD Radeon Graphics
AMD Ryzen 7 5700U	8	16	1.8GHz	4.3GHz	4MB L2 / 8MB L3	DDR4-3200	AMD Radeon Graphics
AMD Ryzen 7 5800U	8	16	1.9GHz	4.4GHz	4MB L2 / 16MB L3	DDR4-3200	AMD Radeon Graphics

Operating System

Operating System\*\*

- Windows® 11 Pro
- Windows 11 Home
- Windows 11 Home Single Language
- Windows 11 DG Windows 10 Pro 64
- Windows 10 Pro 64
- Windows 10 Home 64
- Windows 10 Home 64 Single Language
- No operating system

Graphics

Graphics

Graphics	Type	Memory	Key Features
AMD Radeon Graphics	Integrated	Shared	DirectX® 12

Monitor Support

Monitor Support

Supports up to 4 independent displays (native display and 3 external monitors via HDMI® and USB-C®)

- HDMI supports up to 4K@30Hz
- USB-C supports up to 4K@60Hz

Chipset

Chipset

AMD SoC (System on Chip) platform

Memory

Max Memory<sup>[1]</sup>

- Up to 36GB (4GB soldered + 32GB SO-DIMM) DDR4-3200
- Up to 40GB (8GB soldered + 32GB SO-DIMM) DDR4-3200

Memory Slots

One memory soldered to systemboard, one DDR4 SO-DIMM slot, dual-channel capable

Memory Type

DDR4-3200

Notes:

- 1. Maximum memory is only to test technical readiness of notebook. Available memory to sell would vary.

Storage

Storage Support<sup>[1][2]</sup>

- HDD/SSD mode: up to two drives, 1x 2.5" HDD + 1x M.2 SSD
  - 2.5" HDD up to 2TB
  - M.2 2242 SSD up to 512GB
  - M.2 2280 SSD up to 1TB
- Dual SSD mode: up to two drives, 2x M.2 SSD
  - M.2 2242 SSD up to 512GB
  - M.2 2280 SSD up to 1TB

Storage Type<sup>\*\*\*[3]</sup>

Disk Type	Interface	RPM	Security
2.5" SATA HDD	SATA 6Gb/s	5.4K	-
2.5" SATA HDD	SATA 6Gb/s	7.2K	-
M.2 2242 SSD	PCIe® NVMe®, PCIe 3.0 x4	-	-
M.2 2280 SSD	PCIe NVMe, PCIe 3.0 x4	-	-

Notes:

- 1. The storage capacity supported is based on the test results with current Lenovo® storage offerings. The system may support larger storage as the technology develops.
- 2. System supports 1x M.2 2280 PCIe 3.0x4 SSD slot + 1x HDD bay or 1x M.2 2280 PCIe 3.0x4 SSD slot + 1x M.2 2280 PCIe 3.0x2 SSD slot, depends on model configuration
- 3. System that comes with two M.2 SSD slots doesn't support to adding an extra 2.5" HDD.

Removable Storage

Optical

None

Card Reader

4-in-1 card reader (SD, SDHC, SDXC, MMC)

Multi-Media

Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers

Stereo speakers, 2W x2, Dolby® Audio™

Microphone

Dual-microphone array with AI-based noise-cancelling, switchable audio modes

Camera

HD 720p, with privacy shutter, fixed focus

Battery

Battery<sup>\*\*[1]</sup>

- Integrated Li-Polymer 45Wh battery, supports Rapid Charge Pro (charge up to 50% in 30min)
- Integrated Li-Polymer 60Wh battery, supports Rapid Charge (charge up to 80% in 1hr)

Max Battery Life<sup>[2]</sup>

- MobileMark® 2018: 10 hr (60Wh)
- MobileMark 2018: 7.5 hr (45Wh)

Notes:

- 1. 60Wh battery is not available for models with HDD bay.
- 2. All battery life claims are approximate maximum and based on results using the MobileMark 2014, MobileMark 2018, JEITA 2.0, continuous 1080p video playback (with 150nits brightness and default volume level) or Google Power Load Test (PLT) battery-life

benchmark tests. Actual battery life will vary and depends on many factors such as product configuration and usage, software use, wireless functionality, power management settings, and screen brightness. The maximum capacity of the battery will decrease with time and use.

Power Adapter

Power Adapter\*\*[1][2]

- 65W USB-C (3-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
- 65W USB-C slim (2-pin, wall-mount) AC adapter, supports PD 3.0, 100-240V, 50-60Hz

- Notes:
- AC adapter offerings depend on the country.
  - 65W USB-C slim (Wall Mount) AC adapter is only available in selected countries

DESIGN

Display

Display\*\*[1]

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Contrast Ratio	Color Gamut	Viewing Angle
14"	FHD (1920x1080)	None	IPS	300 nits	Anti-glare	16:9	1200:1	100% sRGB	170°
14"	FHD (1920x1080)	None	IPS	250 nits	Anti-glare	16:9	700:1	45% NTSC	170°
14"	FHD (1920x1080)	None	IPS	300 nits	Anti-glare	16:9	700:1	45% NTSC	170°
14"	FHD (1920x1080)	Multi-touch	IPS	300 nits	Anti-glare	16:9	700:1	45% NTSC	170°
14"	FHD (1920x1080)	None	TN	220 nits	Anti-glare	16:9	500:1	45% NTSC	90°

Touchscreen

- Capacitive-type on-cell multi-touch, supports 10-point touch
- Non-touch

- Notes:
- California Electronic Waste Recycling Fee  
In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to <https://www.calrecycle.ca.gov/Electronics/Consumer>

Input Device

Keyboard

6-row, spill-resistant, multimedia Fn keys

Keyboard Backlight

- LED backlight
- Non-backlight

Touchpad

Buttonless Mylar® surface multi-touch touchpad, supports Precision TouchPad (PTP)

Mechanical[1]

Dimensions (WxDxH)

323 x 218 x 17.9 mm (12.72 x 8.58 x 0.7 inches)

Weight

Starting at 1.4 kg (3.09 lbs)

Case Color

Mineral grey, dual-tone design

Surface Treatment

Anodizing sandblasting

**Case Material**

Aluminium (top), aluminium (bottom)

**Notes:**

1. The system dimensions and weight vary depending on configurations.

## CONNECTIVITY

### Network

**Ethernet**

Gigabit Ethernet, Realtek RTL8111H-CG, 1x RJ-45, supports Wake-on-LAN

**WLAN + Bluetooth®**<sup>[1][2]</sup>

- 802.11ac 2x2 Wi-Fi® + Bluetooth 5.0, M.2 card
- Wi-Fi 6, 802.11ax 2x2 Wi-Fi + Bluetooth 5.1, M.2 card

**Notes:**

1. Bluetooth 5.2 is hardware ready but may run at a lower version due to OS limitation
2. Wi-Fi 6 full features might be limited by country-level restrictions.  
BT5.1 is supported on Windows 10 version 2004 or above (limited to BT5.0 on the earlier version).

### Ports<sup>[1]</sup>

**Standard Ports**

- 1x USB 3.2 Gen 1
- 1x USB 3.2 Gen 1 (Always On)
- 2x USB-C 3.2 Gen 2 (support data transfer, Power Delivery 3.0, and DisplayPort™ 1.4)
- 1x HDMI 1.4b
- 1x Card reader
- 1x Ethernet (RJ-45)
- 1x Headphone / microphone combo jack (3.5mm)

**Notes:**

1. The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.  
USB 2.0: 480 Mbit/s;  
USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;  
USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;  
USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;  
Thunderbolt™ 3/4: 40 Gbit/s

## Docking

**Docking**

Various docking solutions supported via USB-C.

For more compatible docking solutions, please visit [Docking for ThinkBook 14 G3 ACL](#)

## SECURITY & PRIVACY

### Security

**Security Chip**

Firmware TPM 2.0 integrated in SoC

**Physical Locks**

Kensington® Nano Security Slot™

**Fingerprint Reader**

Touch style fingerprint reader integrated in smart power button

**BIOS Security**

- Power-on password
- Supervisor password

- Hard disk password

**Other Security**

Camera privacy shutter

## SERVICE

### Warranty

**Base Warranty\*\***

- 1-year courier or carry-in service
- 2-year (1-yr battery) courier or carry-in service

## ENVIRONMENTAL

### Operating Environment

**Temperature<sup>[1]</sup>**

- At altitudes up to 2438 m (8,000 ft)
  - Operating: 5°C to 35°C (41°F to 95°F)
  - Storage: 5°C to 43°C (41°F to 109°F)
- At altitudes above 2438 m (8,000 ft)
  - Maximum temperature when operating under the unpressurized condition: 31.3°C (88°F)

**Humidity**

- Operating: 8% to 95% at wet-bulb temperature 23°C (73°F)
- Storage: 5% to 95% at wet-bulb temperature 27°C (81°F)

**Altitude**

Maximum altitude (without pressurization): 3048 m (10,000 ft)

---

**Notes:**

1. When you charge the battery, its temperature must be no lower than 10°C (50°F).

## CERTIFICATIONS

### Green Certifications

**Green Certifications**

- EPEAT™ Silver
- ENERGY STAR® 8.0
- ErP Lot 3
- RoHS compliant

### Other Certifications

**Mil-Spec Test**

MIL-STD-810H military test passed

**Other Certifications**

(Optional) TÜV Rheinland® Low Blue Light

- Feature with \*\* means that only one offering listed under the feature is configured on selected models.
- Feature with \*\*\* means that one or more offerings listed under the feature could be configured on selected models.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES

disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.

- The specifications on this page may not be available in all regions, and may be changed or updated without notice.




AMD



AMD



AMD



AMD



AMD



AMD