

GME423TAA

3-Button Optical USB Wired Mouse TAA Compliant

- High-sensitivity optical sensor
- Delivers smooth, precise cursor movement
- Left, right and scroll button/wheel
- USB 2.0 connector
- 1000 Dpi sensor



Precision Optical Mouse

The TAA- Compliant IOGEAR 3-Button Optical Wired Mouse offers smooth, precise cursor movement for your everyday computing needs. Equipped with left, right and center buttons, a scroll-wheel, and an optical tracking 1000 DPI sensor, the 3-Button Optical Wired Mouse is ready to be connected to your preferred docking station, desktop or KVM.

TAA Compliant

The TAA-compatible mouse is designed for federal government agencies, the military, and other organizations and vendors requiring products manufactured under the provisions of the U.S. Trade Agreements Act.

Ergonomic Design

The mouse is designed with a comfortable grip to eliminate hand strain for office or work from home use. Easily navigate documents or webpages with the convenient scroll wheel that also doubles as a third button.

- High-sensitivity optical sensor
- Delivers smooth, precise cursor movement
- Left, right and scroll button/wheel
- 6ft cable
- USB 2.0 connector
- 1000 Dpi sensor



Requirements

- Windows® 10, Windows® 11
- Mac OS X 10.3+
- USB-A Port

Package Contents

- 1x GME423

Specifications

Function	GME423TAA	Dimensions	GME423TAA
Housing		Unit Dimensions	
Case	ABS Plastic	Height	1 in (2.54 cm)
Operating System Support		Length	4.4" (11.17 cm)
Windows 7,10, 11 and Mac OS 10.7+		Width	2.4 in (6 cm)
Connectors		Inner Pack	
Cable	USB-A (6ft)	Height	9 in (23 cm)
Mouse	3-button mouse	Length	7.6 in (19.5 cm)
		Width	6 in (15.4 cm)
		Inner Pack Qty.	12 pcs
		Unit Package Dimensions	
		Height	1.4 in (3.6 cm)
		Length	5.3 in (13.4 cm)
		Width	3.6 in (9.2 cm)
		Master Carton	
		Height	18.9 in (48 cm)
		Length	15.9 in (40.5 cm)
		Width	7 in (18 cm)
		Master Carton Qty.	48 pcs
		Weight	
		Master Carton Wt.	14.6 lb (6.65 kg)
		Inner Pack Wt.	3.17 lbs (1.44 kg)
		Unit Pack Wt.	0.25 lbs (0.10 kg)
		Unit Wt.	0.20 lbs (0.08 kg)