

OVERVIEW



1. Power connector	5. Headphone / microphone combo jack (3.5mm)
2. HDMI 1.4b	6. Card reader
3. USB 2.0	7. NOVO button hole
4. 2x USB 3.2 Gen 1	

PERFORMANCE

Processor

Processor Family

Intel® Celeron®, Intel Pentium®, or 10th Generation Intel Core™ i3 / i5 / i7 Processor

Operating System

Operating System**

- Windows® 11 Pro 64
- Windows 11 Home 64
- Windows 11 Home in S mode
- Windows 10 Pro 64
- Windows 10 Home 64
- Windows 10 Home in S mode
- FreeDOS
- No operating system

Monitor Support

Monitor Support

Supports up to 2 independent displays (native display and 1 external monitor via HDMI®)

- HDMI supports up to 4096x2160@30Hz

Chipset

Chipset

Intel SoC (System on Chip) platform

Memory

Max Memory^[1]

- Up to 8GB (4GB soldered + 4GB SO-DIMM) DDR4-2400 offering (Intel Celeron or Pentium Gold models)
- Up to 12GB (4GB soldered + 8GB SO-DIMM) DDR4-2666 offering (Intel Core models)

Memory Slots

One memory soldered to systemboard, one DDR4 SO-DIMM slot, dual-channel capable

Memory Type**

- Intel Celeron or Pentium Gold model: DDR4-2400
- Intel Core model: DDR4-2666

Notes:

1. The max memory is based on the test results with current Lenovo® memory offerings. The system may support more memory as the technology develops.

Storage

Storage Support^[1]

- Model with 35Wh battery: up to two drives, 1x 2.5" HDD + 1x M.2 SSD
 - 2.5" HDD up to 1TB
 - M.2 2242 SSD up to 512GB
 - M.2 2280 SSD up to 1TB
 - Optional Intel Optane™ Memory integrated with SSD, M.2
- Model with 45Wh battery: one drive, 1x M.2 SSD
 - M.2 2242 SSD up to 512GB
 - M.2 2280 SSD up to 1TB
 - Optional Intel Optane Memory integrated with SSD, M.2

Storage Slot

- Model with 35Wh battery: one 2.5" drive slot + one M.2 slot
 - One 2.5" drive slot, supports 2.5" SATA HDD
 - One M.2 2280 PCIe® Gen 3x4 slot, supports M.2 2242/2280 SSD
- Model with 45Wh battery: one M.2 slot
 - One M.2 2280 PCIe Gen 3x4 slot, supports M.2 2242/2280 SSD

Storage Type***

Disk Type	Interface	RPM
2.5" SATA HDD	SATA 6Gb/s	5.4K
M.2 2242 SSD	PCIe NVMe®, PCIe 3.0 x2	-
M.2 2280 SSD	PCIe NVMe, PCIe 3.0 x4	-
Intel Optane Memory with Solid State Storage, M.2 2280	PCIe NVMe, PCIe 3.0 x4	-

Notes:

- The storage capacity supported is based on the test results with current Lenovo storage offerings. The system may support larger storage as the technology develops.

Removable Storage

Optical

None

Card Reader

4-in-1 card reader (SD, SDHC, SDXC, MMC)

Multi-Media

Audio Chip

High Definition (HD) Audio

Speakers

Stereo speakers, 1.5W x2, Dolby® Audio™

Microphone

Dual array microphone

Camera^[1]**

- 0.3-megapixel, with privacy shutter, fixed focus
- HD 720p, with privacy shutter, fixed focus

Notes:

- HD720p camera for AP and NA only.

Battery

Battery**

- Integrated Li-Polymer 35Wh battery
- Integrated Li-Polymer 45Wh battery, supports Rapid Charge (charge up to 80% in 1hr) with 65W AC adapter

Max Battery Life^[1]

- MobileMark® 2014: 11.5 hr (45Wh)
- MobileMark 2014: 9 hr (35Wh)

Notes:

- All battery life claims are approximate maximum and based on results using the MobileMark 2014, MobileMark 2018, JEITA 2.0, continuous 1080p video playback (with 150nits brightness and default volume level) or Google Power Load Test (PLT) battery-life benchmark tests. Actual battery life will vary and depends on many factors such as product configuration and usage, software use, wireless functionality, power management settings, and screen brightness. The maximum capacity of the battery will decrease with time and use.

Power Adapter

Power Adapter^[1]**

- 45W round tip (2-pin, wall-mount) AC adapter, 100-240V, 50-60Hz
- 65W round tip (2-pin, wall-mount) AC adapter, 100-240V, 50-60Hz

Notes:

- AC adapter offerings depend on the country.

DESIGN

Display

Display**^[1]

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio
14.0"	HD (1366x768)	None	TN	220 nits	Anti-glare	16:9
14.0"	FHD (1920x1080)	None	TN	220 nits	Anti-glare	16:9
14.0"	FHD (1920x1080)	None	IPS	250 nits	Anti-glare	16:9

Touchscreen

Non-touch

Notes:

- California Electronic Waste Recycling Fee

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product.

For more information, go to <https://www.calrecycle.ca.gov/Electronics/Consumer>

Input Device

Keyboard

6-row, multimedia Fn keys

Keyboard Backlight

Non-backlight

Touchpad

Buttonless Mylar® surface multi-touch touchpad, supports Precision TouchPad (PTP), 69 x 104 mm (2.72 x 4.09 inches)

Mechanical^[1]

Dimensions (WxDxH)

327.1 x 241 x 19.9 mm (12.88 x 9.49 x 0.78 inches)

Weight

Around 1.5 kg (3.31 lbs)

Case Color**

- Abyss blue
- Business black
- Cherry red
- Platinum grey

Surface Treatment**

- IMR (in-mold decoration by roller)
- Texture

Case Material

PC + ABS (top), PC + ABS (bottom)

Notes:

- The system dimensions and weight vary depending on configurations.

CONNECTIVITY

Network

Onboard Ethernet

No Ethernet

WLAN + Bluetooth®**^[1]

- 802.11ac 2x2 Wi-Fi® + Bluetooth 5.0, M.2 card
- Wi-Fi 6, 802.11ax 2x2 Wi-Fi + Bluetooth 5.0, M.2 card

Notes:

- Bluetooth 5.2 is hardware ready but may run at a lower version due to OS limitation

Ports^[1]

Standard Ports

- 1x USB 2.0
- 2x USB 3.2 Gen 1
- 1x HDMI 1.4b
- 1x Card reader
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Power connector

Notes:

1. The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.
USB 2.0: 480 Mbit/s;
USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;
USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;
USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;
Thunderbolt™ 3/4: 40 Gbit/s

SECURITY & PRIVACY

Security

Security Chip

Firmware TPM 2.0 integrated in SoC

Fingerprint Reader

- Touch style fingerprint reader on power button
- No fingerprint reader

BIOS Security

- Administrator password
- Power-on password
- Hard disk password

Other Security

Camera privacy shutter

SERVICE

Warranty

Base Warranty^{**[1]}

- 1-year depot service
- 1-year depot with 2-year system board service (Korea only)
- 2-year (1-yr battery) depot service
- 3-year (1-yr battery) depot service

Notes:

1. More information of warranty policy, please access <https://pcsupport.lenovo.com/warranty>

ENVIRONMENTAL

Operating Environment

Temperature^[1]

- At altitudes up to 2438 m (8,000 ft)
 - Operating: 5°C to 35°C (41°F to 95°F)
 - Storage: 5°C to 43°C (41°F to 109°F)
- At altitudes above 2438 m (8,000 ft)
 - Maximum temperature when operating under the unpressurized condition: 31.3°C (88°F)

Humidity

- Operating: 8% to 95% at wet-bulb temperature 23°C (73°F)

- Storage: 5% to 95% at wet-bulb temperature 27°C (81°F)

Altitude

Maximum altitude (without pressurization): 3048 m (10,000 ft)

Notes:

1. When you charge the battery, its temperature must be no lower than 10°C (50°F).

CERTIFICATIONS

Green Certifications

Green Certifications

- ENERGY STAR® 8.0
- ErP Lot 3
- RoHS compliant

- Feature with ** means that only one offering listed under the feature is configured on selected models.
- Feature with *** means that one or more offerings listed under the feature could be configured on selected models.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION “AS IS,” WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

