

ideapad FLEX 5 (14", 15")

ACCESSORIZE YOUR LIFESTYLE.

Proudly powered by AMD Ryzen™ 5000 Series Mobile Processors with Radeon™ Graphics, the 14" & 15" Lenovo™ **IdeaPad™** Flex 5 offers excellent all-around performance, graphics and productivity in a flexible device, built to be what you need it to be.




SUPREME PERFORMANCE. INFINITE POSSIBILITIES.

Run your most demanding apps all at once with the world's best mobile processors.* Experience lightning-fast responsiveness and hyper-efficient battery life thanks to industry-leading technology that keeps you productive and entertained from anywhere.

* 'Best Mobile Processors' is defined as having the highest multi-thread processing performance in each of four (4) classes of Ryzen 5000 series processors. Testing by AMD engineering using the the Cinebench R20 nT benchmark, measuring multithreaded performance of a Ryzen 9 5900HX processor engineering sample vs Core i9-10980HK, Ryzen 7 5800U processor engineering sample vs Core i7-1185G7 processor, the Ryzen 5 5600U processor engineering sample vs Core i5-1135G7 processor, and a Ryzen 3 5400U processor engineering sample vs Core i3-1115G4 processor. Performance may vary. C2M-1.

WHY YOU SHOULD BUY THE LENOVO IDEAPAD FLEX 5 (14", 15")



Reduce the clutter

A narrow bezel on 4 sides gives you more viewing area and less clutter to interfere with the task at hand, whether that's at work, or play, enjoy the most out of your screen with IPS panel technology and up to Full High Definition screens on the **IdeaPad** Flex 5.



Peek-proof privacy at your fingertips

Today's world is not a simple place, but that doesn't mean we can't build a simple solution to a complex problem. A physical shutter on the webcam ensures you keep out unwanted attention when you are concerned about your privacy.



Create till your heart's content

This isn't your typical laptop that you carry around—it's a fashion statement. The **IdeaPad** Flex 5 is built with a new level of attention to detail, making this machine soft and comfortable to the touch with a durable paint that creates a better user-experience and multiple color options, so you can find the one that best fits you.



From zero to 360° in a flash

The **IdeaPad** Flex 5 is designed for you to keep your ideas flowing, anywhere, anytime with the ability to multi-mode your laptop and use it in 'Laptop' mode for everyday computing, 'Tent' mode for sharing things, 'Stand' mode for binge-watching, or 'Tablet' mode for more intuitive interaction.

Lenovo™



WWW.LENOVO.COM

ideapad FLEX 5 (14", 15")

SPECIFICATIONS

Lenovo IdeaPad Flex 5 14ALC-05 | Lenovo IdeaPad Flex 5 15ALC-05*

PERFORMANCE

Processor

AMD Ryzen™ 7 5700U Mobile Processor
AMD Ryzen™ 5 5500U Mobile Processor
AMD Ryzen™ 3 5300U Mobile Processor

Operating System

Windows 10 Pro
Windows 10 Home
Windows 10 Home in S mode

Graphics

UMA: AMD Radeon™ Graphics (Integrated Graphics)

Memory

8GB / 16GB

Storage

SSD : 128GB / 256GB / 512GB
QLC 512GB

Camera

Slim Camera (3.0 mm) 720p with
Fixed-Focus CMOS

Audio

2 x 2W Speakers with Dolby Audio™,
Dual Microphone (DAX3, LVA)

Battery¹

IdeaPad Flex 5 - 14"

MobileMark® 2014 : Up to 12 Hours
1080p Video Playback : Up to 12 Hours
Rapid Charge Boost : 15 min. @ 2 Hours
(52.5Whr)

IdeaPad Flex 5 - 15"

MobileMark® 2014 : Up to 10 Hours
1080p Video Playback : Up to 10.5 Hours
Rapid Charge Boost : 15 min. @ 2 Hours
(52.5Whr)

DESIGN

Display

IdeaPad Flex 5 - 14"

14" FHD (1920 x 1080) IPS, 250 nits, 45% NTSC
14" FHD (1920 x 1080) TN, 220 nits, 45% NTSC

IdeaPad Flex 5 - 15"

15.6" FHD (1920 x 1080) IPS, 250 nits, 45% NTSC

4-Side Narrow Bezel

IdeaPad Flex 5 - 14"

Left/Right : 7 mm

Top : 9 mm

Bottom : 11.8 mm

IdeaPad Flex 5 - 15"

Left/Right : 6 mm

Top : 8 mm

Bottom : 12 mm

Dimensions (W x D x H)

IdeaPad Flex 5 - 14" (Plastic A-Cover)

(mm) : 321.5 x 217.5 x 17.9-20.9

(inches) : 12.66" x 8.56" x 0.7"-0.82"

IdeaPad Flex 5 - 15" (Plastic A-Cover)

(mm) : 357.6 x 237.9 x 17.9-20.9

(inches) : 14.01" x 9.37" x 0.7"-0.82"

Weight

IdeaPad Flex 5 - 14"
Starting at 1500 g (3.3 lbs)

IdeaPad Flex 5 - 15"
Starting at 1800 g (4 lbs)

Hinge

-360°

Colors

Platinum Grey
Graphite Grey
Abyss Blue²

CONNECTIVITY

WLAN

2x2 WiFi 6 (802.11 ax)
2x2 WiFi 5 (802.11 ac)

Bluetooth®


Bluetooth® 5.0

I/O (Input/Output) Ports⁴

2 x USB 3.1 Gen 1⁵ (Type-A)
(one supports USB charging)
1 x USB 3.1 Gen 1⁵ (Type-C™) with PD
HDMI™ 1.4b
4-in-1 Card Reader
3.5 mm Microphone & Earphone
Combo Jack
DC Port (round)

PRELOADED SOFTWARE

- McAfee LiveSafe™
- Microsoft Office
- Lenovo Utility
- Lenovo Vantage
- Mirkat



Lenovo™

¹ All battery life claims are approximate and based on two methods of testing: MobileMark® 2014 battery life benchmark and continuous 1080p video playback on the latest update of Windows 10 (with 150 nits brightness and default volume level). Actual battery life will vary and depends on many factors such as product configuration and usage, software use, wireless functionality, power management settings, and screen brightness. The maximum capacity of the battery will decrease with time and use.

² Available only for 14" model.

³ Numpad is available only for 15" model.

⁴ Not all configurations will allow for these I/O ports.

⁵ The actual transfer speed of the USB 3.1 Gen 1 will vary and, depending on many factors, such as the processing capability of host and peripheral devices, file attributes and other factors related to system configuration and your operating environments, will be slower than a speed of 5 Gbit/s.

WOW FEATURES

Standard

Privacy Shutter, Windows Cortana (NF),
Touch Display with Direct Bonding + OGS/
GFF, 10-Touch Numpad on Keyboard⁵

Optional

Alexa, Backlit Keyboard, Fingerprint Reader,
Lenovo Digital Pen (supported), LVA


OPTIONS & ACCESSORIES



Lenovo 600
Bluetooth®
Silent Mouse



Lenovo 15.6"
Laptop Urban
Backpack B530



Lenovo 65W
USB-C AC
Travel Adapter

* Example of Lenovo
IdeaPad Flex catalogue
naming convention



LENOVO SERVICES

Warranty Upgrades - On-site / In-Home Service

Maximizes PC uptime and productivity by providing convenient, fast repair services in your own home.

Accidental Damage Protection

Avoid the hassles of unexpected repair costs. Provides coverage for non-warranted damage incurred under normal operating conditions, such as minor spills, drops or damage to the integrated screen.

Warranty Extensions (1-to-3 Years Total Duration)

This fixed-term, fixed-cost service helps accurately budget for PC expenses, protect your valuable investment and potentially lower the cost of ownership over time.



WWW.LENOVO.COM



Lenovo reserves the right to alter product offerings and specifications at any time, without notice. Lenovo makes every effort to ensure accuracy of all information but is not liable or responsible for any editorial, photographic or typographic errors. All images are for illustration purposes only. For full Lenovo product, service and warranty specifications visit www.lenovo.com. Lenovo makes no representations or warranties regarding third party products or services. **Trademarks:** The following are trademarks or registered trademarks of Lenovo: Lenovo, the Lenovo logo, ideapad, ideacentre, yoga and yoga home. Microsoft, Windows and Vista are registered trademarks of Microsoft Corporation. Battery life (and recharge times) will vary based on many factors including system settings and usage. Visit www.lenovo.com/lenovo/us/en/safecomp/ periodically for the latest information on safe and effective computing. ©2021 Lenovo. All rights reserved.