

ideapad 1

YOUR DAILY COMPUTING COMPANION.

The Lenovo™ **IdeaPad™ 1** is built with reliable performance, FHD display and storage options to help you handle daily tasks easily.



WHY YOU SHOULD BUY THE LENOVO IDEAPAD 1



Wider view
less distraction

IdeaPad 1 features an up to FHD display, so you can view your content with deeper and more intense clarity. If you're looking for bigger and wider screens, the 14" option is designed with 2-sided narrow bezels that afford you increased screen area and less clutter.



Experience
crystal-clear sound

Dolby Audio™ delivers crystal-clear audio whether you're watching a video or streaming music. With the built-in dual stereo speaker, you're sure to fall in love with what you hear on the **IdeaPad 1**.



Be efficient. Be productive.

Discover a new world of quick apps, beautiful entertainment and long-lasting battery life with AMD Athlon™ Silver 3050e Mobile Processor. Count on a laptop that brings incredible performance and speed to everything you do - from completing everyday tasks to streaming your favorite movies, on the go or at home.



Your travel
companion

For those looking for an on-the-go laptop, the **IdeaPad 1** is your best choice. The 14" **IdeaPad 1** starts at just 1.4 kg, while the 11" model starts at a feather-light 1.2 kg. With all-day battery life, you can take your **IdeaPad 1** anywhere and do more.



Secure your data
your way

Keep your data secure and safe with reliable options including hybrid storage.



WWW.LENOVO.COM

Lenovo™

ideapad 1

SPECIFICATIONS

Lenovo IdeaPad 1 11"* , Lenovo IdeaPad 1 14"*

PERFORMANCE

Processor

AMD Athlon™ Silver 3050e Mobile Processor
AMD 3020e Mobile Processor

Operating System

Windows 10 Pro
Windows 10 Home
Windows 10 S

Graphics

AMD Radeon™ Graphics (Integrated)

Memory

4 GB

Storage

IdeaPad 1 11"

eMMC : 32 GB / 64 GB
M.2 PCIe SSD : 128 GB / 256 GB

IdeaPad 1 14"

eMMC : 32 GB / 64 GB
M.2 PCIe SSD : 128 GB / 256 GB

Audio

2 x 1.5W Speakers with Dolby Audio™

Battery¹

IdeaPad 1 11"

MobileMark® 2018 : Up to 7.3 Hours

Local 1080p Video Playback : Up to 9 Hours

IdeaPad 1 14"

MobileMark® 2018 : Up to 7.3 Hours

Local 1080p Video Playback : Up to 9 Hours

DESIGN

Display

IdeaPad 1 11"

11" HD (1366 x 768) TN, Anti-Glare, 250 nits, 45% NTSC

IdeaPad 1 14"

14" FHD (1920 x 1080) TN, Anti-Glare, 220 nits, 45% NTSC, 2-sided Narrow Bezel
14" HD (1366 x 768) TN, Anti-Glare, 220 nits, 45% NTSC, 2-sided Narrow Bezel

Dimensions (W x D x H)

IdeaPad 1 11"

(mm) : 288 x 200 x 18.8-19.9
(inches) : 11.33" x 7.87" x 0.74"-0.78"

IdeaPad 1 14"

(mm) : 327.1 x 235 x 18.8-19.9
(inches) : 12.87" x 9.25" x 0.74"-0.78"

Net Weight

IdeaPad 1 11"

Starting at 2.64 lbs (1.2 kg)

IdeaPad 1 14"

Starting at 3.08 lbs (1.4 kg)

Colors

Platinum Grey

Ice Blue

Flame Orange²

WOW Features

- Dual Microphone Camera with 0.3M
- Office 365 (1 year)

CONNECTIVITY

WLAN

2 x 2 WiFi 802.11 ac

Bluetooth®

Bluetooth® 4.2

I/O (Input/Output) Ports

2 x USB 3.0³
1 x microSD™ Card Reader
1 x HDMI™ 1.4
1 x Microphone/Earphone Combo
1 x Power DC Jack

PRELOADED SOFTWARE

- Lenovo Vantage
- Microsoft Office 2019

¹ All battery life claims are approximate and based on two methods of testing: MobileMark® 2014 battery life benchmark and continuous 1080p video playback on the latest update of Windows 10 (with 150 nits brightness and default volume level). Actual battery life will vary and depends on many factors such as product configuration and usage, software use, wireless functionality, power management settings, and screen brightness. The maximum capacity of the battery will decrease with time and use.

² Available only for 14".

³ The actual transfer speed of the USB 3.0 will vary and, depending on many factors, such as the processing capability of host and peripheral devices, file attributes and other factors related to system configuration and your operating environments, will be slower than a speed of 5 Gbit/s.




OPTIONS & ACCESSORIES



Lenovo 530
Wireless Mouse



Lenovo Urban
Sleeve Case



Lenovo 100
In-Ear Headphone

LENOVO SERVICES

Warranty Upgrades - On-site / In-Home Service

Maximizes PC uptime and productivity by providing convenient, fast repair services in your own home.


Accidental Damage Protection

Avoid the hassles of unexpected repair costs. Provides coverage for non-warranted damage incurred under normal operating conditions, such as minor spills, drops or damage to the integrated screen.

Warranty Extensions (1-to-3 Years Total Duration)

This fixed-term, fixed-cost service helps accurately budget for PC expenses, protect your valuable investment and potentially lower the cost of ownership over time.

* Example of Lenovo IdeaPad catalogue naming convention



WWW.LENOVO.COM



Lenovo reserves the right to alter product offerings and specifications at any time, without notice. Lenovo makes every effort to ensure accuracy of all information but is not liable or responsible for any editorial, photographic or typographic errors. All images are for illustration purposes only. For full Lenovo product, service and warranty specifications visit www.lenovo.com. Lenovo makes no representations or warranties regarding third party products or services. **Trademarks:** The following are trademarks or registered trademarks of Lenovo: Lenovo, the Lenovo logo, ideapad, ideacentre, yoga and yoga home. Microsoft, Windows and Vista are registered trademarks of Microsoft Corporation. Battery life (and recharge times) will vary based on many factors including system settings and usage. Visit www.lenovo.com/lenovo/us/en/safecomp/ periodically for the latest information on safe and effective computing. ©2020 Lenovo. All rights reserved.

Lenovo™