

NetWay4E1WP

4-port Hardened PoE Switch with Power Supply/Charger;
NEMA4/4X, IP66 rated Outdoor enclosure

Altronix NetWay4E1WP Outdoor PoE+ Hardened Switch provides a 1Gb SFP port and four (4) PoE+ (30W) ports. Cameras/edge devices may be located up to 100m from the unit.



Specifications

Input

- Voltage: 115VAC, 60Hz, 2.5A or 230VAC, 50/60Hz, 1.3A.
- Fusing: 5A/250V.

Power Output

Maximum Power:

- Four (4) 10/100/1000 Mbps.
- PoE/PoE+ (up to 30W) ports.
- IEEE 802.3af (15W) and IEEE 802.3at (30W) compliant.
- 120W total power.
- Integral surge protection.

Fiber Port

- One (1) Gigabit SFP (Fiber) port.

Back-up Battery (not included)

- Type: Sealed lead acid or gel type.
- Failover: Upon AC loss, instantaneous.

Indicators (LED)

- Individual PoE On LEDs for each port.

Agency Listings

CE Compliant

Accessories

Name	Description
P1AB2K	Small Form-Factor Pluggable (SFP) Single-Mode Transceiver Kit
P1GCE	Small Form-Factor Pluggable (SFP) Copper Transceiver
P1MM	Small Form-Factor Pluggable (SFP) Multi-Mode Transceiver
P1SM10	Small Form-Factor Pluggable (SFP) Single Mode Transceiver
PMK1	Pole Mount Kit, For Outdoor Enclosures
WG1	NEMA Rated Wire Gland Inlets

- Individual IP Link status, 10/100Base-T/active LEDs for each port.
- ALOS LED indicates fiber connection for SFP port.
- Heartbeat LED indicates proper operation of the unit.

Temperature

Operating:

- 60W: - 40° C to 75° C (- 40° F to 167° F).
- 75W: - 40° C to 70° C (- 40° F to 158° F).
- 100W: - 40° C to 55° C (- 40° F to 131° F).
- 120W: - 40° C to 45° C (- 40° F to 113° F).
- Storage: - 40° C to 85° C (- 40° F to 185° F).
- Relative Humidity: 85% +/- 5%.
- BTU/Hr. (approx.): 61 BTU/Hr.

Operating Altitude

- - 304.8 to 2,000m.

Dimensions & Weight

Enclosure:

NEMA 4/4X, IP66-11 Rated enclosure for outdoor use.

Dimensions 11.31"W x 13.31"H x 5.59"D (287 mm W x 338 mm H x 142 mm D).

Weights (approximate):

Product Weight: 10.32 Lbs. (4.68 kg).

Shipping Weight: 11.7 Lbs. (5.3 kg).