

Safety Data Sheet
acc. to OSHA HCS

Printing date 03/04/2021

Reviewed on 07/30/2020

1 Identification

- **Product identifier**
- **Trade name:** Elevate Imaging Remanufactured Replacement Cartridge for HP® CE251A Cyan
- **Article number:** AHWE2512B0RC
- **Application of the substance / the mixture** Printing inks
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
Static Control Components Inc.
P.O. Box 152
Sanford, North Carolina, 27331
info@scc-inc.com
- **Information department:** Product Safety Department
- **Emergency telephone number:**
During Normal Operating Hours: 919-774-3808
Emergency Telephone Number: 1-919-770-7984 or 1-919-770-6019

2 Hazard(s) identification

- **Classification of the substance or mixture**
Combustible Dust May form combustible dust concentrations in air.
- **Label elements**
- **GHS label elements** The product is classified and labeled according to the Globally Harmonized System (GHS).
- **Hazard pictograms** Void
- **Signal word** Warning
- **Hazard statements**
May form combustible dust concentrations in air.
- **Classification system:**
- **NFPA ratings (scale 0 - 4)**
 Health = 1
Fire = 1
Reactivity = 0
- **HMIS-ratings (scale 0 - 4)**
 HEALTH 1 Health = 1
FIRE 1 Fire = 1
REACTIVITY 0 Reactivity = 0
- **Other hazards**
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

3 Composition/information on ingredients

- **Chemical characterization:** Mixtures
- **Description:** Resin mixture

(Contd. on page 2)

Safety Data Sheet
acc. to OSHA HCS

Printing date 03/04/2021

Reviewed on 07/30/2020

Trade name: Elevate Imaging Remanufactured Replacement Cartridge for HP® CE251A Cyan

(Contd. of page 1)

· **Dangerous components:** Void· **Non-hazardous components**

292629-36-8	Resin	>50-≤100%
9002-88-4	Polyethylene low density	>10-≤25%
147-14-8	Phthalocyanine Blue	>2.5-≤10%

4 First-aid measures· **Description of first aid measures**· **General information:** No special measures required.· **After inhalation:** Supply fresh air; consult doctor in case of complaints.· **After skin contact:**

Immediately wash with water and soap and rinse thoroughly.

Generally the product does not irritate the skin.

· **After eye contact:** Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.· **After swallowing:** Drink copious amounts of water and provide fresh air. Immediately call a doctor.· **Information for doctor:**· **Most important symptoms and effects, both acute and delayed** No further relevant information available.· **Indication of any immediate medical attention and special treatment needed** No further relevant information available.**5 Fire-fighting measures**· **Extinguishing media**· **Suitable extinguishing agents:** Use fire fighting measures that suit the environment.· **For safety reasons unsuitable extinguishing agents:** No Information Available· **Special hazards arising from the substance or mixture**

Like most finely divided organic powders, toner dust may form an explosive mixture in air.

· **Advice for firefighters**· **Protective equipment:** Wear self-contained respiratory protective device.**6 Accidental release measures**· **Personal precautions, protective equipment and emergency procedures**

Wear protective equipment. Keep unprotected persons away.

· **Environmental precautions:** Do not allow to enter sewers/ surface or ground water.· **Methods and material for containment and cleaning up:**

Vacuum or sweep the material into a sealed container. If a vacuum is used it must be dust explosion-proof. Dispose of in compliance with national, state, regional or provincial regulations.

· **Reference to other sections**

No dangerous substances are released.

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

(Contd. on page 3)

Safety Data Sheet

acc. to OSHA HCS

Printing date 03/04/2021

Reviewed on 07/30/2020

Trade name: Elevate Imaging Remanufactured Replacement Cartridge for HP® CE251A Cyan

(Contd. of page 2)

· Protective Action Criteria for Chemicals
· PAC-1:

9002-88-4	Polyethylene low density	16 mg/m ³
-----------	--------------------------	----------------------

· PAC-2:

9002-88-4	Polyethylene low density	170 mg/m ³
-----------	--------------------------	-----------------------

· PAC-3:

9002-88-4	Polyethylene low density	1,000 mg/m ³
-----------	--------------------------	-------------------------

7 Handling and storage

· Handling:
· Precautions for safe handling

- No special measures required.
- Store in cool, dry place in tightly closed receptacles.
- Keep away from heat and direct sunlight.
- No special precautions are necessary if used correctly.
- Use only in well ventilated areas.

· Information about protection against explosions and fires: Keep ignition sources away - Do not smoke.
· Conditions for safe storage, including any incompatibilities
· Storage:
· Requirements to be met by storerooms and receptacles:

- Store in a cool location.
- Store only in the original receptacle.

· Information about storage in one common storage facility:

- Do not store together with oxidizing and acidic materials as well as heavy-metal compounds.

· Further information about storage conditions:

- Store in cool, dry conditions in well sealed receptacles.
- Protect from heat and direct sunlight.
- Protect from humidity and water.

· Specific end use(s) No further relevant information available.

8 Exposure controls/personal protection

· Additional information about design of technical systems: No further data; see item 7.
· Control parameters
· Components with limit values that require monitoring at the workplace:

- The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.

· Additional Occupational Exposure Limit Values for possible hazards during processing:

USA OSHA (TWA/PEL): 15 mg/m³ (Total Dust), 5 mg/m³ (Respirable Fraction)

ACGIH (TWA/TLV): 10 mg/m³ (Inhalable Particulate), 3 mg/m³ (Respirable Particulate)

Amorphous Silica: USA OSHA (TWA/PEL): 20mppcf 80 mg/m³, ACGIH (TWA/TLV): 10 mg/m³

TRGS 900 (Luftgrenzwert): 10 mg/m³ (Einatembare partikel)). 3 mg/m³ (Alveolengängige fraktion)

(Contd. on page 4)

Safety Data Sheet

acc. to OSHA HCS

Printing date 03/04/2021

Reviewed on 07/30/2020

Trade name: Elevate Imaging Remanufactured Replacement Cartridge for HP® CE251A Cyan

(Contd. of page 3)

UK WEL: 10 mg/m³ (Respirable Dust) 5 mg/m³ (Inhalible Dust)

· **Additional information:** The lists that were valid during the creation were used as basis.

· **Exposure controls**

· **Personal protective equipment:**

· **General protective and hygienic measures:**

Wash hands before breaks and at the end of work.

Do not inhale dust / smoke / mist.

· **Protection of hands:**

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:** Safety glasses

9 Physical and chemical properties

· **Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

Form: Powder

Color: Blue

· **Odor:** Odorless

· **Odor threshold:** Not determined.

· **pH-value:** Not applicable.

· **Change in condition**

Melting point/Melting range: Undetermined.

Boiling point/Boiling range: Undetermined.

· **Flash point:** Not applicable.

· **Flammability (solid, gaseous):** Not determined.

· **Decomposition temperature:** Not determined.

· **Auto igniting:** Product is not selfigniting.

· **Danger of explosion:** Product does not present an explosion hazard in its original state.

· **Explosion limits:**

Lower: 0.0 Vol %

Upper: 0.0 Vol %

· **Vapor pressure:** Not applicable.

· **Density at 20 °C (68 °F):** 1.3 g/cm³ (10.8485 lbs/gal)

SG: 1.3-1.8

· **Relative density** Not determined.

· **Vapor density** Not applicable.

(Contd. on page 5)

Safety Data Sheet

acc. to OSHA HCS

Printing date 03/04/2021

Reviewed on 07/30/2020

Trade name: Elevate Imaging Remanufactured Replacement Cartridge for HP® CE251A Cyan

(Contd. of page 4)

- | | |
|---|--|
| · Evaporation rate | Not applicable. |
| · Solubility in / Miscibility with Water: | Insoluble. |
| · Partition coefficient (n-octanol/water): | Not determined. |
| · Viscosity: | |
| Dynamic: | Not applicable. |
| Kinematic: | Not applicable. |
| · Solvent content: | |
| VOC content: | 0.00 % |
| · Other information | No further relevant information available. |

10 Stability and reactivity

- **Reactivity** Non reactive.
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**
- **Primary irritant effect:**
- **on the skin:** No toxic irritating effect, according to Directive 67/548/EEC or Directive 199/45/EC.
- **on the eye:** No toxic irritating effect, according to Directive 67/548/EEC or Directive 199/45/EC.
- **Sensitization:** No toxic sensitizing effects known, according to EU Directive 67/548/EEC or Directive 199/45/EC.
- **Other information (about experimental toxicology):**
Mutagenicity : Ames test Negative (According to the test result of similar composition.)
- **Additional toxicological information:**
The product is not subject to classification according to internally approved calculation methods for preparations:
When used and handled according to specifications, the product does not have any harmful effects according to our experience and the information provided to us.

- **Carcinogenic categories**

· IARC (International Agency for Research on Cancer)	
9002-88-4 Polyethylene low density	3

· NTP (National Toxicology Program)	
None of the ingredients is listed.	

(Contd. on page 6)

US

Safety Data Sheet

acc. to OSHA HCS

Printing date 03/04/2021

Reviewed on 07/30/2020

Trade name: Elevate Imaging Remanufactured Replacement Cartridge for HP® CE251A Cyan

(Contd. of page 5)

· OSHA-Ca (Occupational Safety & Health Administration)

None of the ingredients is listed.

12 Ecological information

- **Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **Persistence and degradability** No further relevant information available.
- **Behavior in environmental systems:**
- **Bioaccumulative potential** No further relevant information available.
- **Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**
Water hazard class 1 (Self-assessment): slightly hazardous for water
Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

13 Disposal considerations

- **Waste treatment methods**
- **Recommendation:** Smaller quantities can be disposed of with household waste.
- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to official regulations.

14 Transport information

- | | |
|-------------------------------------|---|
| · UN-Number | Not a regulated material under the United States DOT, IMDG, ADR, RID, or ICAO/IATA. |
| · DOT, ADR, ADN, IMDG, IATA | Void |
| · UN proper shipping name | Not a regulated material under the United States DOT, IMDG, ADR, RID, or ICAO/IATA |
| · DOT, ADR, ADN, IMDG, IATA | Void |
| · Transport hazard class(es) | Not a regulated material under the United States DOT, IMDG, ADR, RID, or ICAO/IATA. |
| · DOT, ADR, ADN, IMDG, IATA | |
| · Class | Void |
| · Packing group | Not a regulated material under the United States DOT, IMDG, ADR, RID, or ICAO/IATA. |
| · DOT, ADR, IMDG, IATA | Void |

(Contd. on page 7)

Safety Data Sheet

acc. to OSHA HCS

Printing date 03/04/2021

Reviewed on 07/30/2020

Trade name: Elevate Imaging Remanufactured Replacement Cartridge for HP® CE251A Cyan

(Contd. of page 6)

- | | |
|--|-----------------|
| · Environmental hazards: | |
| · Marine pollutant: | No |
| · Special precautions for user | Not applicable. |
| · Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code | Not applicable. |
| · UN "Model Regulation": | Void |

15 Regulatory information

- **Safety, health and environmental regulations/legislation specific for the substance or mixture**
No further relevant information available.

- **Sara**

- **Section 355 (extremely hazardous substances):**

None of the ingredients is listed.

- **Section 313 (Specific toxic chemical listings):**

None of the ingredients is listed.

- **TSCA (Toxic Substances Control Act):**

9002-88-4	Polyethylene low density	ACTIVE
147-14-8	Phthalocyanine Blue	ACTIVE

- **Hazardous Air Pollutants**

None of the ingredients is listed.

- **Proposition 65**

- **Chemicals known to cause cancer:**

None of the ingredients is listed.

- **Chemicals known to cause reproductive toxicity for females:**

None of the ingredients is listed.

- **Chemicals known to cause reproductive toxicity for males:**

None of the ingredients is listed.

- **Chemicals known to cause developmental toxicity:**

None of the ingredients is listed.

- **Carcinogenic categories**

- **EPA (Environmental Protection Agency)**

None of the ingredients is listed.

- **TLV (Threshold Limit Value established by ACGIH)**

None of the ingredients is listed.

- **NIOSH-Ca (National Institute for Occupational Safety and Health)**

None of the ingredients is listed.

- **GHS label elements** The product is classified and labeled according to the Globally Harmonized System (GHS).

- **Hazard pictograms** Void

(Contd. on page 8)

Safety Data Sheet
acc. to OSHA HCS

Printing date 03/04/2021

Reviewed on 07/30/2020

Trade name: Elevate Imaging Remanufactured Replacement Cartridge for HP® CE251A Cyan

(Contd. of page 7)

- **Signal word** Warning
- **Hazard statements**
May form combustible dust concentrations in air.
- **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Date of preparation / last revision** 03/04/2021 / -
- **Abbreviations and acronyms:**
ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)
IMDG: International Maritime Code for Dangerous Goods
DOT: US Department of Transportation
IATA: International Air Transport Association
ACGIH: American Conference of Governmental Industrial Hygienists
EINECS: European Inventory of Existing Commercial Chemical Substances
ELINCS: European List of Notified Chemical Substances
CAS: Chemical Abstracts Service (division of the American Chemical Society)
NFPA: National Fire Protection Association (USA)
HMIS: Hazardous Materials Identification System (USA)
VOC: Volatile Organic Compounds (USA, EU)
PBT: Persistent, Bioaccumulative and Toxic
vPvB: very Persistent and very Bioaccumulative
NIOSH: National Institute for Occupational Safety
OSHA: Occupational Safety & Health
TLV: Threshold Limit Value
PEL: Permissible Exposure Limit
REL: Recommended Exposure Limit
- *** Data compared to the previous version altered.**
No changes to the Material Safety Data Sheet, all sections are current as the date of print seen above describes.