

## OVERVIEW



1. Power button	6. USB-C 3.2 Gen 1
2. Volume button	7. USB 3.2 Gen 1 (Always On)
3. USB 3.2 Gen 1	8. HDMI 1.4b
4. MicroSD card reader	9. Headphone / microphone combo jack (3.5mm)
5. Kensington Nano Security Slot	10. Pen slot

## PERFORMANCE

### Processor

#### Processor Family

Intel® Celeron® or Intel Pentium® Processor

#### Processor\*\*

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Memory Support	Processor Graphics
Celeron N5100	4	4	1.1GHz	2.8GHz	4MB L3	LPDDR4x-2933	Intel UHD Graphics
Pentium Silver N6000	4	4	1.1GHz	3.3GHz	4MB L3	LPDDR4x-2933	Intel UHD Graphics

### Operating System

#### Operating System\*\*

- Windows® 11 Pro 64
- Windows 11 Home 64
- Windows 11 Pro (National Academic License)
- Windows 11 SE 64
- Windows 11 DG Windows 10 Pro 64
- Windows 11 DG Windows 10 Pro 64 (National Academic License)
- Windows 10 Pro 64
- Windows 10 Pro (National Academic License)
- Windows 10 Home 64
- No operating system

### Graphics

#### Graphics

Graphics	Type	Memory	Key Features
Intel UHD Graphics	Integrated	Shared	DirectX® 12

### Monitor Support

#### Monitor Support

Supports up to 3 independent displays (native display and 2 external monitors via HDMI® and USB-C)

- HDMI supports up to 4K@30Hz
- USB-C supports up to 4K@60Hz

### Chipset

#### Chipset

Intel SoC (System on Chip) platform

### Memory

#### Max Memory<sup>[1]</sup>

- 4GB soldered memory, not upgradable
- 8GB soldered memory, not upgradable

#### Memory Slots

Memory soldered to systemboard, no slots, dual-channel

#### Memory Type<sup>[2]</sup>

LPDDR4x-2933

#### Notes:

1. The max memory is based on the test results with current Lenovo® memory offerings. The system may support more memory as the technology develops.
2. Installed memory is actually 4266MHz but run at 2933MHz due to processor limitation

### Storage

#### Storage Support<sup>[1][2]</sup>

- One drive, up to 256GB M.2 2242 SSD

- 64GB eMMC 5.1 on systemboard
- 128GB eMMC 5.1 on systemboard

**Storage Slot**

- eMMC on systemboard, no slots (eMMC model)
- One M.2 2242 PCIe® Gen 3x4 slot, supports M.2 2242 SSD (M.2 SSD model)

**Storage Type\*\***

Disk Type	Interface	RPM	Offering	Security
Flash Memory	eMMC 5.1	-	64GB / 128GB	-
M.2 2242 SSD	PCIe NVMe®, PCIe 3.0 x4	-	128GB / 256GB	-

Notes:

1. The storage capacity supported is based on the test results with current Lenovo storage offerings. The system may support larger storage as the technology develops.
2. System has one eMMC on systemboard or one M.2 2242 SSD exclusively

**Removable Storage**

**Optical**

None

**Card Reader**

MicroSD card reader

**Multi-Media**

**Audio Chip**

High Definition (HD) Audio, Realtek® ALC3287 codec

**Speakers**

Stereo speakers, 2W x2

**Microphone**

Single microphone

**Camera\*\***

- Front 720p, with privacy shutter, fixed focus
- Front 720p, with privacy shutter, fixed focus; rear 5.0-megapixel, autofocus

**Battery**

**Battery**

Integrated Li-Polymer 47Wh battery, supports Rapid Charge (charge up to 80% in 1hr) with 65W AC adapter

**Max Battery Life<sup>[1]</sup>**

MobileMark® 2018: 9.7 hr

Notes:

1. All battery life claims are approximate maximum and based on results using the MobileMark 2014, MobileMark 2018, JEITA 2.0, continuous 1080p video playback (with 150nits brightness and default volume level) or Google Power Load Test (PLT) battery-life benchmark tests. Actual battery life will vary and depends on many factors such as product configuration and usage, software use, wireless functionality, power management settings, and screen brightness. The maximum capacity of the battery will decrease with time and use.

**Power Adapter**

**Power Adapter\*\*<sup>[1]</sup>**

- 45W USB-C (3-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
- 65W USB-C (2-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz
- 65W USB-C (3-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz

Notes:

1. AC adapter offerings depend on the country.

**DESIGN**

## Display

### Display<sup>[1]</sup>

Size	Resolution	Touch	Type	Brightness	Surface	Aspect Ratio	Contrast Ratio	Color Gamut	Viewing Angle	Key Features
11.6"	HD (1366x768)	Multi-touch	IPS	250 nits	Glossy, anti-fingerprint	16:9	500:1	50% NTSC	170°	Corning® Gorilla® Glass

### Touchscreen

GF2 or OGM (One Glass Metal mesh) Direct Bonding, capacitive-type multi-touch, supports 10-point touch

#### Notes:

- California Electronic Waste Recycling Fee  
In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to <https://www.calrecycle.ca.gov/Electronics/Consumer>

## Multi-mode

### Multi-mode

Laptop, tent, stand, and tablet modes supported by 360° hinge

## Input Device

### Pen

- Lenovo Integrated Pen, on-board rechargeable
- No support

### Keyboard

6-row, spill-resistant, Anti-pry Key Caps

### Keyboard Backlight

No support

### Touchpad

Buttonless Mylar® surface multi-touch touchpad, supports Precision TouchPad (PTP)

## Mechanical<sup>[1]</sup>

### Dimensions (WxDxH)

289.6 x 202.4 x 19.9 mm (11.4 x 7.97 x 0.78 inches)

### Weight

1.33 kg (2.93 lbs)

### Case Color

Abyss blue

### Surface Treatment

Texture

### Case Material

PC + ABS covered with rubber bumper (top), PC + ABS (bottom)

### Others<sup>[2]</sup>

Buttons: power key, volume key

#### Notes:

- The system dimensions and weight vary depending on configurations.
- Power key and volume key are on the right side.

## CONNECTIVITY

## Network

### Onboard Ethernet

No Ethernet

### WLAN + Bluetooth<sup>[1]</sup>

Intel Wi-Fi® 6 AX201, 802.11ax 2x2 Wi-Fi + Bluetooth 5.2, M.2 Card

#### Notes:

1. Wi-Fi 6 full features might be limited by country-level restrictions.  
Bluetooth 5.2 is supported with driver version 22.30 and later.

## Ports<sup>[1]</sup>

### Standard Ports

- 1x USB 3.2 Gen 1
- 1x USB 3.2 Gen 1 (Always On)
- 1x USB-C 3.2 Gen 1 (support data transfer, Power Delivery 3.0, and DisplayPort™ 1.2)
- 1x HDMI 1.4b
- 1x Card reader
- 1x Headphone / microphone combo jack (3.5mm)

#### Notes:

1. The transfer speed of following ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.  
USB 2.0: 480 Mbit/s;  
USB 3.2 Gen 1 (SuperSpeed USB 5Gbps, formerly USB 3.0 / USB 3.1 Gen 1): 5 Gbit/s;  
USB 3.2 Gen 2 (SuperSpeed USB 10Gbps, formerly USB 3.1 Gen 2): 10 Gbit/s;  
USB 3.2 Gen 2x2 (SuperSpeed USB 20Gbps): 20 Gbit/s;  
Thunderbolt™ 3/4: 40 Gbit/s;  
FireWire 400: 400 Mbit/s;  
FireWire 800: 800 Mbit/s

## SECURITY & PRIVACY

### Security

#### Security Chip

Discrete TPM 2.0, TCG certified

#### Physical Locks

Kensington® Nano Security Slot

#### Fingerprint Reader

No fingerprint reader

#### BIOS Security

- Power-on password
- Supervisor password
- Hard disk password

#### Other Security

Camera privacy shutter

## SERVICE

### Warranty

#### Base Warranty\*\*<sup>[1]</sup>

- 1-year mail-in service
- 1-year depot service

#### Notes:

1. More information of warranty policy, please access <https://pcsupport.lenovo.com/warranty>

## ENVIRONMENTAL

### Operating Environment

#### Temperature<sup>[1]</sup>

- Operating: 5°C (41°F) to 35°C (95°F)

- Storage: 5°C (41°F) to 43°C (109°F)

## Humidity

- Operating: 8% to 95% at wet-bulb temperature 23°C (73°F)
- Storage: 5% to 95% at wet-bulb temperature 27°C (81°F)

## Altitude

Maximum altitude (without pressurization): 3048 m (10,000 ft)

## Notes:

1. When you charge the battery, its temperature must be no lower than 10°C (50°F).

# CERTIFICATIONS

## Green Certifications

### Green Certifications

- EPEAT™ Silver
- ENERGY STAR® 8.0
- ErP Lot 3
- TCO Certified 8.0
- RoHS compliant

## Other Certifications

### Mil-Spec Test

MIL-STD-810H military test passed

- Feature with \*\* means that only one offering listed under the feature is configured on selected models.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. **LENOVO PROVIDES THIS PUBLICATION “AS IS,” WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.



intel



intel



intel



intel



intel



intel