

OVERVIEW



1. USB-C (USB 10Gbps), with USB PD 3.0 & DP 1.4	5. Power button
2. USB-A (USB 5Gbps)	6. Volume button
3. Headphone / microphone combo jack (3.5mm)	7. USB-C (USB 10Gbps), with USB PD 3.0 & DP 1.4
4. microSD card reader	8. Kensington Nano Security Slot

PERFORMANCE

Processor

Processor Family

Intel® Pentium® or 12th Generation Intel® Core™ i3 / i5 Processor

Processor**

Processor Name	Cores	Threads	Base Frequency	Max Frequency	Cache	Processor Graphics
Pentium® Gold 8505	5 (1 P-core + 4 E-core)	6	P-core 1.2GHz / E-core 0.9GHz	P-core 4.4GHz / E-core 3.3GHz	8MB	Intel® UHD Graphics
Core i3-1215U	6 (2 P-core + 4 E-core)	8	P-core 1.2GHz / E-core 0.9GHz	P-core 4.4GHz / E-core 3.3GHz	10MB	Intel® UHD Graphics
Core i5-1235U	10 (2 P-core + 8 E-core)	12	P-core 1.3GHz / E-core 0.9GHz	P-core 4.4GHz / E-core 3.3GHz	12MB	Intel® Iris® Xe Graphics

Operating System

Operating System

ChromeOS

Graphics

Graphics**

Graphics	Type	Memory	Key Features
Intel® UHD Graphics	Integrated	Shared	DirectX® 12.1
Intel® Iris® Xe Graphics	Integrated	Shared	DirectX® 12.1

Monitor Support

Monitor Support

Supports up to 3 independent displays (native display and 2 external monitors via USB-C®)

- USB-C® supports up to 3840x2160@60Hz

Chipset

Chipset

Intel® SoC (System on Chip) platform

Memory

Max Memory

- 4GB soldered memory, not upgradable
- 8GB soldered memory, not upgradable

Memory Slots**

- Memory soldered to systemboard, no slots, single-channel (4GB models)
- Memory soldered to systemboard, no slots, dual-channel (8GB models)

Memory Type

LPDDR4x-4266

Storage

Storage Support^{[1][2]}

- One drive, up to 128GB eMMC 5.1 storage card
- One drive, up to 512GB M.2 2242 SSD

Storage Slot

One M.2 2242 PCIe® 4.0 x4 slot, supports M.2 2242 SSD or eMMC storage card (PCIe® 1x1)

Storage Type**

Disk Type	Interface	Offering
-----------	-----------	----------

Flash Memory	eMMC 5.1	64GB / 128GB
M.2 2242 SSD	PCIe® NVMe®, PCIe® 3.0 x4	256GB
M.2 2242 SSD	PCIe® NVMe®, PCIe® 4.0 x4	256GB / 512GB

Notes:

[1] The storage capacity supported is based on the test results with current Lenovo® storage offerings.

[2] The system has one eMMC storage card or one M.2 2242 SSD exclusively.

Removable Storage

Card Reader

microSD card reader

Multi-Media

Audio Chip

High Definition (HD) Audio, Realtek® ALC5682I-VD codec

Speakers^[1]

Stereo speakers, 2W x2, optimized with Waves MaxxAudio®

Microphone

Dual-microphone array, support Google Assistant

Camera

FHD 1080p, with privacy shutter, fixed focus

Notes:

[1] Google Approved Vendor List (AVL) Certification.

Sensor

Sensors

- (Optional) Human Presence Sensor (HPS)
- Accelerometer (G) sensor
- Gyroscope sensor
- Hall sensor

Battery

Battery

Integrated Li-Polymer 51Wh battery

Max Battery Life^[1]

Google power load test: 10 hr

Notes:

[1] All battery life claims are approximate maximum and based on results using the MobileMark® 2014, MobileMark® 2018, MobileMark® 25, MobileMark® 30, JEITA 2.0, JEITA 3.0, continuous 1080p video playback (with 150nits brightness and default volume level) or Google Power Load Test (PLT) battery-life benchmark tests. Actual battery life will vary depending on many factors such as product configuration and usage, software use, wireless functionality, power management settings, and screen brightness. The maximum capacity of the battery will decrease with time and use.

Power Adapter

Power Adapter

45W USB-C® (3-pin) AC adapter, supports PD 3.0, 100-240V, 50-60Hz

DESIGN

Display

Display^{**[1]}

Size	Resolution	Touch	Type	Brightness	Surface	Aspect	Contrast	Color	Refresh	Viewing Angle
------	------------	-------	------	------------	---------	--------	----------	-------	---------	---------------

						Ratio	Ratio	Gamut	Rate	(L/R/U/D)
14"	WUXGA (1920x1200)	Multi-touch	IPS	300nits	Glossy	16:10	800:1	45% NTSC	60Hz	85° / 85° / 85° / 85°
14"	WUXGA (1920x1200)	Multi-touch	IPS	400nits	Glossy	16:10	800:1	100% sRGB	60Hz	85° / 85° / 85° / 85°

Touchscreen

OGM (One Glass Metal mesh) or OGS (One Glass Solution) multi-touch, supports 10-point touch

Notes:

[1] IPS (in-plane switching) technology may refer to IPS, PLS, ADS, AHVA, AAS.

Multi-mode

Multi-mode

Laptop, tent, stand, and tablet modes supported by 360° hinge

Input Device

Pen^[1]

- Lenovo® USI Pen with replaceable AAAA alkaline battery, 4096 levels of pressure sensitivity
- No pen (purchase separately)

Keyboard

Chrome keyboard, 6-row

Keyboard Backlight

- LED backlight
- Non-backlight

Touchpad

Buttonless Mylar® surface multi-touch touchpad, 75 x 120 mm (2.95 x 4.72 inches)

Notes:

[1] IP Flex 5 Chrome 14IAU7 is only compatible with USI 1.0 stylus pens.

Mechanical

Dimensions (WxDxH)^[1]

315.5 x 229 x 19.8 mm (12.42 x 9.02 x 0.78 inches)

Weight^[2]

Starting at 1.58 kg (3.48 lbs)

Case Color**

- Stone blue
- Storm grey

Surface Treatment

Aluminium stamping (anodized)

Case Material

Aluminium (top), PC-ABS (bottom)

Notes:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo® lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

CONNECTIVITY

Network

Ethernet

No onboard Ethernet

WLAN + Bluetooth^[1]

Wi-Fi® 6E, 802.11ax 2x2 Wi-Fi® + Bluetooth® 5.3

WWAN

No support

Notes:

[1] Wi-Fi® 6E full features might be limited by country-level restrictions. 6GHz Wi-Fi® 6E operation is dependent on the support of the operating system, routers/APs/Gateways that support Wi-Fi® 6E, and the regional regulatory certifications & spectrum allocation. Bluetooth® 5.3 operation requires Windows® 11. For more information please visit [General Bluetooth® Support Information on Microsoft®](#).

Ports^[1]**Standard Ports**

- 1x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 2x USB-C® (USB 10Gbps / USB 3.2 Gen 2), with USB PD 3.0 and DisplayPort™ 1.4
- 1x Headphone / microphone combo jack (3.5mm)
- 1x microSD card reader

Notes:

[1] The transfer speed of the ports will vary and, depending on many factors, such as the processing speed of the host device, file attributes and other factors related to system configuration and your operating environment, will be slower than theoretical speed.

SECURITY & PRIVACY

Security

Security Chip

Google Security Chip H1

Physical Locks

Kensington® Nano Security Slot™, 2.5 x 6 mm

Fingerprint Reader

- Touch style fingerprint reader on palm rest
- No fingerprint reader

BIOS Security

No support

Other Security

- Camera privacy shutter
- (Optional) Human Presence Detection

SERVICE

Warranty

Base Warranty**

- 1-year courier or carry-in service
- 2-year (1-yr battery) courier or carry-in service
- 3-year (1-yr battery) courier or carry-in service

ACCESSORIES

Bundled Accessories

Bundled Accessories^[1]

None

Notes:

[1] For more compatible accessory solutions, please visit [Accessories for IP Flex 5 Chrome 14IAU7](#).

OPERATING REQUIREMENTS

Operating Environment

Temperature^[1]

- At altitudes up to 2438 m (8,000 ft)
 - Operating: 5°C to 35°C (41°F to 95°F)
 - Storage: 5°C to 43°C (41°F to 109°F)
- At altitudes above 2438 m (8,000 ft)
 - Maximum temperature when operating under the unpressurized condition: 31.3°C (88°F)

Relative Humidity

- Operating: 8% to 95% at wet-bulb temperature 23°C (73°F)
- Storage and transportation: 5% to 95% at wet-bulb temperature 27°C (81°F)

Altitude

Maximum altitude (without pressurization): 3048 m (10,000 ft)

Notes:

[1] When you charge the battery, its temperature must be no lower than 10°C (50°F).

CERTIFICATIONS

Green Certifications^[1]

Green Certifications^[2]

- ENERGY STAR® 8.0
- EPEAT™ Silver Registered
- ErP Lot 6/26
- RoHS compliant

Notes:

[1] The items listed under the "Green Certifications" section may not only refer to certification but also registration or self-declaration. For ESG & regulatory compliance documents, please visit <https://compliance.lenovo.com>.

[2] EPEAT™ registration and ENERGY STAR® certification are optional and only available on the models with preloaded OS. Please visit epeat.net and energystar.gov for more information.

- Feature with ** means that only one option listed under the feature can be configured on selected models. Please refer to the model configuration for specific information.
- Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. LENOVO PROVIDES THIS PUBLICATION "AS IS," WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. Some jurisdictions do not allow disclaimer of express or implied warranties in certain transactions, therefore this disclaimer may not apply to you.
- The specifications on this page may not be available in all regions, and may be changed or updated without notice.

