

USBC22322C31H42D4RJAM-DK

USB 3.1 (C) to USB 3.1 (C) PD, 2x USB 3.0 (A), 2x USB 2.0 (A), USB 3.1 (C), HDMI 4K, 2x DisplayPort 4K, RJ-45, Audio, and Mic Black Docking Station

Features

- USB-C Triple 4K Docking Station with PD
- External Power Adapter (20V/6A – 120W)
- Color: Black
- 3x display outputs
- Super Speed data transmission between USB peripherals



System Requirements

- USB-C (Thunderbolt 3 compatible) device with DP Alt Mode Support
- USB-C with USB-C mode only up to 2 monitors
- Windows 8.x/10, Mac OS X 10.8 and later
- DisplayLink Driver Installation
- Host Computer USB-C port must support USB Power
- Power Delivery 2.0 and above to be charged

Product Description


This is a USB 3.1 (C) to USB 3.1 (C) PD, 2x USB 3.0 (A), 2x USB 2.0 (A), USB 3.1 (C), HDMI 4K, 2x DisplayPort 4K, RJ-45, Audio, and Mic Black Docking Station. It allows your USB 3.1 (C) equipped MacBook®, laptop or PC to connect to any USB 3.1 (C) to USB 3.1 (C) PD, 2x USB 3.0 (A), 2x USB 2.0 (A), USB 3.1 (C), HDMI 4K, 2x DisplayPort 4K, RJ-45, Audio, or Mic equipped device, such as a monitor or projector. This also allows for high-definition viewing on any HD capable device that is equipped with an appropriate port. Our video adapters are backed by a 3-year warranty and are guaranteed to work the first time.

Specifications

Parameter	Specifications
Product Type	Hub
Connector A	USB-C Male
Connector B	USB 3.1 (C) Port for Host Computer (Power Delivery up to 60W to Charge)
Connector C	USB 3.0 (A) (BC1.2 Charging Port w/Maximum 1.5A)
Connector D	USB 3.0 (A)
Connector E	USB 2.0 (A)
Connector F	USB 2.0 (A)
Connector G	USB 3.1 (C) (For Data Transfer Only)
Connector H	HDMI (4K/30Hz)
Connector I	DisplayPort (4K/60Hz)
Connector J	DisplayPort (4K/60Hz)
Connector K	10/100/1000 Giga LAN Port (RJ-45)
Connector L	3.5mm Audio Output
Connector M	3.5mm Microphone Input
Color	Black
Power Adapter	External Power Adapter (20V/6A – 120W)
DC Power Port	DC Power Jack (DC20V)
Family Type	USB Hub
Length (ft)	0.67
Length (m)	0.2

Product Diagram

Front



- A. Power LED Indicator
- B. 3.5 mm microphone input
- C. 3.5 mm headphone output

- D. USB-A 3.0 Port (BC1.2 charging port w/ max 1.5A)
- E. USB-A 3.0 Port
- F. USB-C (for data transfer only)


Rear



- G. Power On/Off Switch
- H. USB 2.0 A Port
- I. USB 2.0 A Port
- J. USB 3.1 Type C Port for Host Computer
(Power Delivery up to 60W to charge)

- K. HDMI (4K/30Hz)
- L. DisplayPort (4K/60Hz)
- M. DisplayPort (4K/60Hz)
- N. 10/100/1000 Giga LAN Port (RJ-45)
- O. DC Power Jack (DC20V)

Application Diagram



About AddOn Networks

In 1999, AddOn Networks entered the market with a single product. Our founders fulfilled a severe shortage for compatible, cost-effective optical transceivers that compete at the same performance levels as leading OEM manufacturers. Adhering to the idea of redefining service and product quality not previously had in the fiber optic networking industry, AddOn invested resources in solution design, production, fulfillment, and global support.

Combining one of the most extensive and stringent testing processes in the industry, an exceptional free tech support center, and a consistent roll-out of innovative technologies, AddOn has continually set industry standards of quality and reliability throughout its history.

Reliability is the cornerstone of any optical fiber network and is ingrained in AddOn's DNA. It has played a key role in nurturing the long-term relationships developed over the years with customers. AddOn remains committed to exceeding industry standards with certifications from ranging from NEBS Level 3 to ISO 9001:2005 with every new development while maintaining the signature reliability of its products.



U.S. Headquarters

Email: sales@addonnetworks.com

Telephone: +1 877.292.1701

Fax: 949.266.9273

Europe Headquarters

Email: salesupportemea@addonnetworks.com

Telephone: +44 1285 842070