

SPECIFICATIONS

Model Name	GeForce RTX™ 4070 Ti VENTUS 3X 12G OC
Graphics Processing Unit	NVIDIA® GeForce RTX™ 4070 Ti
Cores	7680 Units
Memory	12GB GDDR6X
Power connectors	16pin x 1
Bus Standard	PCI Express® Gen 4
Memory Interface	192-bit
Core Clocks	Extreme Performance: 2655 MHz (MSI Center) Boost: 2640 MHz
Memory Speed	21 Gbps
Maximum Displays	4
Digital Maximum Resolution	7680 x 4320
HDCP Support	Y
Power consumption (W)	285W
Output	DisplayPort x 3 (v1.4a) HDMI™ x 1 (Supports 4K@120Hz HDR, 8K@60Hz HDR, and Variable Refresh Rate as specified in HDMI 2.1a)
Recommended Power Supply (W)	700W
DirectX Version Support	12 Ultimate
OpenGL Version Support	4.6
Card Dimension(mm)	308 x 123 x 52 mm
Weight	1150g / 1722g

FEATURES



Triple Fan

Three fans and a huge heatsink ensure a cool and quiet experience for you.



TORX FAN 4.0

A masterpiece of teamwork, fan blades work in pairs to create unprecedented levels of focused air pressure.



Core Pipe

Precision-machined heat pipes ensure max contact and spread heat along the full length of the heatsink.



Airflow Control

Don't sweat it, Airflow Control guides the air to exactly where it needs to be for maximum cooling.



Metal Backplate


Thermal pads under the sturdy metal backplate provide additional cooling while the flow-through ventilation reduces trapped heat.



MSI Center

The exclusive MSI Center software lets you monitor, tweak and optimize MSI products in real-time.

CONNECTIONS



1. DisplayPort
2. HDMI