

GUV302G

# UpStream 4k Game Capture Card with Party Chat Mixer



- Supports 4k@60 HDR input and pass-through
- Real time Ultra HD 4k@30 Video Capture on Laptop or PC via USB 3.1 Type C
- Supports up to 1440p@144Hz and 1080p@240Hz pass-through
- Supports party chat recording for Game Consoles
- UVC based driver

## Unlock Your 4K Streaming Potential

The UpStream™ Game Capture Adapter (GUV302G) evolves the next generation of streaming with 4K @30Hz capture, passthrough resolutions designed for gamers including 4K @60Hz, 1440p @144Hz and 1080p @240Hz with built-in party chat mixer for any game console streamers.

## 4K @30Hz HDR Recording

Capture stunning 4K @30Hz quality for the latest 4K gameplay or stream and capture at 1440p @60Hz or 1080p @120Hz resolutions

## Easy Plug & Play Design

No additional adapters or software to capture 4K gameplay or team chat via the latest game consoles

- |   |  |
|---|--|
| <ul style="list-style-type: none"> <li>• Supports 4k@60 HDR input and pass-through</li> <li>• Real time Ultra HD 4k@30 Video Capture on Laptop or PC via USB 3.1 Type C</li> <li>• Supports up to 1440p@144Hz and 1080p@240Hz pass-through</li> </ul> | <ul style="list-style-type: none"> <li>• Supports party chat recording for Game Consoles</li> <li>• UVC based driver</li> <li>• Compatible with OBS software</li> <li>• Compliant with the Specification of High-Bandwidth Digital Content Protection (HDCP).</li> </ul> |
|---|--|



### Requirements

- Windows® 10, 11 w/ UVC support
- Mac OS X (10.2.x or later) w/ UVC support
- One available USB-A port, USB 3.1 is required for 4K Capture.
- Desktop: Intel® Core™ i5 6xxx above + NVIDIA GeForce GTX 1060 and above  
Laptop: Intel® Core™ i7-7700HQ above + NVIDIA GeForce GTX 1050 Ti and above
- RAM: 8GB or higher

### Package Contents

- 1 x GUV302G
- 1 x USB-C to A cable
- 1 x HDMI cable
- 1 x 3.5mm Audio cable
- 1 x Quick Start Guide

## Specifications

Function	GUV302G	Dimensions	GUV302G
<b>Connectors</b>		<b>Unit Dimensions</b>	
USB	1x USB-C for Host computer	Height	0.66 " (1.7 cm)
Video Input	3840x2160p 60/50/30/25/24Hz 2560x1440p 144/60/50/30/25/24Hz 1920x1080p 240/144/120/60/50/30/25/24Hz 1280x720p 60/50Hz 720x576p 50Hz 640x480 60Hz	Length	1.7 " (4.4 cm)
Video Output	1280x720p 60/50Hz 720x576p 50Hz 640x480 60 Hz	Width	0.9" (2.5 cm)
Power	Bus Powered via USB-C to A cable	<b>Inner Pack</b>	
<b>Video connections</b>		Height	*15.7 in (40 cm)
Input	1x HDMI input up to 4K@60 HDR	Length	*7.4 in (19 cm)
Output	1x HDMI input up to 4K@60 HDR	Width	*7 in (18 cm)
<b>Video capture size</b>		Inner Pack Qty.	6 pcs
UVC Capture: 3840x2160p 30/25Hz 2560x1440p 60/50/30/25Hz 1920x1080p 120/60/50/30/25Hz 1280x720p 60/50/30/25Hz 720x576p 50/25Hz 640x480p 60/30Hz		<b>Unit Package Dimensions</b>	
<b>Operating System Requirements</b>		Height	7.4 in (19 cm)
Mac	Mac OS X (10.2.x or later) w/ UVC support	Length	6.2 in (15.9 cm)
Windows	Windows® 10, 11 w/ UVC support	Width	2.1 in (5.5 cm)
<b>Operating System Support</b>		<b>Master Carton</b>	
One available USB-A port, USB 3.1 is required for 4K Capture. Desktop: Intel® Core? i5 6xxx above + NVIDIA GeForce GTX 1060 and above Laptop: Intel® Core? i7-7700HQ above + NVIDIA GeForce GTX 1050 Ti and above RAM: 8GB or higher		Height	*16.5 in (42 cm)
<b>Console Connectors</b>		Length	*15.9 in (40.5 cm)
Audio	1x 3.5 mm for Headset 1x 3.5 mm for Console Gamepad	Width	*15.9 in (40.5 cm)
<b>Cable Length</b>		Master Carton Qty.	12 pcs
USB-C to A 3.3ft (1m)		<b>Weight</b>	
		Master Carton Wt.	*26.12 lbs (11.85 kgs)
		Inner Pack Wt.	*2.68 lbs (1.21 kgs)
		Unit Pack Wt.	*0.83 lbs (0.38 kgs)
		Unit Wt.	0.2 lbs (0.08 kgs)