


# IFP7552-1C-C1 - 75" VIEWBOARD® INTERACTIVE FLAT PANEL BUNDLE WITH CHROMEBOX

## Key Features


- 75" ViewBoard IFP7552-1C 4K interactive flat panel
- VB-WIFI-001 WiFi and Bluetooth adapter
- NMP760 Chromebox
- WMK-047 wall mount



75  
**DISPLAY**



**PANEL**



**RESOLUTION**

## Product Description

Ideal for education environments, this all-in-one ViewBoard Bundle includes a 75" ViewBoard IFP7552-1C 4K interactive flat panel, a VB-WIFI-001 WiFi and Bluetooth adapter, a NMP760 Chromebox, and a WMK-047 wall mount.

## Specifications

More Information


<b>Display Type</b>	LCD
<b>Screen Size</b>	75
<b>Viewable Area (in.)</b>	75
<b>Orientation</b>	Landscape
<b>Light Source</b>	LED

<b>Resolution</b>	3840 x 2160
<b>Refresh Rate (Hz)</b>	60
<b>Aspect Ratio</b>	16:9
<b>Static Contrast Ratio</b>	1,200:1
<b>Brightness</b>	350 cd/m2
<b>Response Time (Typical GTG)</b>	8ms
<b>Viewing Angles</b>	178° horizontal, 178° vertical
<b>Panel Surface</b>	Anti-glare 7H tempered glass
<b>Ethernet LAN</b>	10/100/1000MB GigaLAN
<b>Wifi</b>	Wi-Fi 6 (802.11ax (a/b/g/n/ac/ax))
<b>Bluetooth</b>	Bluetooth 5.0
<b>OS</b>	ViewBoard OS based on Android 9.0
<b>GPU</b>	ARM Mali-G52
<b>CPU</b>	ARM Quad Core Cortex A73
<b>CPU Processor Speed</b>	1.8GHz
<b>Memory</b>	4GB
<b>Storage</b>	32GB
<b>Internal Speakers</b>	15W (x2)
<b>Subwoofer</b>	15W (x1)
<b>HDMI 2.0 In</b>	4
<b>HDMI Out</b>	1
<b>VGA</b>	1
<b>DisplayPort</b>	1
<b>3.5mm Audio In</b>	1
<b>3.5mm Audio Out</b>	1
<b>SPDIF</b>	1
<b>USB 3.0</b>	3
<b>USB 2.0</b>	2
<b>USB 2.0 Type B</b>	3
<b>USB 3.1 Type C</b>	1
<b>OPS PC Slot</b>	1
<b>RS232</b>	1
<b>Ethernet LAN (RJ45)</b>	2
<b>WIFI Module Slot</b>	1
<b>Intel® OPS Slot In (80-pin)</b>	1
<b>Voltage</b>	100-240 VAC

<b>Consumption (typical)</b>	233.5W
<b>Stand-by</b>	<0.5W
<b>On Screen Display</b>	Input, Volume, Backlight, Audio, Screen, Display, Adjust
<b>Temperature</b>	32-104° F (0 - 40° C)
<b>Humidity (non-condensing)</b>	10-90%
<b>Touch Technology</b>	Infrared
<b>Touch Points</b>	Windows: 33-Point Touch, Android: 20-Point Touch
<b>Tip Detection</b>	Dual tips, 2.5mm and 9mm
<b>Net (lbs)</b>	121.81
<b>Gross (lbs)</b>	170.81
<b>Net (kg)</b>	55.25
<b>Gross (kg)</b>	77.48
<b>Packaging (in.)</b>	73.2 x 46.3 x 8.9
<b>Physical (in.)</b>	67.3 x 42.2 x 4.7
<b>Packaging (mm)</b>	1860 x 1175 x 225
<b>Physical (mm)</b>	1709 x 1071 x 120
<b>VESA Compatible</b>	800 x 400 mm
<b>Warranty</b>	3-year limited warranty on parts, labor and backlight, onsite warranty
<b>Recycle/Disposal</b>	Please dispose of in accordance with local, state or federal laws.
<b>PACKAGE CONTENTS</b>	IFP7552-1C display, power cord, Remote control with AAA battery, Touch USB cable, Touch pen x 2, Quick Start Guide + Compliance statement, RS232 adapter, Clamp x 5, Camera Plate, Screw x 8, HDMI cable, Type-C cable, Eraser
<b>Regulations</b>	cTUVus, FCC, ENERGY STAR 7.0, Mexico Energy, CE, CB, RoHS, ErP, WEEE

## Contact Sales

[ViewSonic.com](http://ViewSonic.com)

888.881.8781 

email: [salesinfo@viewsonic.com](mailto:salesinfo@viewsonic.com) 