

ideapad 3i (14", 15", 17")

TAILOR YOUR PERFORMANCE.


Engineered for long-lasting performance, the Lenovo™ **IdeaPad™ 3i** is the perfect laptop for your everyday tasks with features that you can depend on.

WHY YOU SHOULD BUY THE LENOVO IDEAPAD 3i (14", 15", 17")




Expect more from your entertainment

Dolby Audio™ delivers crystal-clear sound whether you're watching a video, streaming music, or video-chatting, you're sure to love what you hear on the **IdeaPad 3i**.



See more, do more

A narrow bezel on 2 sides makes for a clean design, and larger display giving you more viewing area and less clutter.



Privacy at your fingertips

Keep your privacy intact with a physical shutter for your webcam bringing you peace of mind when you need it.



Quick and quiet with Q-Control

It's your choice. Swap effortlessly between 'Max mode' where your CPU takes charge and provides the quickest performance and 'battery saving mode' for better battery performance - all with a simple keystroke.



Lenovo™

BIG-TIME ENTERTAINMENT IN A REMARKABLY THIN & LIGHT DESIGN.

Up to 11th Generation Intel® Core™ Processors and Intel® Iris® Xe graphics, break the boundaries of performance for thin and light laptops.



WWW.LENOVO.COM



ideapad 3i (14", 15", 17")

SPECIFICATIONS

Lenovo IdeaPad 3 14ITL-5 | Lenovo IdeaPad 3 15ITL-5 | Lenovo IdeaPad 3 17IML-5*

PERFORMANCE

Processor

IdeaPad 3i - 14" | IdeaPad 3i - 15"

11th Generation Intel® Core™ i7-1165G7

11th Generation Intel® Core™ i5-1135G7

11th Generation Intel® Core™ i3-1115G4

Intel® Pentium® Gold 7505

Intel® Celeron® 6305

IdeaPad 3i - 17"

Up to 10th Generation Intel® Core™ i7-10510U

Operating System

Windows 10 Pro

Windows 10 Home

Graphics

IdeaPad 3i - 14" | IdeaPad 3i - 15"

Dis : Up to NVIDIA® GeForce® MX330

UMA : Integrated with Intel® Iris® X® Graphics

IdeaPad 3i - 17"

Dis : NVIDIA® GeForce® MX330

UMA : Integrated with Intel® Iris® Plus Graphics

Memory

DDR4 : 4GB / 8GB / 12GB

Storage

HDD SATA : 500GB / 1TB; 5400 rpm

M.2 PCIe SSD : 128GB¹ / 256GB / 512GB / 1TB

Dual Storage : QLC 512GB

SSD + HDD : 128GB/256GB + 1TB

Camera

Up to 1M with Dual Microphone

Audio

2 x 1.5W Speakers with Dolby Audio™,

Dual Microphone

Battery²

IdeaPad 3i - 14" | IdeaPad 3i - 15"

MobileMark® 2014 : Up to 9 Hours

1080p Video Playback : Up to 9 Hours

IdeaPad 3i - 17"

MobileMark® 2014 : Up to 11.5 Hours

1080p Video Playback : Up to 10 Hours

¹ 128GB is the only available storage slot for 14" and 15" models.

² All battery life claims are approximate and based on two methods of testing: MobileMark® 2014 battery life benchmark and continuous 1080p video playback on the latest update of Windows 10 (with 150 nits brightness and default volume level). Actual battery life will vary and depends on many factors such as product configuration and usage, software use, wireless functionality, power management settings, and screen brightness. The maximum capacity of the battery will decrease with time and use.

³ Not available for 17" model.

⁴ Not all configurations will allow for these I/O ports.

⁵ The actual transfer speed of the USB 3.1 Gen 1 will vary and, depending on many factors, such as the processing capability of host and peripheral devices, file attributes and other factors related to system configuration and your operating environments, will be slower than a speed of 5Gbit/s.

DESIGN

Display

IdeaPad 3i - 14"

14" FHD (1920 x 1080) IPS, 250 nits, 45% NTSC

14" FHD (1920 x 1080) TN, 220 nits, 45% NTSC

14" HD (1366 x 768) TN, 220 nits, 45% NTSC

IdeaPad 3i - 15"

15.6" FHD (1920 x 1080) IPS, 250 nits, 45% NTSC

15.6" FHD (1920 x 1080) TN, 220 nits, 45% NTSC

15.6" HD (1366 x 768) TN, 220 nits, 45% NTSC

IdeaPad 3i - 17"

17" FHD (1920 x 1080) IPS, 300 nits, 45% NTSC

17" HD+ (1600 x 900) TN, 250 nits, 45% NTSC

Narrow Bezel

IdeaPad 3i - 14" | IdeaPad 3i - 15"

X/Y: 7.5 mm

IdeaPad 3i - 17"

X/Y: 8.25 mm

Dimension (W x D x H)

IdeaPad 3i - 14"

(mm) : 327.1 x 241 x 19.9

(inches) : 12.88" x 9.49" x 0.78"

IdeaPad 3i - 15"

(mm) : 362.2 x 253.4 x 19.9

(inches) : 14.26" x 9.98" x 0.78"

IdeaPad 3i - 17"

(mm) : 402 x 281.25 x 19.9

(inches) : 15.83" x 11.07" x 0.78"

Weight

IdeaPad 3i - 14"

Starting at 1.5 kg (3.3 lbs)

IdeaPad 3i - 15"

Starting at 1.7 kg (3.7 lbs)

IdeaPad 3i - 17"

Starting at 2.2 kg (4.8 lbs)

Hinge

IdeaPad 3i - 14"

180°

IdeaPad 3i - 15"

170°

IdeaPad 3i - 17"

143°

Colors

Platinum Grey

Abbyss Blue

Cherry Red³

WOW FEATURES

Standard

Privacy Shutter

Windows Cortana

Alexa

LVA

Optional

Fingerprint Reader (on power button)

CONNECTIVITY

WLAN

Up to WiFi 6 (2x2 802.11 ax/ac/ac(LC))

Bluetooth®

Up to Bluetooth® 5.0

Input/Output (I/O) Ports⁴

2 x USB 3.1 Gen 1⁵

1 x USB 2.0

HDMI™ 1.4b

SD Card Reader

PRELOADED SOFTWARE

- Windows 10 S
- McAfee LiveSafe™
- Microsoft Office
- Lenovo Utility
- Lenovo Vantage
- Alexa
- Mirkat

LENOVO SERVICES

Warranty Upgrades - On-site / In-Home Service

Maximizes PC uptime and productivity by providing convenient, fast repair services in your own home.


Accidental Damage Protection

Avoid the hassles of unexpected repair costs. Provides coverage for non-warranted damage incurred under normal operating conditions, such as minor spills, drops or damage to the integrated screen.

Warranty Extensions (1-to-3 Years Total Duration)

This fixed-term, fixed-cost service helps accurately budget for PC expenses, protect your valuable investment and potentially lower the cost of ownership over time.

* Example of Lenovo catalogue naming convention



Intel® platform codes

Haswell H81: IHH, BroadWell U: IBU, Skylake Z170: ISZ, Skylake B150: ISB, Kabylake: IKL, Skylake H110/H170: ISH, Skylake U: ISU, Apollo Lake: IAP, Coffee Lake B360: ICB, Coffee Lake H Refresh: IRH, Coffee Lake Z370 Overclock: ICO, Comet Lake: IML, Tiger Lake: ITL.



WWW.LENOVO.COM

Lenovo reserves the right to alter product offerings and specifications at any time, without notice. Lenovo makes every effort to ensure accuracy of all information but is not liable or responsible for any editorial, photographic or typographic errors. All images are for illustration purposes only. For full Lenovo product, service and warranty specifications visit www.lenovo.com. Lenovo makes no representations or warranties regarding third party products or services. **Trademarks:** The following are trademarks or registered trademarks of Lenovo: Lenovo, the Lenovo logo, ideapad, IdeaCentre, yoga and yoga home. Microsoft, Windows and Vista are registered trademarks of Microsoft Corporation. Ultrabook, Celeron, Celeron Inside, Core Inside, Intel, Intel Atom, Intel Atom Inside, Intel Core, Intel Inside, Intel Inside Logo, Intel vPro, Itanium, Itanium Inside, Pentium, Pentium Inside, vPro Inside, Xeon, Xeon Phi, and Xeon Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product and service names may be trademarks or service marks of others. Visit www.lenovo.com/lenovo/us/en/safecomp/ periodically for the latest information on safe and effective computing.

©2020 Lenovo. All rights reserved.



Lenovo™