



Sharp NEC Display Solutions

Large Format Displays

SHARP / NEC

NEC E Series | Essential Displays

MultiSync® Model	Size inch/cm	Brightness in cd/m ²	Haze Level*	Orientation**	Video Signals
E328	32 / 81	350	S	L	3 HDMI, VGA
E438 ²	43 / 109	350	S	L	3 HDMI, VGA
E498 ²	49 / 123	350	S	L	3 HDMI, VGA
E558 ²	55 / 140	350	S	L	3 HDMI, VGA
E658 ²	65 / 165	350	S	L	3 HDMI, VGA
E758 ^{1,2}	75 / 189	350	P	L, P	3 HDMI, VGA
E868 ^{1,2}	86 / 217	350	P	L, P	3 HDMI, VGA

167¹ 187² 4K UHD



- Slim design and integrated speakers
- Future-ready connectivity
- Standalone operation



NEC ME Series | Midrange Displays

MultiSync® Model	Size inch/cm	Brightness in cd/m ²	Haze Level*	Orientation**	Video Signals
ME431	43 / 108	400	S	L, P	2 HDMI, DP
ME501	50 / 126	400	S	L, P	2 HDMI, DP
ME551	55 / 139	400	S	L, P	2 HDMI, DP
ME651	65 / 164	400	S	L, P	2 HDMI, DP

187 4K UHD



- Driving content with RPi NEC MediaPlayer
- Improved connectivity and control
- Infrared touch models available for 43", 50" and 55"



NEC C Series | Midrange Displays

MultiSync® Model	Size inch/cm	Brightness in cd/m ²	Haze Level*	Orientation**	Video Signals
C981Q	98 / 248	350	P	L, P	3 HDMI, DP: 2 In, 1 Out



- Low reflective panel
- Modular Computing for scalable computing power
- Ambient Light Sensor




NEC M Series | Midrange Displays

MultiSync® Model	Size inch/cm	Brightness in cd/m ²	Haze Level*	Orientation**	Video Signals
M321	32 / 80	450	P	L, P, FU	2 HDMI, DP
M431 ¹	43 / 108	500	P	L, P	2 HDMI, DP
M491 ¹	49 / 124	500	P	L, P	2 HDMI, DP
M551 ¹	55 / 139	500	P	L, P	2 HDMI, DP
M651 ¹	65 / 164	500	P	L, P	2 HDMI, DP
M751 ¹	75 / 189	500	P	L, P	2 HDMI, DP
M861 ¹	86 / 217	500	P	L, P	2 HDMI, DP



- Professional haze level for best visibility and no reflections
- Driving content with RPi4 or Intel® SDM
- PCAP™ touch models available



NEC V Series | Midrange Displays

MultiSync® Model	Size inch/cm	Brightness in cd/m ²	Haze Level*	Orientation**	Video Signals
V984Q	98 / 248	500	P	L, P, FU	3 HDMI, DP: 2 In, 1 Out

247

4K UHD



SpectraView™ engine

- Modular Computing for scalable computing power
- SpectraView® engine for superb colour accuracy
- Future-proof signal connectivity and processing



NEC MA Series | Advanced Displays

MultiSync® Model	Size inch/cm	Brightness in cd/m ²	Haze Level*	Orientation**	Video Signals
MA431	43 / 108	500	P	L, P, FU	HDMI: 2 In, 1 Out, DP: 2 In, 1 Out
MA491	49 / 124	500	P	L, P, FU	
MA551	55 / 139	500	P	L, P, FU	

247

4K UHD



SpectraView™ engine

- Advanced connectivity
- WCG panel and SpectraView® engine for superb colour accuracy
- Driving content with RPi4 or Intel® SDM



NEC P Series | Professional Displays

MultiSync® Model	Size inch/cm	Brightness in cd/m ²	Haze Level*	Orientation**	Video Signals
P435	43 / 108	700	P	L, P, FU, FD	HDMI: 2 In, 1 Out, DP: 2 In, 1 Out
P495	49 / 125	700	P	L, P, FU, FD	
P555	55 / 139	700	P	L, P, FU, FD	
P754Q	75 / 189	650	P	L, P, FU	



- Modular Computing for scalable computing power
- Superb readability in bright light environments
- Long-term operation in demanding environments



NEC UN Series | Video Wall Displays

MultiSync® Model	Size inch/cm	Brightness in cd/m ²	Haze Level*	Orientation**	Video Signals
UN552	55 / 140	700	P	L, P	HDMI In/Out, DP In/Out, DVI-D, VGA
UN552V	55 / 140	500	P	L, P	
UN552S	55 / 140	700	P	L, P	
UN552VS	55 / 140	500	P	L, P	



- Enhanced imaging performance
- Easy set-up with Auto TileMatrix
- Long lasting picture quality thanks to intelligent calibration



* Haze Level (Anti-Reflection): S = **Standard** (<5 %); A = **Advanced** (5 % - 25 %); P = **Pro** (>25 %)

** Orientation: L = **Landscape**; P = **Portrait**; FU = **Face Up**; FD = **Face Down**

NEC BT Series | Stretched Display

MultiSync® Model	Size inch/cm	Brightness in cd/m ²	Haze Level*	Orientation**	Video Signals
BT421	42 / 107	700	P	L, P	DVI: 2 In, 1 Out, LAN



- Space efficient display with ultra-wide screen ratio of 16:4



NaViSet Administrator 2



Unified remote management software for NEC desktop monitors, large format displays and projectors.

SpectraView® Engine



Advanced settings of all relevant visual parameters allow full control of brightness, colour, gamma and uniformity via the SpectraView® Engine for precise, natural images.

Modular Computing

Future ready expansion to upgrade the power of your display at any time by seamlessly integrating one of Sharp/NEC's options for Intel® SDM modules, OPS Slot-in PCs, Raspberry Pi compute module or signal interfaces for content feed and computing.

Protective Glass

Guaranteed reliability even under the toughest conditions is achieved with robust protective glass designed to withstanding external impacts. Available for NEC MultiSync® M / MA / P Series.

Document Name:	Large Format Displays Pocket Guide
Document Revision:	Edition 12, 2023
Document Date:	2/23

For more information visit us at
www.sharpnecdisplays.eu