

ThinkCentre neo 50q Gen 4 Thin Client

The fast and intuitive 1-liter small form factor is designed to provide high performance to business professionals with the processing power of up to 12th Gen Intel Core i3 processor. Combined with integrated Intel UHD graphics, this device ensures faster responsiveness for memory-intensive data applications. Moreover, with up to 32GB DDR4 memory and up to 256GB SSD storage, the modern workforce can work efficiently and store heavy files.



The desktop computer facilitates improved accessibility by enabling professionals to connect with up to three distinct displays through HDMI, DisplayPort, and VGA ports. Additionally, the process of connecting USB drives, extra cables, or verifying a connection is significantly less cumbersome.

Prevent unauthorized access to the system with security solutions such as integrated TPM 2.0 chipset, BIOS security, chassis intrusion switch, and Kensington security slot.

The device is energy-efficient, with optional Energy Star 8.0 and optional EPEAT Gold certifications, ensuring businesses save money and reduce environmental impact.

Mainstream computing for a variety of business uses

ThinkCentre Neo series offers organizations enhanced manageability and security features, along with additional configuration and expansion options.

Lenovo services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



On-site Service

If a problem can't be fixed remotely, we will visit your location
 Normally next business day service
 Agreed appointment times

Accessories

Lenovo Professional Wireless Keyboard & Mouse

Wireless keyboard and mouse combo with reliable 2.4 GHz wireless connection
 Slim keyboard with number pad, noise-suppression design, dedicated media controls & adjustable tilt legs
 Contoured design of the mouse suits both left-handed & right-handed users



PN: 4X30H56796

ThinkVision MC50 Monitor Webcam

1080p webcam with 1/2.9-inch large sensor delivers super video clarity
 Flexible setup by tilting up to +/-30° and swiveling the camera -45° to 225° to be in the position for your needs
 Anti-theft locking functionality with a physical key



PN: 4XC1D66056

ThinkCentre neo 50q Gen 4 Thin Client

Performance

Processor

Intel Celeron, or 12th Generation Intel Core i3 Processor

Operating System

Windows 10 IoT Enterprise, IGEL Linux, LeTOS V2 (Lenovo Terminal Operating System, Linux-based)

Graphics

Intel UHD Graphics (integrated)

Memory

Intel Celeron model:
up to 16GB DDR4-3200, 1x SO-DIM

Intel Core model:
up to 32GB DDR4-3200, 2x SO-DIM

Storage

One drive, 256GB M.2 SSD

Optical

optional
DVD burner (DVD±RW), SATA connector, slim (9.0mm)

Design

Dimensions

179 x 182.9 x 36.5 mm (7.05 x 7.2 x 1.44 inches)

Weight

Around 1.11 kg (2.45 lbs)

Expansion Slots

One M.2 slot (for WLAN)
One M.2 slot (for SSD)

Connectivity

Front I/O

1x USB 3.2 Gen 2 (Always On and 5V@2.1A charging), 1x USB-C 3.2 Gen 2 (support data transfer and 5V@0.9A charging), 1x headphone / microphone combo jack (3.5mm)

Rear I/O

1x HDMI 2.1 TMDS, 1x DisplayPort 1.4, 2x USB 2.0, 2x USB 3.2 Gen 2, 1x Ethernet (RJ-45) 1x VGA (Punch out port), Optional 1x DisplayPort 1.4 (Punch out port), Optional 1x Serial (Punch out port)

Security & Privacy

Firmware TPM 2.0 integrated in SoC
Kensington Security Slot, 3 x 7 mm
Chassis intrusion switch

Certifications

Green Certifications

Optional EPEAT Gold, Optional ENERGY STAR 8.0, ErP Lot 3 and Lot 7, TCO Certified 9.0, RoHS compliant

Other Certifications

Optional TÜV Rheinland Low Noise, Optional TÜV Rheinland Ultra Low Noise