

ThinkCentre neo 50q Gen 4

This fast and intuitive 1-liter small form factor equipped with the processing power of up to 13th Gen Intel Core i5 processor delivers high performance to business professionals. Combined with integrated Intel UHD graphics, the desktop enables faster responsiveness for memory-intensive data applications. Additionally, the modern workforce can work efficiently and store heavy files with up to 32GB DDR4 memory and up to 1TB SSD storage.



For enhanced accessibility, the desktop allows professionals to access up to three independent displays via HDMI, DisplayPort, and VGA ports; plus plugging in USB drives, extra cables, or checking a connection is a lot less tedious.

Discreet TPM 2.0 chipset, chassis intrusion switch, Kensington security slot, and BIOS security prevent unauthorized access into the interior of the system.

The device is energy-efficient, with optional Energy Star 8.0 and optional EPEAT Gold certifications, ensuring businesses save money and reduce environmental impact.

Mainstream computing for a variety of business uses

ThinkCentre Neo series offers organizations enhanced manageability and security features, along with additional configuration and expansion options.

Lenovo services

Lenovo delivers tailored sustainability services, devices, and infrastructure solutions from our broad portfolio, working closely with you to support your target outcomes across the IT lifecycle..



On-site Service

If a problem can't be fixed remotely, we will visit your location
 Normally next business day service
 Agreed appointment times

Accessories

ThinkCentre Tiny VESA Mount II

Supports mounting of a ThinkCentre Tiny to the back of VESA-compatible displays
 Can be used separately or combined with other options for secure mounting
 Simple 4-screw design keeps the device securely attached to the mount



PN: 4XF0N03161

ThinkCentre neo 50q Gen 4

Key Specifications

Processor

12th Generation Intel Core i3, or 13th Generation Intel Core i5 Processor

Operating System

Windows 11 Pro, Windows 11 Home, Windows 11 Home Single Language, Windows 11 DG Windows 10 Pro 64, Ubuntu Linux

Graphics

Intel UHD Graphics (integrated)

Memory

Up to 32GB DDR4-3200, two SO-DIMM slots

Storage

Up to two drives, 1x 2.5" HDD + 1x M.2 SSD
2.5" HDD up to 1TB
M.2 SSD up to 1TB

Optical

Optional DVD burner (DVD±RW), SATA connector, slim (9.0mm)

Additional Internal Bays

2.5" HDD Bracket

Expansion Slots

One M.2 slot (for WLAN)
One M.2 slot (for SSD)

Power Supply

One of the following

135W 89% Adapter | 65W 89% Adapter | 90W 89% Adapter

Dimensions

179 x 182.9 x 36.5 mm (7.05 x 7.2 x 1.44 inches)

Weight

Around 1.11 kg (2.45 lbs)

Green Certifications

Optional EPEAT Gold, Optional ENERGY STAR 8.0, ErP Lot 3 and Lot 7, TCO Certified 9.0, RoHS compliant

Other Certifications

Optional TÜV Rheinland Low Noise, Optional TÜV Rheinland Ultra Low Noise

Connectivity

Front I/O

1x USB 3.2 Gen 2 (Always On and 5V@2.1A charging), 1x USB-C 3.2 Gen 2 (support data transfer and 5V@0.9A charging), 1x headphone / microphone combo jack (3.5mm)

Rear I/O

1x HDMI 2.1 TMDS, 1x DisplayPort 1.4, 2x USB 2.0, 2x USB 3.2 Gen 2, 1x Ethernet (RJ-45), Optional 1x VGA (Punch out port), Optional 1x DisplayPort 1.4 (Punch out port), Optional 1x Serial (Punch out port)*

Optional Rear Ports

One of the following

DP 1.4 | Serial | VGA

WLAN + Bluetooth

One of the following

Intel Wi-Fi 6 AX201, 11ax 2x2 + BT5.1 | Realtek Wi-Fi 6 RTL8852BE, 11ax 2x2 + BT5.1

Ethernet

Integrated 100/1000M

Security & Privacy

Chassis Intrusion Switch
Firmware TPM 2.0 integrated in SoC
Kensington Security Slot, 3 x 7 mm
Chassis intrusion switch

Manageability

Non-vPro