

Kensington®



SD5765T Thunderbolt™ 4 Dual 4K Docking Station (DfS)

Part Number: K34112NA/WW | UPC Code: 0 85896 34112 3

Enhanced
productivity today
and in the future
for your Surface.

Ideal for professionals and creatives using Thunderbolt™ based Surface devices who want more speed to work with large files, support for multiple 4K monitors, and more ports so they can connect to accessories without using adapters, the SD5765T Thunderbolt™ 4 Dual 4K Docking Station is an affordable high-speed dock that provides everything you need to enhance your productivity now and well into the future.

Designed exclusively for Surface, the SD5765T Thunderbolt™ 4 Dual 4K Docking Station provides more speed, more power, and more video options. Delivering 40Gbps data transfer speeds, support for Single 8K or Dual 4K @ 60Hz, two HDMI® ports, multiple USB-C® and USB-A ports, up to 96W of dynamic Power Delivery, and daisy chaining via Thunderbolt™ 4, the SD5765T provides a true plug-and-play experience and a tidier desktop—so you can be more productive and focused.

Features include:

- Designed exclusively for Surface to provide a seamless dock and charge experience
- Supports up to 96W of Power Delivery and automatically adjusts for optimal performance
- Transfers up to 40Gbps of data, video, and audio
- 13-in-1 design includes Thunderbolt™, USB-C®, USB-A, HDMI®, Ethernet, a combo audio jack, and Micro and SD card readers
- Supports up to Single 8K @ 60Hz via a Thunderbolt 4 port when DSC is enabled or Dual 4K @ 60Hz via two HDMI ports


Designed for




SD5765T Thunderbolt™ 4 Dual 4K Docking Station (DfS)

Part Number: K34112NA/WW | UPC Code: 0 85896 34112 3

Front




Back



SD5765T Thunderbolt™ 4 Dual 4K Docking Station (DfS)

Part Number: K34112NA/WW | UPC Code: 0 85896 34112 3



Designed Exclusively for Surface

Kensington worked directly with Microsoft to provide professional-level connectivity that looks as good as it functions. Connect with confidence for a seamless dock and charge experience.

Plug-and-Play

Offers a quick and powerful plug-and-play solution for Thunderbolt™ based Surface devices running Windows (10 or later).

Thunderbolt™ 4 Technology

Transfer up to 40Gbps of data, video, and audio—all through the included 2.6' (0.8m) Thunderbolt™ 4 cable. Provides daisy chain support for SSDs, monitors, and other Thunderbolt™ devices. Blocks peripheral devices from unauthorized access to your system memory using Intel VT-d DMA protection.

Single 8K or Dual 4K Support for Thunderbolt™ Devices

Extend visual productivity with the resolution, contrast, and color depth of Ultra HD. Supports up to Single 8K @ 60Hz via a Thunderbolt™ 4 port or Dual 4K @ 60Hz via two HDMI® ports.




Up to 96W Dynamic Power Delivery

Delivers power whenever and wherever you need it—to host and connected accessories. Supports up to 96W of Power Delivery and provides optimal performance under any usage scenario.



Productive 13-in-1 Design

Extend your productivity with two HDMI® ports, one Thunderbolt™ 4 port, one Thunderbolt™ 4 host port, one USB-C® 3.2 Gen2 10Gbps port, two USB-A 3.2 Gen2 10Gbps ports, two USB-A 3.2 Gen1 5Gbps ports, one Gigabit Ethernet port, one audio combo jack, and two UHS-II 4.0 SD and Micro SD card readers.



Zero-Footprint Mounting and Security Cable Lock Slots

Maximize desktop space and reduce cable clutter by mounting your docking station out of the way. Mounting bracket sold separately (K34050WW). Standard and Nano lock slots allow you to protect your investment with a Kensington cable lock (K65020WW or K65021WW), sold separately.



Industry-Leading Quality, Warranty, and Support

Built with quality in mind, we stand behind the SD5765T Thunderbolt™ 4 Dual 4K Docking Station with a dedicated support team and a three-year limited warranty.

SD5765T Thunderbolt™ 4 Dual 4K Docking Station (DfS)

Part Number: K34112NA/WW | UPC Code: 0 85896 34112 3

System Requirements

Systems Supported	Supports Thunderbolt™ 4 / Thunderbolt™ 3 / USB4
Operating Systems Supported	Windows® 10 or above
Plug & Play	Yes
Software	For Windows, need to enable Intel Thunderbolt™ software
System Resource Requirement	CPU: Intel® Core™ i5 6th generation or above Memory: 8Gb or above GPU: Intel® HD Graphics 620 or above
Additional Software Information	DockWorks compatible
USB-C Power Delivery	PD3.0: 5V, 9V, 15V/3A & 20V/4.8A (up to 96W Dynamic Power)

Docking Station

Technology	Intel® JHL8440 Thunderbolt™ 4 controller
------------	--

USB Interface

Type of USB Connector	Thunderbolt™ 4 / Thunderbolt™ 3 / USB4 Connector
Host Connector	Supports Thunderbolt™ 4 / Thunderbolt™ 3 / USB4

USB Connections

Ports	<p>Front Panel :</p> <ul style="list-style-type: none"> - 1 x Thunderbolt™ 4 Host Port (up to Dynamic PD 96W, 40Gbps) - 1 x Thunderbolt™ 4 DFP (up to PD 5V/3A, 40Gbps) - 2 x USB-A 3.2 Gen1 5Gbps (5V/0.9A) - 1 x SD/Micro SD 4.0 Card reader (UHS-II) - 1 x 3.5mm Audio combo <p>Back Panel :</p> <ul style="list-style-type: none"> - 1 x USB-C 3.2 Gen2 10Gbps (5V/1.5A) - 2 x USB-A 3.2 Gen2 10Gbps (5V/0.9A) - 2 x HDMI 2.0 - 1 x 1Gbps Ethernet
-------	---

Network Connections

Ethernet Port	RJ45
Compatible Ethernet Speeds	10/100/1000 Mbps

Host Connectivity





Host Docking Connector	Thunderbolt™ 4 upstream port PD up to 96W, Dynamic Power
------------------------	--





SD5765T Thunderbolt™ 4 Dual 4K Docking Station (DfS)

Part Number: K34112NA/WW | UPC Code: 0 85896 34112 3

Video Connections

Video Connectors	1 x Thunderbolt™ 4 2 x HDMI 2.0
Maximum Resolution Supported	Please refer to table below

			
Thunderbolt™ 4 Surface Pro 9-Intel® Surface Pro 8 Surface Laptop 5 Surface Laptop Studio	8K @ 60Hz*	4K @ 60Hz	4K @ 60Hz

			
Thunderbolt™ 4 Surface Pro 9-Intel® Surface Pro 8 Surface Laptop 5 Surface Laptop Studio	4K up to 120Hz* or 1080p up to 240Hz	1080p up to 240Hz	1080p up to 240Hz

* Support for Display Stream Compression (DSC) is based on the host device and monitor capabilities.



Audio Connections

Audio Connectors	1 x 3.5mm audio combo jack
------------------	----------------------------

LED Indicator

Blue LED	Power indicator
----------	-----------------

Material Specifications

Exterior	Enclosure: Aluminum / PC + ABS
Bottom	PC + ABS
Product Color	Deep Space Gray / PMS Black

Other Features

Kensington Security Slot	Kensington Security Slot Kensington Nano Security Slot
VESA Mount Compatible	Yes, with K34050WW

Product Dimensions

Cable Dimensions	31.5in (0.8m)
Unit Weight	0.79lbs (0.36kg)
Unit Dimensions without Peripherals	8.86 x 3.34 x 0.87in (225 x 85 x 22mm)
Enclosure Color & Material	Black PMS, PC+ABS with texture Deep Space Grey Aluminum
Desktop Footprint	27.92in ² (191.25cm ²)

SD5765T Thunderbolt™ 4 Dual 4K Docking Station (DfS)

Part Number: K34112NA/WW | UPC Code: 0 85896 34112 3

Packaging Dimensions

Packaging Style	Retail Package (K34112NA)
Packaging Dimensions	9.53 x 4.25 x 3.94in (242 x 108 x 100mm)
Packaging Weight	2.62lbs (1.19kg)
Packaging Content	1 x SD5765T Dock 1 x Thunderbolt™ 4 passive cable (0.8m) 1 x Power Supply Unit (135W) 1 x Instruction Guide 1 x Warranty Card 1 x Compliance Sheet 1 x Welcome card insert
Master Carton	6 pcs

Power and Environmental

Power Adapter Rating	Input: 100-240V; AC 50/60Hz; 2A Output: 21V DC 6.4A (134.4W)
Relative Humidity	55% operating temperature @ 77°F (25°C)
Operating Temperature	32 to 113°F (0 to 45°C)
Storage Temperature	32 to 140°F (0 to 60°C)

Country of Origin, Regulatory, and Warranty

Country of Origin	Vietnam: NA China: EU/WW
Certifications & Compliance	FCC, IC, CE, RCM, VCCI, UKCA, CB, RoHS, ACCO RSL
Warranty	3-Year Limited - worldwide



All specifications are subject to change without notice. Products may not be available in all markets. Kensington® and Kensington, The Professionals' Choice™ are trademarks of ACCO Brands. All other registered and unregistered trademarks are the property of their respective owners. © 2023 Kensington Computer Products Group, a division of ACCO Brands. k23-22075p

Kensington

The Professionals' Choice™