



# CLEANWIPE PRO WATERPROOF & ERGONOMIC KEYBOARDS

Model: SSWKSV101PRO

State-of-the-art Cleanwipe Pro Waterproof Keyboards from Seal Shield™ with a compact footprint perfect for any workspace. Washable, waterproof & dishwasher-safe keyboard is IP68-certified & compatible with industrial-grade cleaners & disinfectants. Three Ergonomic Tilt Positions allows keyboard angle for optimal comfort, reducing wrist strain and repetitive strain injury. Your choice of Cleanwipe Pro latex-free silicone cover is available.

# **FEATURES:**



100% Waterproof & Dishwasher-Safe



Three Ergonomic Keyboard Tilt Positions -Inclined, Declined and Flat



IP68-Certified



MagSeal™ Magnetic USB Connector for Convenient Connection and Cleaning



Supports USB 3.0 Connectivity



SealLok™ Technology Key Lock Function (ALT+F12) for Easy Cleaning While Still Connected



LED Key Illumination on Caps Lock, Number Lock, Scroll Lock, and Key Lock



Designed to withstand Industrial-Grade Disinfectants



Compact footprint perfect for tight applications including mobile carts and exam rooms



SSWKSV101Pro

Silicone Cover Options





SSxKSV101PRO-FFSC

SSxKSV101PRO-KFSC

#### ADVANCED CLEANING CAPABILITIES

· Dishwasher-Safe

Compatible with Spray & Wipe Disinfectant Products:

- · Clorox Healthcare®
- · Lysol®
- · PDI Products
- · Bleach, Ethanol, IPA, Quats, Citric Acid, & Hydrogen Peroxide, and Other Industrial-Grade Cleaners and Disinfectants





## **CLEANWIPE PRO WATERPROOF & ERGONOMIC KEYBOARDS**

Model: SSWKSV101PRO

### **TECHNICAL DATA:**

Compatibility:	Windows 10 Version 1607 x64 (USB Models)
Construction:	ABS Plastic (Chiclet Style with Silicone Cover)
Net Dimensions L x W x H:	13.94 x 5.12 x 0.886in (354 x 130 x 22.5 mm)
Gross Dimensions:	14.25 x 5.6 x 1.2in (362 x 142 x 30.5 mm)
Key Layout:	99 Keys including 10 Keypad
Net Weight:	.66lb (.299kg)
Gross Weight:	.73lb (.331kg)
Connection Type:	6ft (1.83m) Long USB Cable with Magnetic Connector to Keyboard
Key Switch Force:	60 ± 15 gf
Key Switch Life Cycle:	8,000,000 keystrokes
Key Switch Type:	Chiclet Style with Scissor Mechanism
Keycaps Imaging Type:	Laser-Etched Keys
Key Illumination:	Caps Lock, Num. Lock, Keyboard Lock, Scroll Lock Keys,
Total Key Travel:	.08 in (2mm)
Operating Voltage:	+ 5VDC ± 5%
Storage Temperature:	-5° to 55° C
EMI - RFI:	Conforms to FCC Rules for Class B Computing Device
Waterproof/Dustproof Ratings:	IP68, NEMA 4X
Safety, Regulatory and Environmental Compliance:	IPx8, FCC Class B, CE, RoHS, WEEE, WHQL, Industrie <b>UK</b> Canada (IC) ICES-003, RSS-210, RED 2014/53/EU
Supported Card Types:	ISO 15693 (HID Seos®, HID™ iCLASS, HID™ iCLASS SE, ICODE SLI, ICODE SLI-S, ICODE SLI-L, ICODE SLIX, ICODE SLIX-S, ICODE SLIX-L, ICODE DNA), ISO 14443A (MIFAREClassic, MIFARE Classic EV1, MIFARE DESFire EV1, MIFARE DESFire EV2, MIFARE Plus, MIFARE SMART MX, NTAG2xx)(read only) 125 kHz (HID Prox II, HID PROX, HID DuoProx II, HID Micro Prox, HID ProxKey III, AWID, EM4100, HITAG1/S, HITAG2, Indala, Keri)
RF Frequency:	13.56MHz and 125kHz and 134.2kHz2
Read Range:	Up to 5cm
Mount Compatibility:	VESA Mount 200 x 100mm Hold Pattern



Copyright® 2020, Seal Shield, LLC. All rights reserved. All other trademarks and trade names are those of their respective owners