



# Poly Voyager 4310 USB-C Headset +BT700 dongle TAA (7E2L8AA)



## Overview

### Cut wires. Cut Costs.

Free your workers from their desks with the entry-level Bluetooth® wireless headset. Meet the Voyager 4300 UC Series. It's everything your teams need to stay productive and connect to all their devices whether at home or in the office.

### Freedom to work

Move freely between all your workspaces with this portable headset. Roam with ease with up to 50 m / 164 ft of wireless range. Reduce background noise and control your conversations with Acoustic Fence technology.

### Round-the-clock efficiency

Boost your productivity with continuous comfort, up to 24 hours of talk time, and connectivity to multiple devices. Extend your talk time by using the desktop charge stand or by using the headset in the corded USB mode.[1,2]

## Features

### Escape your desk

Walk-and-talk with ease with up to 50 meters / 164 feet of Bluetooth® wireless range with included BT700 USB adapter.

### It's your call

Stay productive with up to a full 24 hours of wireless talk time.<sup>[3]</sup>

### On-call indicator

Give those around you a visual cue that you're busy — an on-call indicator flashes on the ear cup when you're on a call.

### Corded USB mode

Extend the battery life of your headset by using it corded, with audio over USB mode.

### Easy management via Poly Lens

Take control of your deployment from anywhere via remote management with Poly Lens cloud-based device management software.

### Communications platforms

An IT manager's dream, this headset was created for communication and is optimized and certified to work with top virtual meeting providers.<sup>[4]</sup>

---

*[1] Connectivity includes: PC via included BT700 Bluetooth® adapter or via USB cable; smartphone via Bluetooth v5.2; desk phone with Voyager Office base, available as an accessory, sold separately.*

*[2] Desktop charge stand available with certain models or sold separately.*

*[3] Online indicator off. Requires setting change via Poly Lens.*

*[4] Visit <https://www.poly.com/us/en/products/headsets/voyager/voyager-4300-uc> for more detail.*

## Additional specifications

<b>Acoustic protection technology</b>	SoundGuard Digital <sup>[1,2]</sup>
<b>Audio</b>	Flexible noise cancellation; Noise cancellation with Acoustic Fence technology
<b>Battery life</b>	Up to 24 hours (talk time, online indicator off); Up to 18 hours (talk time, online indicator on); Up to 47 hours (music time); Up to 50 days (standby time)
<b>Battery type</b>	Rechargeable Li-ion
<b>Button user controls</b>	Call answer/end; Mute; Volume +/-; Power on/off; Pairing
<b>Cable length</b>	Up to 150 cm
<b>Cable length (imperial)</b>	Up to 5 ft
<b>Certified collaboration software</b>	Zoom
<b>Charge time</b>	<1.6 hours
<b>Color</b>	Black
<b>Compatibility</b>	Compatible with PCs via included BT700 USB-A Bluetooth® adapter and smartphones via Bluetooth®
<b>Compatible Operating Systems</b>	Windows; macOS
<b>Connection type</b>	Bluetooth® 5.2; USB Type-C®
<b>Ear cushions</b>	Artificial leather (surface material)
<b>Headphone type</b>	On-ear (monoaural)
<b>Indicator light</b>	On call; Connectivity
<b>Management Software</b>	Poly Lens
<b>Manufacturer Warranty</b>	Poly standard two-year limited warranty
<b>Microphone bandwidth</b>	100 Hz to 6.8 kHz
<b>Microphone type</b>	MEMS & ECM
<b>Number of microphones</b>	2
<b>Paired devices</b>	Up to 8
<b>Speaker size</b>	32 mm
<b>Special features</b>	Multipoint technology
<b>Supported bluetooth profiles</b>	A2DP; AVRCP; HFP; HSP
<b>UNSPSC code</b>	52161514
<b>UPC number</b>	197192156452
<b>Voice alerts</b>	Volume maximum; Volume minimum; Mute on; Mute off; Muted; Connection status; Talk time; Battery low
<b>Voice assistant</b>	Siri; Google
<b>What's in the box</b>	USB Type-C® charging cable; Quick start guide; Travel pouch; Wireless headset; BT700 Bluetooth® Type-C® adapter

**Wireless range**

Up to 50 m; Up to 91 m (with Voyager Office base)

**Wireless range (imperial)**

Up to 164 ft; Up to 300 ft (with Voyager Office base)

---

*[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA).*

*[2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.*

---

## Disclaimer — Copyright

Bluetooth® is a trademark owned by its proprietor and used by HP Inc. under license.

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Dec 13, 2023 7:49 AM UTC+0000